

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579948

Luminaire Tested: **FLD6C-90-D010 FEU6C-X-90-35 F6X-N-X-H**

Issue Date: 3/1/2023



**Test Information**

Test Method: LM-79-08  
Report Number: P579948  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 3/1/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: FLD6C-90-D010 FEU6C-X-90-35 F6X-N-X-H  
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 3500K, 90 CRI LEDS, 6LBNH TRIM

Light Source: -  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6177.0 lumens  
Efficiency: N/A  
Efficacy: 63.6 lumens/watt  
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct

Input Watts (W): 97.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P579948

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-35 F6X-N-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P579948

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-35 F6X-N-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93				93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87				87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81				81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75				75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70				70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65				65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61				61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58				58
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54				54
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51				51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	434083
5°	423337
10°	390624
15°	345836
20°	300279
25°	256841
30°	211754
35°	139448
40°	74962
45°	33189
50°	13458
55°	9711
60°	6162
65°	4410
70°	3638
75°	2393
80°	3567
85°	0



TEST NUMBER: P579948

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-35 F6X-N-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	712.1	11.5
10°-20°	1698.1	27.5
20°-30°	1945.3	31.5
30°-40°	1307.0	21.2
40°-50°	373.4	6.0
50°-60°	91.4	1.5
60°-70°	34.8	0.6
70°-80°	13.4	0.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4355.4	70.5
0°-40°	5662.5	91.7
0°-60°	6127.3	99.2
0°-90°	6177.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6177.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	7918	
5°	7693	712
15°	6094	1698
25°	4246	1945
35°	2084	1307
45°	428	373
55°	102	91
65°	34	35
75°	11	13
85°	0	2
90°	0	



TEST NUMBER: P579948

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-35 F6X-N-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	7918.3
2.5°	7862.1
5°	7692.9
7.5°	7388.7
10°	7017.3
12.5°	6543.9
15°	6093.6
17.5°	5620.6
20°	5147.2
22.5°	4696.9
25°	4246.2
27.5°	3829.5
30°	3345.2
32.5°	2703.1
35°	2083.7
37.5°	1520.5
40°	1047.5
42.5°	687.0
45°	428.1
47.5°	258.9
50°	157.8
52.5°	123.8
55°	101.6
57.5°	78.9
60°	56.2
62.5°	44.9
65°	34.0
67.5°	22.7
70°	22.7
72.5°	11.3
75°	11.3
77.5°	11.3
80°	11.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC







— 0°-180°







(END OF REPORT)