

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C05D010 FEU4C059027 F4LC-DFSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C05D010 FEU4C059027 F4LC-DFSSQ-MW
 Description: 4 INCH 500 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 2700K, 90CRI LEDS AND F4LC-DFSSQ TRIM WITH MW FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 617.0 lumens
 Efficiency: N/A
 Efficacy: 85.7 lumens/watt
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 7.2
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C05D010 FEU4C059027 F4LC-DFSSQ-MW

Luminous Intensity Polar Plot



TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C05D010 FEU4C059027 F4LC-DFSSQ-MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89				89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67				67
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46				46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41				41
8	65	53	45	40	64	52	45	39	51	44	39	50	44	39	49	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	34				34
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	31				31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	27866	27866	27866
5°	27420	27779	27856
10°	27659	27581	27698
15°	27171	27211	27291
20°	26543	26964	26841
25°	26424	26424	26605
30°	25692	25871	25915
35°	24889	25125	24689
40°	23718	24184	23982
45°	22447	22952	22229
50°	19769	21496	19649
55°	16015	19665	16082
60°	11714	16307	11482
65°	7123	11621	6941
70°	2765	6263	2652
75°	298	1678	298
80°	222	222	222
85°	0	0	0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C05D010 FEU4C059027 F4LC-DFSSQ-MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.3	4.4
10°-20°	77.2	12.5
20°-30°	114.5	18.6
30°-40°	132.6	21.5
40°-50°	127.2	20.6
50°-60°	93.5	15.2
60°-70°	40.4	6.5
70°-80°	4.4	0.7
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	218.9	35.5
0°-40°	351.5	57.0
0°-60°	572.2	92.7
0°-90°	617.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	617.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	289	289	289	289	289	
5°	283	286	287	287	288	27
15°	272	274	272	273	273	77
25°	248	248	248	249	250	114
35°	211	212	213	213	210	132
45°	164	165	168	166	163	125
55°	95	105	117	105	96	86
65°	31	39	51	39	30	32
75°	1	1	4	1	1	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C05D010 FEU4C059027 F4LC-DFSSQ-MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	288.8	288.8	288.8	288.8	288.8	288.8	288.8	288.8	288.8	288.8	288.8
2.5°	286.8	290.1	290.5	288.4	287.6	286.4	289.2	287.2	288.0	287.2	286.8
5°	283.1	286.8	287.2	287.2	286.4	286.0	287.2	286.8	286.4	285.6	286.8
7.5°	281.5	283.5	285.6	283.1	284.3	283.9	286.8	285.6	285.1	285.1	284.3
10°	282.3	281.9	283.5	281.0	281.9	281.0	283.5	283.5	282.7	281.9	281.5
12.5°	275.7	279.0	279.0	278.6	277.8	276.5	279.0	280.6	278.2	278.2	277.8
15°	272.0	272.8	273.2	273.2	272.8	273.7	274.9	273.2	273.7	271.6	272.4
17.5°	267.9	266.3	267.5	266.7	267.1	267.9	269.6	269.6	267.1	266.7	267.5
20°	258.5	263.4	263.8	261.4	261.8	261.8	264.6	262.2	263.8	261.8	262.6
22.5°	254.0	257.2	257.7	254.4	256.4	254.0	256.8	253.1	257.2	254.4	255.6
25°	248.2	247.8	249.0	247.4	247.8	247.8	249.9	248.2	249.4	247.8	248.2
27.5°	238.8	242.1	241.6	240.0	240.8	240.4	244.5	240.0	242.5	240.4	241.2
30°	230.6	233.4	232.6	231.0	231.0	229.7	234.3	233.0	232.6	232.6	232.2
32.5°	222.4	222.8	222.0	222.4	222.8	221.1	224.8	223.2	222.8	223.2	223.6
35°	211.3	211.3	212.1	210.9	212.5	212.5	215.8	213.7	213.3	212.1	213.3
37.5°	201.4	200.2	200.6	200.6	201.4	202.3	203.9	203.1	203.1	201.9	202.7
40°	188.3	187.5	188.7	188.7	190.0	190.0	191.6	190.8	192.0	192.0	192.0
42.5°	176.8	176.8	176.0	177.2	177.7	177.2	180.1	179.7	180.1	179.3	179.7
45°	164.5	164.5	163.7	163.3	165.3	164.9	168.2	167.0	168.6	167.8	168.2
47.5°	147.7	149.7	148.5	149.7	152.2	152.6	154.7	153.9	155.5	154.3	155.9
50°	131.7	131.7	132.9	134.6	137.0	137.4	139.9	141.5	142.4	142.8	143.2
52.5°	114.9	114.5	115.7	117.7	119.8	121.4	123.9	126.4	128.0	130.5	129.2
55°	95.2	96.0	97.2	99.7	103.0	105.0	107.1	110.4	113.2	114.5	116.9
57.5°	78.4	77.5	78.4	81.6	85.3	87.0	89.9	93.1	97.2	99.7	100.5
60°	60.7	61.1	62.0	64.8	67.7	70.2	71.4	76.7	80.4	82.9	84.5
62.5°	44.7	45.5	46.4	48.8	51.7	53.7	55.8	60.3	63.6	66.1	67.7
65°	31.2	31.6	32.8	34.0	36.9	39.0	40.6	44.3	47.6	49.6	50.9
67.5°	19.3	19.7	20.5	22.2	24.2	25.8	27.5	29.9	32.8	34.9	35.3
70°	9.8	10.3	10.7	11.9	13.5	14.4	15.6	17.6	19.7	21.3	22.2
72.5°	3.3	3.3	3.7	4.5	5.3	6.2	6.6	8.6	10.3	11.1	11.5
75°	0.8	0.8	0.8	0.8	0.8	1.2	1.2	2.5	3.3	4.1	4.5
77.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.8	0.8
80°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C05D010 FEU4C059027 F4LC-DFSSQ-MW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	288.8	288.8	288.8	288.8	288.8	288.8	288.8	288.8	288.8	288.8
2.5°	288.8	288.0	287.6	288.0	288.0	287.6	288.8	290.5	292.5	287.2
5°	288.4	287.6	288.4	286.0	287.2	286.4	288.0	287.6	289.2	287.6
7.5°	287.2	285.6	286.0	284.7	286.4	284.3	285.6	288.0	286.4	283.9
10°	283.1	282.3	285.1	281.0	280.2	281.9	285.1	282.7	281.9	282.7
12.5°	279.0	279.0	280.2	276.9	277.3	278.2	279.8	278.2	279.0	281.0
15°	274.5	273.7	275.7	273.2	272.8	272.0	273.7	273.7	274.5	273.2
17.5°	269.1	267.9	267.9	267.1	266.7	268.7	269.6	270.0	270.4	268.7
20°	262.6	262.2	263.4	262.2	262.6	263.0	263.0	262.2	265.9	261.4
22.5°	255.6	256.8	255.2	254.4	255.2	256.0	256.0	256.4	255.6	254.8
25°	248.6	249.4	249.9	247.4	248.6	247.4	250.3	250.7	249.0	249.9
27.5°	242.5	241.2	240.8	239.2	240.0	239.6	240.0	240.0	242.5	239.2
30°	233.0	231.8	232.2	231.0	231.4	231.0	231.4	231.4	233.0	232.6
32.5°	224.0	222.8	223.2	222.0	222.0	222.4	221.5	221.5	222.8	222.0
35°	215.4	212.5	212.9	212.5	212.9	211.3	211.3	210.9	211.7	209.6
37.5°	203.1	201.9	201.4	201.0	201.4	200.6	201.4	200.2	201.4	199.8
40°	192.0	191.2	191.6	189.1	189.1	189.5	188.7	188.3	188.7	190.4
42.5°	180.9	179.3	178.5	177.7	178.1	176.8	176.4	175.6	176.4	174.8
45°	167.8	167.8	167.4	165.3	165.8	165.8	164.1	162.5	162.9	162.9
47.5°	155.9	155.1	154.7	152.6	152.2	151.8	150.2	148.9	148.9	147.7
50°	142.8	141.9	140.7	138.7	137.8	135.4	134.2	132.5	130.9	130.9
52.5°	130.5	127.6	125.9	122.7	121.4	120.2	116.9	115.7	114.5	113.2
55°	115.7	113.2	110.0	106.3	104.6	102.6	99.3	96.8	95.2	95.6
57.5°	101.3	97.2	94.0	89.0	87.0	85.7	82.5	79.2	77.5	77.5
60°	83.7	80.4	76.3	71.8	70.2	68.1	64.0	62.0	60.7	59.5
62.5°	66.9	64.4	60.7	55.0	53.7	51.7	48.8	46.4	45.1	45.1
65°	50.1	47.6	44.3	40.2	38.6	36.9	34.5	32.0	30.8	30.4
67.5°	35.3	32.4	29.5	26.3	25.0	24.2	21.7	20.1	19.3	18.9
70°	21.3	19.7	17.6	15.2	13.9	13.1	11.5	10.3	9.8	9.4
72.5°	11.1	9.8	8.2	6.6	5.7	4.9	4.1	3.3	2.9	2.9
75°	4.1	3.3	2.1	1.2	0.8	0.8	0.8	0.8	0.8	0.8
77.5°	0.8	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
80°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)