

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P579988

Luminaire Tested: **FLD6C-90-D010 FEU6C-X-90-40 F6X-M-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P579988
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-90-D010 FEU6C-X-90-40 F6X-M-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 6LBMH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7191.0 lumens
Efficiency: N/A
Efficacy: 74.1 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P579988

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-40 F6X-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P579988

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-40 F6X-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	390133
5°	383149
10°	363570
15°	340933
20°	317513
25°	292559
30°	243765
35°	171812
40°	109498
45°	65301
50°	38540
55°	24525
60°	16885
65°	11986
70°	8255
75°	6524
80°	3189
85°	0



TEST NUMBER: P579988

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-40 F6X-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	650.7	9.0
10°-20°	1683.3	23.4
20°-30°	2181.1	30.3
30°-40°	1619.3	22.5
40°-50°	683.6	9.5
50°-60°	242.7	3.4
60°-70°	93.7	1.3
70°-80°	32.4	0.5
80°-90°	4.1	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4515.1	62.8
0°-40°	6134.4	85.3
0°-60°	7060.8	98.2
0°-90°	7191.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	7191.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7117	
5°	6963	651
15°	6007	1683
25°	4837	2181
35°	2567	1619
45°	842	684
55°	257	243
65°	92	94
75°	31	32
85°	0	4
90°	0	



TEST NUMBER: P579988

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-40 F6X-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7116.6
2.5°	7095.9
5°	6962.6
7.5°	6767.2
10°	6531.3
12.5°	6274.4
15°	6007.2
17.5°	5709.7
20°	5442.6
22.5°	5165.4
25°	4836.7
27.5°	4384.8
30°	3850.9
32.5°	3224.3
35°	2567.3
37.5°	2012.8
40°	1530.1
42.5°	1139.8
45°	842.3
47.5°	616.1
50°	451.9
52.5°	338.8
55°	256.6
57.5°	195.0
60°	154.0
62.5°	113.1
65°	92.4
67.5°	71.7
70°	51.5
72.5°	40.9
75°	30.8
77.5°	20.7
80°	10.1
82.5°	10.1
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)