

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C05D010 FEU4C059030 F4LC-CSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.



Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C05D010 FEU4C059030 F4LC-CSSQ-MW
 Description: 4 INCH 500 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND F4LC-CSSQ TRIM WITH MW FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 642.0 lumens
 Efficiency: N/A
 Efficacy: 89.2 lumens/watt
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 7.2
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C05D010 FEU4C059030 F4LC-CSSQ-MW

Luminous Intensity Polar Plot



TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C05D010 FEU4C059030 F4LC-CSSQ-MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96		97	95	94		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	74	71		77	73	69	67
4	88	77	70	64	86	76	69	63	74	67	63		71	66	62		69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55		65	59	54		63	58	54	52
6	75	63	55	49	73	62	55	49	61	54	49		59	53	48		57	52	48	46
7	70	58	50	44	68	57	49	44	55	49	44		54	48	43		53	47	43	41
8	65	53	45	40	64	52	45	39	51	44	39		50	44	39		49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36		46	40	35		45	39	35	33
10	57	45	38	33	56	44	37	33	44	37	32		43	37	32		42	36	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	28995	28995	28995
5°	28534	28902	28989
10°	28776	28698	28815
15°	28270	28320	28399
20°	27611	28053	27919
25°	27500	27500	27681
30°	26729	26918	26974
35°	25891	26150	25690
40°	24675	25166	24952
45°	23361	23880	23129
50°	20565	22366	20445
55°	16654	20473	16738
60°	12196	16963	11945
65°	7397	12078	7215
70°	2878	6517	2765
75°	336	1752	336
80°	222	222	222
85°	0	0	0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C05D010 FEU4C059030 F4LC-CSSQ-MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.4	4.4
10°-20°	80.3	12.5
20°-30°	119.1	18.6
30°-40°	138.0	21.5
40°-50°	132.3	20.6
50°-60°	97.3	15.2
60°-70°	42.0	6.5
70°-80°	4.5	0.7
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	227.8	35.5
0°-40°	365.8	57.0
0°-60°	595.4	92.7
0°-90°	642.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	642.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	300	300	300	300	300	
5°	295	298	298	299	299	28
15°	283	285	284	284	284	80
25°	258	258	258	259	260	118
35°	220	221	222	222	218	137
45°	171	172	175	172	170	130
55°	99	109	122	109	100	89
65°	32	40	53	40	32	33
75°	1	1	5	1	1	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C05D010 FEU4C059030 F4LC-CSSQ-MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	300.5	300.5	300.5	300.5	300.5	300.5	300.5	300.5	300.5	300.5	300.5
2.5°	298.4	301.8	302.2	300.1	299.3	298.0	301.0	298.8	299.7	298.8	298.4
5°	294.6	298.4	298.8	298.8	298.0	297.5	298.8	298.4	298.0	297.1	298.4
7.5°	292.9	295.0	297.1	294.6	295.8	295.4	298.4	297.1	296.7	296.7	295.8
10°	293.7	293.3	295.0	292.4	293.3	292.4	295.0	295.0	294.1	293.3	292.9
12.5°	286.9	290.3	290.3	289.9	289.0	287.7	290.3	292.0	289.4	289.4	289.0
15°	283.0	283.9	284.3	284.3	283.9	284.7	286.0	284.3	284.7	282.6	283.5
17.5°	278.8	277.1	278.3	277.5	277.9	278.8	280.5	280.5	277.9	277.5	278.3
20°	268.9	274.1	274.5	271.9	272.4	272.4	275.4	272.8	274.5	272.4	273.2
22.5°	264.2	267.7	268.1	264.7	266.8	264.2	267.2	263.4	267.7	264.7	265.9
25°	258.3	257.8	259.1	257.4	257.8	257.8	260.0	258.3	259.6	257.8	258.3
27.5°	248.5	251.9	251.4	249.7	250.6	250.2	254.4	249.7	252.3	250.2	251.0
30°	239.9	242.9	242.1	240.3	240.3	239.1	243.8	242.5	242.1	242.1	241.6
32.5°	231.4	231.8	231.0	231.4	231.8	230.1	233.9	232.2	231.8	232.2	232.7
35°	219.8	219.8	220.7	219.4	221.1	221.1	224.5	222.4	222.0	220.7	222.0
37.5°	209.6	208.3	208.7	208.7	209.6	210.5	212.2	211.3	211.3	210.0	210.9
40°	195.9	195.1	196.4	196.4	197.7	197.7	199.4	198.5	199.8	199.8	199.8
42.5°	184.0	184.0	183.1	184.4	184.9	184.4	187.4	187.0	187.4	186.6	187.0
45°	171.2	171.2	170.3	169.9	172.0	171.6	175.0	173.7	175.4	174.6	175.0
47.5°	153.7	155.8	154.5	155.8	158.4	158.8	160.9	160.1	161.8	160.5	162.2
50°	137.0	137.0	138.3	140.0	142.6	143.0	145.6	147.3	148.1	148.6	149.0
52.5°	119.5	119.1	120.4	122.5	124.7	126.4	128.9	131.5	133.2	135.8	134.5
55°	99.0	99.9	101.2	103.7	107.2	109.3	111.4	114.8	117.8	119.1	121.7
57.5°	81.5	80.7	81.5	84.9	88.8	90.5	93.5	96.9	101.2	103.7	104.6
60°	63.2	63.6	64.5	67.5	70.4	73.0	74.3	79.8	83.7	86.2	87.9
62.5°	46.5	47.4	48.2	50.8	53.8	55.9	58.1	62.8	66.2	68.7	70.4
65°	32.4	32.9	34.2	35.4	38.4	40.5	42.3	46.1	49.5	51.7	52.9
67.5°	20.1	20.5	21.3	23.1	25.2	26.9	28.6	31.2	34.2	36.3	36.7
70°	10.2	10.7	11.1	12.4	14.1	14.9	16.2	18.4	20.5	22.2	23.1
72.5°	3.4	3.4	3.8	4.7	5.6	6.4	6.8	9.0	10.7	11.5	11.9
75°	0.9	0.9	0.9	0.9	0.9	1.3	1.3	2.6	3.4	4.3	4.7
77.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.9	0.9
80°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C05D010 FEU4C059030 F4LC-CSSQ-MW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	300.5	300.5	300.5	300.5	300.5	300.5	300.5	300.5	300.5	300.5
2.5°	300.5	299.7	299.3	299.7	299.7	299.3	300.5	302.2	304.4	298.8
5°	300.1	299.3	300.1	297.5	298.8	298.0	299.7	299.3	301.0	299.3
7.5°	298.8	297.1	297.5	296.3	298.0	295.8	297.1	299.7	298.0	295.4
10°	294.6	293.7	296.7	292.4	291.6	293.3	296.7	294.1	293.3	294.1
12.5°	290.3	290.3	291.6	288.2	288.6	289.4	291.1	289.4	290.3	292.4
15°	285.6	284.7	286.9	284.3	283.9	283.0	284.7	284.7	285.6	284.3
17.5°	280.0	278.8	278.8	277.9	277.5	279.6	280.5	280.9	281.3	279.6
20°	273.2	272.8	274.1	272.8	273.2	273.6	273.6	272.8	276.6	271.9
22.5°	265.9	267.2	265.5	264.7	265.5	266.4	266.4	266.8	265.9	265.1
25°	258.7	259.6	260.0	257.4	258.7	257.4	260.4	260.8	259.1	260.0
27.5°	252.3	251.0	250.6	248.9	249.7	249.3	249.7	249.7	252.3	248.9
30°	242.5	241.2	241.6	240.3	240.8	240.3	240.8	240.8	242.5	242.1
32.5°	233.1	231.8	232.2	231.0	231.0	231.4	230.5	230.5	231.8	231.0
35°	224.1	221.1	221.6	221.1	221.6	219.8	219.8	219.4	220.3	218.1
37.5°	211.3	210.0	209.6	209.2	209.6	208.7	209.6	208.3	209.6	207.9
40°	199.8	198.9	199.4	196.8	196.8	197.2	196.4	195.9	196.4	198.1
42.5°	188.3	186.6	185.7	184.9	185.3	184.0	183.6	182.7	183.6	181.9
45°	174.6	174.6	174.2	172.0	172.5	172.5	170.8	169.1	169.5	169.5
47.5°	162.2	161.4	160.9	158.8	158.4	158.0	156.2	155.0	155.0	153.7
50°	148.6	147.7	146.4	144.3	143.4	140.9	139.6	137.9	136.2	136.2
52.5°	135.8	132.8	131.1	127.6	126.4	125.1	121.7	120.4	119.1	117.8
55°	120.4	117.8	114.4	110.6	108.9	106.7	103.3	100.7	99.0	99.5
57.5°	105.4	101.2	97.8	92.6	90.5	89.2	85.8	82.4	80.7	80.7
60°	87.1	83.7	79.4	74.7	73.0	70.9	66.6	64.5	63.2	61.9
62.5°	69.6	67.0	63.2	57.2	55.9	53.8	50.8	48.2	47.0	47.0
65°	52.1	49.5	46.1	41.8	40.1	38.4	35.9	33.3	32.0	31.6
67.5°	36.7	33.7	30.7	27.3	26.0	25.2	22.6	20.9	20.1	19.6
70°	22.2	20.5	18.4	15.8	14.5	13.7	11.9	10.7	10.2	9.8
72.5°	11.5	10.2	8.5	6.8	6.0	5.1	4.3	3.4	3.0	3.0
75°	4.3	3.4	2.1	1.3	0.9	0.9	0.9	0.9	0.9	0.9
77.5°	0.9	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
80°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)