

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P580008

Luminaire Tested: **FLD6C-90-D010 FEU6C-X-90-40 F6X-N-X-H**

Issue Date: 3/1/2023



Test Information

Test Method: LM-79-08
Report Number: P580008
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 3/1/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: FLD6C-90-D010 FEU6C-X-90-40 F6X-N-X-H
Description: 6 INCH FAIL-SAFE LED DOWNLIGHT WITH 4000K, 90 CRI LEDS, 6LBNH TRIM

Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6186.9 lumens
Efficiency: N/A
Efficacy: 63.7 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 97.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P580008

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-40 F6X-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P580008

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-40 F6X-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93			
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81			
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75			
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70			
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65			
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61			
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58			
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54			
10	72	62	57	53	71	62	57	53	61	56	53	60	56	52	60	55	52	51			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	434784
5°	424025
10°	391253
15°	346392
20°	300769
25°	257259
30°	212096
35°	139668
40°	75084
45°	33244
50°	13475
55°	9720
60°	6173
65°	4410
70°	3638
75°	2393
80°	3567
85°	0



TEST NUMBER: P580008

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-40 F6X-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	713.2	11.5
10°-20°	1700.8	27.5
20°-30°	1948.5	31.5
30°-40°	1309.1	21.2
40°-50°	374.0	6.0
50°-60°	91.5	1.5
60°-70°	34.8	0.6
70°-80°	13.4	0.2
80°-90°	1.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	4362.5	70.5
0°-40°	5671.6	91.7
0°-60°	6137.2	99.2
0°-90°	6186.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	6186.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7931	
5°	7705	713
15°	6103	1701
25°	4253	1948
35°	2087	1309
45°	429	374
55°	102	92
65°	34	35
75°	11	13
85°	0	2
90°	0	



TEST NUMBER: P580008

CATALOG NUMBER: FLD6C-90-D010 FEU6C-X-90-40 F6X-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7931.1
2.5°	7874.8
5°	7705.4
7.5°	7400.6
10°	7028.6
12.5°	6554.5
15°	6103.4
17.5°	5629.7
20°	5155.6
22.5°	4704.5
25°	4253.1
27.5°	3835.7
30°	3350.6
32.5°	2707.5
35°	2087.0
37.5°	1522.9
40°	1049.2
42.5°	688.1
45°	428.8
47.5°	259.4
50°	158.0
52.5°	124.0
55°	101.7
57.5°	79.0
60°	56.3
62.5°	45.0
65°	34.0
67.5°	22.7
70°	22.7
72.5°	11.3
75°	11.3
77.5°	11.3
80°	11.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0



Report Generated By 670246072 / DESKTOP-MV3F9LC





— 0°-180°







(END OF REPORT)