

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C50D010 FEU4C509030 F4LC-SQ-H**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P#  
 Test Lab: INNOVATION CENTER  
 Issue Date: 12/13/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: FAIL-SAFE  
 Catalog Number: FLDSQ4C50D010 FEU4C509030 F4LC-SQ-H  
 Description: 4 INCH 5000 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND F4LC-SQ TRIM WITH H FINISH  
 Light Source: -  
 Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 4201.9 lumens  
 Efficiency: N/A  
 Efficacy: 72.0 lumens/watt  
 Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
 CIE Type: Direct

Input Watts (W): 58.4  
 Input Voltage (V):  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#  
CATALOG NUMBER: FLDSQ4C50D010 FEU4C509030 F4LC-SQ-H

### Luminous Intensity Polar Plot





TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C50D010 FEU4C509030 F4LC-SQ-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100		100	99	97		97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91		94	91	89		91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83		88	84	82		86	83	80	79
4	96	88	82	77	94	86	81	77	84	80	76		82	78	75		80	77	74	73
5	90	82	75	71	89	81	75	70	79	74	70		77	73	69		75	72	69	67
6	86	76	70	65	84	75	69	65	74	68	64		72	68	64		71	67	64	62
7	81	71	65	60	80	70	64	60	69	64	60		68	63	59		67	62	59	58
8	77	67	60	56	75	66	60	56	65	59	56		64	59	55		63	58	55	54
9	73	63	56	52	72	62	56	52	61	56	52		60	55	52		59	55	52	50
10	69	59	53	49	68	59	53	49	58	52	49		57	52	48		56	52	48	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	402021
5°	396186
10°	379633
15°	358565
20°	334700
25°	303826
30°	253671
35°	183766
40°	115037
45°	65758
50°	34285
55°	19211
60°	12235
65°	7237
70°	5360
75°	2349
80°	3501
85°	0

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C50D010 FEU4C509030 F4LC-SQ-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	383.4	9.1
10°-20°	1005.8	23.9
20°-30°	1292.6	30.8
30°-40°	972.5	23.1
40°-50°	390.6	9.3
50°-60°	111.0	2.6
60°-70°	35.1	0.8
70°-80°	10.0	0.2
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2681.8	63.8
0°-40°	3654.3	87.0
0°-60°	4156.0	98.9
0°-90°	4201.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4201.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	4166	
5°	4090	383
15°	3590	1006
25°	2854	1293
35°	1560	973
45°	482	391
55°	114	111
65°	32	35
75°	6	10
85°	0	1
90°	0	

TEST NUMBER: P#  
CATALOG NUMBER: FLDSQ4C50D010 FEU4C509030 F4LC-SQ-H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	4166.5
2.5°	4141.2
5°	4090.4
7.5°	3995.2
10°	3874.7
12.5°	3729.1
15°	3589.5
17.5°	3430.9
20°	3259.6
22.5°	3075.9
25°	2853.8
27.5°	2587.4
30°	2276.8
32.5°	1927.8
35°	1560.1
37.5°	1217.5
40°	913.3
42.5°	672.2
45°	481.9
47.5°	329.9
50°	228.4
52.5°	158.6
55°	114.2
57.5°	82.5
60°	63.4
62.5°	44.4
65°	31.7
67.5°	25.4
70°	19.0
72.5°	12.7
75°	6.3
77.5°	6.3
80°	6.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)