

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C100D010 FEU4C1009030 F4LC-DFSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C100D010 FEU4C1009030 F4LC-DFSSQ-MW
 Description: 4 INCH 10000 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND F4LC-DFSSQ TRIM WITH MW FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 9943.0 lumens
 Efficiency: N/A
 Efficacy: 86.9 lumens/watt
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 114.4
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C100D010 FEU4C1009030 F4LC-DFSSQ-MW

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: FLDSQ4C100D010 FEU4C1009030 F4LC-DFSSQ-MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89				89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67				67
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46				46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41				41
8	65	53	45	40	64	52	45	39	51	44	39	50	44	39	49	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	33				33
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	31				31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	449117	449117	449117
5°	441873	447627	448905
10°	445689	444396	446326
15°	437879	438529	439847
20°	427699	434486	432463
25°	425844	425844	428666
30°	413976	416929	417675
35°	401067	404966	397946
40°	382243	389724	386399
45°	361772	369905	358156
50°	318594	346379	316612
55°	258021	316966	259165
60°	188809	262836	185008
65°	114750	187170	111713
70°	44743	100771	42910
75°	4921	27140	4921
80°	3723	3723	3723
85°	0	0	0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C100D010 FEU4C1009030 F4LC-DFSSQ-MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	439.4	4.4
10°-20°	1243.3	12.5
20°-30°	1844.7	18.6
30°-40°	2137.5	21.5
40°-50°	2049.4	20.6
50°-60°	1506.8	15.2
60°-70°	650.8	6.5
70°-80°	70.2	0.7
80°-90°	0.9	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3527.3	35.5
0°-40°	5664.8	57.0
0°-60°	9221.0	92.7
0°-90°	9943.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	9943.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4655	4655	4655	4655	4655	
5°	4562	4608	4622	4628	4635	435
15°	4384	4410	4390	4397	4403	1235
25°	4000	3994	4000	4007	4026	1831
35°	3405	3425	3438	3431	3378	2129
45°	2651	2658	2711	2671	2625	2015
55°	1534	1692	1884	1686	1541	1380
65°	503	628	820	622	489	517
75°	13	20	73	13	13	41
85°	0	0	0	0	0	1
90°	0	0	0	0	0	

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C100D010 FEU4C1009030 F4LC-DFSSQ-MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	4654.6	4654.6	4654.6	4654.6	4654.6	4654.6	4654.6	4654.6	4654.6	4654.6	4654.6
2.5°	4621.5	4674.3	4681.1	4647.9	4634.7	4615.0	4661.1	4628.2	4641.4	4628.2	4621.5
5°	4562.1	4621.5	4628.2	4628.2	4615.0	4608.2	4628.2	4621.5	4615.0	4601.8	4621.5
7.5°	4535.7	4568.6	4601.8	4562.1	4581.8	4575.3	4621.5	4601.8	4595.0	4595.0	4581.8
10°	4548.9	4542.1	4568.6	4528.9	4542.1	4528.9	4568.6	4568.6	4555.4	4542.1	4535.7
12.5°	4442.9	4495.7	4495.7	4489.3	4476.1	4456.1	4495.7	4522.4	4482.5	4482.5	4476.1
15°	4383.5	4396.7	4403.2	4403.2	4396.7	4410.0	4429.7	4403.2	4410.0	4376.8	4390.0
17.5°	4317.4	4291.0	4310.7	4297.5	4304.2	4317.4	4343.9	4343.9	4304.2	4297.5	4310.7
20°	4165.3	4244.6	4251.3	4211.7	4218.2	4218.2	4264.6	4224.9	4251.3	4218.2	4231.4
22.5°	4092.5	4145.3	4152.1	4099.2	4132.1	4092.5	4138.9	4079.2	4145.3	4099.2	4118.9
25°	3999.9	3993.5	4013.2	3986.7	3993.5	3993.5	4026.4	3999.9	4019.9	3993.5	3999.9
27.5°	3848.1	3900.9	3894.2	3867.8	3881.0	3874.5	3940.6	3867.8	3907.4	3874.5	3887.7
30°	3715.6	3762.0	3748.8	3722.4	3722.4	3702.4	3775.2	3755.3	3748.8	3748.8	3742.1
32.5°	3583.4	3590.2	3577.0	3583.4	3590.2	3563.7	3623.1	3596.7	3590.2	3596.7	3603.4
35°	3404.9	3404.9	3418.1	3398.4	3424.8	3424.8	3477.7	3444.5	3438.0	3418.1	3438.0
37.5°	3246.2	3226.5	3233.0	3233.0	3246.2	3259.5	3285.9	3272.7	3272.7	3253.0	3266.2
40°	3034.7	3021.5	3041.2	3041.2	3061.2	3061.2	3087.6	3074.4	3094.1	3094.1	3094.1
42.5°	2849.7	2849.7	2836.5	2856.2	2862.9	2856.2	2902.6	2895.8	2902.6	2889.3	2895.8
45°	2651.2	2651.2	2637.9	2631.5	2664.4	2657.9	2710.8	2690.8	2717.3	2704.0	2710.8
47.5°	2380.1	2413.2	2393.3	2413.2	2452.9	2459.6	2492.5	2479.3	2505.8	2486.1	2512.5
50°	2122.4	2122.4	2142.1	2168.6	2208.2	2215.0	2254.6	2281.0	2294.3	2300.7	2307.5
52.5°	1851.3	1844.6	1864.5	1897.5	1930.6	1957.1	1996.7	2036.4	2062.8	2102.5	2082.5
55°	1533.8	1547.0	1567.0	1606.7	1659.5	1692.4	1725.6	1778.5	1824.9	1844.6	1884.2
57.5°	1262.7	1249.5	1262.7	1315.6	1375.2	1401.6	1448.0	1500.9	1567.0	1606.7	1619.9
60°	978.4	985.1	998.4	1044.8	1090.9	1130.5	1150.5	1236.3	1295.9	1335.6	1362.0
62.5°	720.8	734.0	747.2	786.9	833.0	866.2	899.1	971.9	1024.8	1064.5	1090.9
65°	502.6	509.0	529.0	548.7	595.1	628.0	654.4	714.0	766.9	800.1	819.8
67.5°	310.8	317.2	330.5	357.2	390.1	416.5	442.9	482.6	529.0	561.9	568.6
70°	158.6	165.4	171.8	191.8	218.2	231.4	251.1	284.3	317.2	343.7	357.2
72.5°	52.9	52.9	59.6	72.8	86.0	99.3	105.7	138.9	165.4	178.6	185.1
75°	13.2	13.2	13.2	13.2	13.2	20.0	20.0	39.7	52.9	66.1	72.8
77.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	13.2	13.2
80°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C100D010 FEU4C1009030 F4LC-DFSSQ-MW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	4654.6	4654.6	4654.6	4654.6	4654.6	4654.6	4654.6	4654.6	4654.6	4654.6
2.5°	4654.6	4641.4	4634.7	4641.4	4641.4	4634.7	4654.6	4681.1	4714.0	4628.2
5°	4647.9	4634.7	4647.9	4608.2	4628.2	4615.0	4641.4	4634.7	4661.1	4634.7
7.5°	4628.2	4601.8	4608.2	4588.5	4615.0	4581.8	4601.8	4641.4	4615.0	4575.3
10°	4562.1	4548.9	4595.0	4528.9	4515.7	4542.1	4595.0	4555.4	4542.1	4555.4
12.5°	4495.7	4495.7	4515.7	4462.8	4469.3	4482.5	4509.0	4482.5	4495.7	4528.9
15°	4423.2	4410.0	4442.9	4403.2	4396.7	4383.5	4410.0	4410.0	4423.2	4403.2
17.5°	4337.1	4317.4	4317.4	4304.2	4297.5	4330.6	4343.9	4350.3	4357.1	4330.6
20°	4231.4	4224.9	4244.6	4224.9	4231.4	4238.1	4238.1	4224.9	4284.3	4211.7
22.5°	4118.9	4138.9	4112.4	4099.2	4112.4	4125.6	4125.6	4132.1	4118.9	4105.7
25°	4006.7	4019.9	4026.4	3986.7	4006.7	3986.7	4033.1	4039.6	4013.2	4026.4
27.5°	3907.4	3887.7	3881.0	3854.5	3867.8	3861.3	3867.8	3867.8	3907.4	3854.5
30°	3755.3	3735.6	3742.1	3722.4	3728.8	3722.4	3728.8	3728.8	3755.3	3748.8
32.5°	3609.9	3590.2	3596.7	3577.0	3577.0	3583.4	3570.2	3570.2	3590.2	3577.0
35°	3470.9	3424.8	3431.3	3424.8	3431.3	3404.9	3404.9	3398.4	3411.6	3378.4
37.5°	3272.7	3253.0	3246.2	3239.8	3246.2	3233.0	3246.2	3226.5	3246.2	3219.8
40°	3094.1	3080.9	3087.6	3048.0	3048.0	3054.4	3041.2	3034.7	3041.2	3067.7
42.5°	2915.8	2889.3	2876.1	2862.9	2869.4	2849.7	2843.0	2829.7	2843.0	2816.5
45°	2704.0	2704.0	2697.6	2664.4	2671.1	2671.1	2644.7	2618.2	2624.7	2624.7
47.5°	2512.5	2499.3	2492.5	2459.6	2452.9	2446.4	2419.7	2400.0	2400.0	2380.1
50°	2300.7	2287.5	2267.8	2234.7	2221.4	2181.8	2162.1	2135.6	2109.2	2109.2
52.5°	2102.5	2056.1	2029.6	1976.8	1957.1	1937.1	1884.2	1864.5	1844.6	1824.9
55°	1864.5	1824.9	1772.0	1712.4	1686.0	1652.8	1599.9	1560.3	1533.8	1540.6
57.5°	1633.1	1567.0	1514.1	1434.8	1401.6	1381.7	1328.8	1275.9	1249.5	1249.5
60°	1348.8	1295.9	1229.8	1157.0	1130.5	1097.6	1031.3	998.4	978.4	958.7
62.5°	1077.7	1038.0	978.4	885.9	866.2	833.0	786.9	747.2	727.3	727.3
65°	806.6	766.9	714.0	648.0	621.5	595.1	555.4	515.8	495.8	489.3
67.5°	568.6	522.2	476.1	423.2	403.3	390.1	350.4	324.0	310.8	304.0
70°	343.7	317.2	284.3	244.7	224.7	211.5	185.1	165.4	158.6	152.1
72.5°	178.6	158.6	132.2	105.7	92.5	79.3	66.1	52.9	46.4	46.4
75°	66.1	52.9	33.2	20.0	13.2	13.2	13.2	13.2	13.2	13.2
77.5°	13.2	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
80°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)