

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C55D010 FEU4C559035 F4LC-DFSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C55D010 FEU4C559035 F4LC-DFSSQ-MW
 Description: 4 INCH 5500 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND F4LC-DFSSQ TRIM WITH MW FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 5870.0 lumens
 Efficiency: N/A
 Efficacy: 91.9 lumens/watt
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 63.9
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C55D010 FEU4C559035 F4LC-DFSSQ-MW

Luminous Intensity Polar Plot



TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C55D010 FEU4C559035 F4LC-DFSSQ-MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	259.4	4.4
10°-20°	734.0	12.5
20°-30°	1089.1	18.6
30°-40°	1261.9	21.5
40°-50°	1209.9	20.6
50°-60°	889.6	15.2
60°-70°	384.2	6.5
70°-80°	41.5	0.7
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2082.4	35.5
0°-40°	3344.3	57.0
0°-60°	5443.8	92.7
0°-90°	5870.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	5870.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2748	2748	2748	2748	2748	
5°	2693	2720	2728	2732	2736	257
15°	2588	2604	2592	2596	2600	729
25°	2361	2358	2361	2365	2377	1081
35°	2010	2022	2030	2026	1994	1257
45°	1565	1569	1600	1577	1550	1190
55°	906	999	1112	995	910	815
65°	297	371	484	367	289	305
75°	8	12	43	8	8	24
85°	0	0	0	0	0	1
90°	0	0	0	0	0	



TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C55D010 FEU4C559035 F4LC-DFSSQ-MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2747.9	2747.9	2747.9	2747.9	2747.9	2747.9	2747.9	2747.9	2747.9	2747.9	2747.9
2.5°	2728.3	2759.6	2763.5	2744.0	2736.1	2724.5	2751.8	2732.3	2740.1	2732.3	2728.3
5°	2693.3	2728.3	2732.3	2732.3	2724.5	2720.5	2732.3	2728.3	2724.5	2716.7	2728.3
7.5°	2677.7	2697.1	2716.7	2693.3	2704.9	2701.1	2728.3	2716.7	2712.7	2712.7	2704.9
10°	2685.5	2681.5	2697.1	2673.7	2681.5	2673.7	2697.1	2697.1	2689.3	2681.5	2677.7
12.5°	2622.9	2654.1	2654.1	2650.3	2642.5	2630.7	2654.1	2669.9	2646.3	2646.3	2642.5
15°	2587.9	2595.7	2599.5	2599.5	2595.7	2603.5	2615.1	2599.5	2603.5	2583.9	2591.7
17.5°	2548.9	2533.3	2544.9	2537.1	2541.1	2548.9	2564.5	2564.5	2541.1	2537.1	2544.9
20°	2459.0	2505.9	2509.8	2486.4	2490.3	2490.3	2517.6	2494.2	2509.8	2490.3	2498.1
22.5°	2416.0	2447.3	2451.2	2420.0	2439.5	2416.0	2443.4	2408.2	2447.3	2420.0	2431.7
25°	2361.4	2357.6	2369.2	2353.6	2357.6	2357.6	2377.0	2361.4	2373.2	2357.6	2361.4
27.5°	2271.8	2303.0	2299.0	2283.4	2291.2	2287.4	2326.4	2283.4	2306.8	2287.4	2295.2
30°	2193.6	2221.0	2213.2	2197.5	2197.5	2185.8	2228.8	2217.0	2213.2	2213.2	2209.2
32.5°	2115.5	2119.5	2111.7	2115.5	2119.5	2103.9	2138.9	2123.3	2119.5	2123.3	2127.3
35°	2010.1	2010.1	2017.9	2006.3	2021.9	2021.9	2053.1	2033.5	2029.7	2017.9	2029.7
37.5°	1916.5	1904.8	1908.7	1908.7	1916.5	1924.3	1939.9	1932.1	1932.1	1920.4	1928.2
40°	1791.6	1783.8	1795.4	1795.4	1807.2	1807.2	1822.8	1815.0	1826.6	1826.6	1826.6
42.5°	1682.4	1682.4	1674.6	1686.2	1690.2	1686.2	1713.6	1709.6	1713.6	1705.8	1709.6
45°	1565.2	1565.2	1557.3	1553.5	1573.0	1569.1	1600.3	1588.6	1604.2	1596.4	1600.3
47.5°	1405.1	1424.7	1412.9	1424.7	1448.1	1452.1	1471.5	1463.7	1479.3	1467.7	1483.3
50°	1253.0	1253.0	1264.6	1280.2	1303.7	1307.6	1331.0	1346.7	1354.5	1358.3	1362.3
52.5°	1093.0	1089.0	1100.8	1120.2	1139.8	1155.4	1178.8	1202.2	1217.8	1241.2	1229.4
55°	905.5	913.3	925.1	948.5	979.7	999.2	1018.7	1050.0	1077.4	1089.0	1112.4
57.5°	745.5	737.7	745.5	776.7	811.9	827.5	854.9	886.1	925.1	948.5	956.3
60°	577.6	581.6	589.4	616.8	644.0	667.4	679.2	729.9	765.1	788.5	804.1
62.5°	425.5	433.3	441.1	464.5	491.8	511.4	530.8	573.8	605.0	628.4	644.0
65°	296.7	300.5	312.3	323.9	351.3	370.7	386.4	421.5	452.8	472.3	484.0
67.5°	183.5	187.3	195.1	210.8	230.3	245.9	261.5	284.9	312.3	331.7	335.7
70°	93.6	97.6	101.4	113.2	128.8	136.6	148.3	167.9	187.3	202.9	210.8
72.5°	31.2	31.2	35.2	43.0	50.8	58.6	62.4	82.0	97.6	105.4	109.3
75°	7.8	7.8	7.8	7.8	7.8	11.8	11.8	23.4	31.2	39.0	43.0
77.5°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	7.8	7.8
80°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C55D010 FEU4C559035 F4LC-DFSSQ-MW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	2747.9	2747.9	2747.9	2747.9	2747.9	2747.9	2747.9	2747.9	2747.9	2747.9
2.5°	2747.9	2740.1	2736.1	2740.1	2740.1	2736.1	2747.9	2763.5	2783.0	2732.3
5°	2744.0	2736.1	2744.0	2720.5	2732.3	2724.5	2740.1	2736.1	2751.8	2736.1
7.5°	2732.3	2716.7	2720.5	2708.9	2724.5	2704.9	2716.7	2740.1	2724.5	2701.1
10°	2693.3	2685.5	2712.7	2673.7	2665.9	2681.5	2712.7	2689.3	2681.5	2689.3
12.5°	2654.1	2654.1	2665.9	2634.7	2638.5	2646.3	2661.9	2646.3	2654.1	2673.7
15°	2611.3	2603.5	2622.9	2599.5	2595.7	2587.9	2603.5	2603.5	2611.3	2599.5
17.5°	2560.5	2548.9	2548.9	2541.1	2537.1	2556.7	2564.5	2568.3	2572.3	2556.7
20°	2498.1	2494.2	2505.9	2494.2	2498.1	2502.0	2502.0	2494.2	2529.3	2486.4
22.5°	2431.7	2443.4	2427.8	2420.0	2427.8	2435.6	2435.6	2439.5	2431.7	2423.9
25°	2365.4	2373.2	2377.0	2353.6	2365.4	2353.6	2381.0	2384.8	2369.2	2377.0
27.5°	2306.8	2295.2	2291.2	2275.6	2283.4	2279.6	2283.4	2283.4	2306.8	2275.6
30°	2217.0	2205.4	2209.2	2197.5	2201.4	2197.5	2201.4	2201.4	2217.0	2213.2
32.5°	2131.1	2119.5	2123.3	2111.7	2111.7	2115.5	2107.7	2107.7	2119.5	2111.7
35°	2049.1	2021.9	2025.7	2021.9	2025.7	2010.1	2010.1	2006.3	2014.1	1994.5
37.5°	1932.1	1920.4	1916.5	1912.6	1916.5	1908.7	1916.5	1904.8	1916.5	1900.9
40°	1826.6	1818.8	1822.8	1799.4	1799.4	1803.2	1795.4	1791.6	1795.4	1811.0
42.5°	1721.4	1705.8	1698.0	1690.2	1694.0	1682.4	1678.4	1670.6	1678.4	1662.8
45°	1596.4	1596.4	1592.5	1573.0	1576.9	1576.9	1561.3	1545.7	1549.5	1549.5
47.5°	1483.3	1475.5	1471.5	1452.1	1448.1	1444.3	1428.5	1416.9	1416.9	1405.1
50°	1358.3	1350.5	1338.8	1319.3	1311.5	1288.0	1276.4	1260.8	1245.2	1245.2
52.5°	1241.2	1213.8	1198.2	1167.0	1155.4	1143.6	1112.4	1100.8	1089.0	1077.4
55°	1100.8	1077.4	1046.1	1010.9	995.3	975.8	944.5	921.1	905.5	909.5
57.5°	964.1	925.1	893.9	847.1	827.5	815.7	784.5	753.3	737.7	737.7
60°	796.3	765.1	726.0	683.0	667.4	648.0	608.8	589.4	577.6	566.0
62.5°	636.2	612.8	577.6	523.0	511.4	491.8	464.5	441.1	429.3	429.3
65°	476.2	452.8	421.5	382.5	366.9	351.3	327.9	304.5	292.7	288.9
67.5°	335.7	308.3	281.1	249.9	238.1	230.3	206.9	191.3	183.5	179.5
70°	202.9	187.3	167.9	144.4	132.7	124.9	109.3	97.6	93.6	89.8
72.5°	105.4	93.6	78.0	62.4	54.6	46.8	39.0	31.2	27.4	27.4
75°	39.0	31.2	19.6	11.8	7.8	7.8	7.8	7.8	7.8	7.8
77.5°	7.8	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
80°	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0	4.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)