

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C75D010 FEU4C759030 F4LC-DFSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P#  
 Test Lab: INNOVATION CENTER  
 Issue Date: 12/13/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: FAIL-SAFE  
 Catalog Number: FLDSQ4C75D010 FEU4C759030 F4LC-DFSSQ-MW  
 Description: 4 INCH 7500 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND F4LC-DFSSQ TRIM WITH MW FINISH  
 Light Source: -  
 Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 8083.0 lumens  
 Efficiency: N/A  
 Efficacy: 99.2 lumens/watt  
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29  
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
 CIE Type: Direct

Input Watts (W): 81.5  
 Input Voltage (V):  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#  
CATALOG NUMBER: FLDSQ4C75D010 FEU4C759030 F4LC-DFSSQ-MW

### Luminous Intensity Polar Plot



TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C75D010 FEU4C759030 F4LC-DFSSQ-MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89				89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67				67
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46				46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41				41
8	65	53	45	40	64	52	45	39	51	44	39	50	44	39	49	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	33				33
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	31				31

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	365104	365104	365104
5°	359215	363884	364930
10°	362311	361262	362830
15°	355967	356497	357566
20°	347689	353203	351560
25°	346188	346188	348477
30°	336531	338927	339540
35°	326034	329215	323502
40°	310737	316820	314112
45°	294090	300708	291156
50°	259000	281576	257379
55°	209758	257684	210683
60°	153495	213665	150407
65°	93266	152147	90823
70°	36365	81898	34898
75°	3989	22070	3989
80°	3056	3056	3056
85°	0	0	0

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C75D010 FEU4C759030 F4LC-DFSSQ-MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	357.2	4.4
10°-20°	1010.7	12.5
20°-30°	1499.6	18.6
30°-40°	1737.6	21.5
40°-50°	1666.0	20.6
50°-60°	1224.9	15.2
60°-70°	529.1	6.5
70°-80°	57.1	0.7
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2867.5	35.5
0°-40°	4605.1	57.0
0°-60°	7496.1	92.7
0°-90°	8083.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8083.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3784	3784	3784	3784	3784	
5°	3709	3746	3757	3762	3768	354
15°	3564	3585	3569	3574	3580	1004
25°	3252	3246	3252	3257	3273	1489
35°	2768	2784	2795	2789	2746	1731
45°	2155	2161	2204	2171	2134	1638
55°	1247	1376	1532	1371	1252	1122
65°	408	510	666	505	398	420
75°	11	16	59	11	11	33
85°	0	0	0	0	0	1
90°	0	0	0	0	0	

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C75D010 FEU4C759030 F4LC-DFSSQ-MW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	3783.9	3783.9	3783.9	3783.9	3783.9	3783.9	3783.9	3783.9	3783.9	3783.9	3783.9
2.5°	3756.9	3799.9	3805.4	3778.4	3767.7	3751.7	3789.2	3762.4	3773.2	3762.4	3756.9
5°	3708.7	3756.9	3762.4	3762.4	3751.7	3746.2	3762.4	3756.9	3751.7	3740.9	3756.9
7.5°	3687.2	3714.0	3740.9	3708.7	3724.7	3719.4	3756.9	3740.9	3735.4	3735.4	3724.7
10°	3697.9	3692.5	3714.0	3681.7	3692.5	3681.7	3714.0	3714.0	3703.2	3692.5	3687.2
12.5°	3611.8	3654.7	3654.7	3649.5	3638.7	3622.5	3654.7	3676.4	3644.0	3644.0	3638.7
15°	3563.5	3574.3	3579.5	3579.5	3574.3	3585.0	3601.0	3579.5	3585.0	3558.0	3568.8
17.5°	3509.8	3488.3	3504.3	3493.6	3499.0	3509.8	3531.3	3531.3	3499.0	3493.6	3504.3
20°	3386.1	3450.6	3456.1	3423.8	3429.1	3429.1	3466.8	3434.6	3456.1	3429.1	3439.8
22.5°	3326.9	3369.9	3375.4	3332.4	3359.1	3326.9	3364.6	3316.2	3369.9	3332.4	3348.4
25°	3251.7	3246.4	3262.4	3240.9	3246.4	3246.4	3273.2	3251.7	3267.9	3246.4	3251.7
27.5°	3128.2	3171.2	3165.7	3144.2	3155.0	3149.7	3203.4	3144.2	3176.5	3149.7	3160.5
30°	3020.5	3058.3	3047.5	3026.0	3026.0	3009.8	3069.0	3052.8	3047.5	3047.5	3042.0
32.5°	2913.1	2918.6	2907.8	2913.1	2918.6	2897.1	2945.3	2923.8	2918.6	2923.8	2929.3
35°	2767.9	2767.9	2778.7	2762.7	2784.1	2784.1	2827.1	2800.2	2794.9	2778.7	2794.9
37.5°	2639.0	2623.0	2628.2	2628.2	2639.0	2649.7	2671.2	2660.5	2660.5	2644.5	2655.2
40°	2467.0	2456.3	2472.3	2472.3	2488.5	2488.5	2510.0	2499.3	2515.3	2515.3	2515.3
42.5°	2316.6	2316.6	2305.9	2321.9	2327.4	2321.9	2359.6	2354.1	2359.6	2348.8	2354.1
45°	2155.2	2155.2	2144.5	2139.2	2166.0	2160.7	2203.7	2187.5	2208.9	2198.2	2203.7
47.5°	1934.8	1961.8	1945.6	1961.8	1994.0	1999.5	2026.3	2015.5	2037.0	2021.0	2042.5
50°	1725.4	1725.4	1741.4	1762.9	1795.1	1800.6	1832.9	1854.3	1865.1	1870.4	1875.8
52.5°	1505.0	1499.5	1515.8	1542.5	1569.5	1591.0	1623.2	1655.4	1676.9	1709.2	1692.9
55°	1246.9	1257.6	1273.9	1306.1	1349.1	1375.8	1402.8	1445.8	1483.5	1499.5	1531.8
57.5°	1026.5	1015.8	1026.5	1069.5	1118.0	1139.4	1177.2	1220.1	1273.9	1306.1	1316.9
60°	795.4	800.9	811.6	849.3	886.8	919.1	935.3	1005.0	1053.5	1085.7	1107.2
62.5°	585.9	596.7	607.4	639.7	677.2	704.1	730.9	790.1	833.1	865.3	886.8
65°	408.5	413.8	430.0	446.0	483.8	510.5	532.0	580.5	623.5	650.4	666.4
67.5°	252.6	257.9	268.6	290.3	317.1	338.6	360.1	392.3	430.0	456.8	462.3
70°	128.9	134.4	139.7	155.9	177.4	188.2	204.2	231.1	257.9	279.4	290.3
72.5°	43.0	43.0	48.5	59.2	70.0	80.7	86.0	112.9	134.4	145.2	150.4
75°	10.7	10.7	10.7	10.7	10.7	16.2	16.2	32.2	43.0	53.7	59.2
77.5°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	10.7	10.7
80°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C75D010 FEU4C759030 F4LC-DFSSQ-MW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	3783.9	3783.9	3783.9	3783.9	3783.9	3783.9	3783.9	3783.9	3783.9	3783.9
2.5°	3783.9	3773.2	3767.7	3773.2	3773.2	3767.7	3783.9	3805.4	3832.2	3762.4
5°	3778.4	3767.7	3778.4	3746.2	3762.4	3751.7	3773.2	3767.7	3789.2	3767.7
7.5°	3762.4	3740.9	3746.2	3730.2	3751.7	3724.7	3740.9	3773.2	3751.7	3719.4
10°	3708.7	3697.9	3735.4	3681.7	3671.0	3692.5	3735.4	3703.2	3692.5	3703.2
12.5°	3654.7	3654.7	3671.0	3628.0	3633.3	3644.0	3665.5	3644.0	3654.7	3681.7
15°	3595.7	3585.0	3611.8	3579.5	3574.3	3563.5	3585.0	3585.0	3595.7	3579.5
17.5°	3525.8	3509.8	3509.8	3499.0	3493.6	3520.5	3531.3	3536.5	3542.0	3520.5
20°	3439.8	3434.6	3450.6	3434.6	3439.8	3445.3	3445.3	3434.6	3482.8	3423.8
22.5°	3348.4	3364.6	3343.1	3332.4	3343.1	3353.9	3353.9	3359.1	3348.4	3337.6
25°	3257.2	3267.9	3273.2	3240.9	3257.2	3240.9	3278.7	3283.9	3262.4	3273.2
27.5°	3176.5	3160.5	3155.0	3133.5	3144.2	3139.0	3144.2	3144.2	3176.5	3133.5
30°	3052.8	3036.8	3042.0	3026.0	3031.3	3026.0	3031.3	3031.3	3052.8	3047.5
32.5°	2934.6	2918.6	2923.8	2907.8	2907.8	2913.1	2902.3	2902.3	2918.6	2907.8
35°	2821.7	2784.1	2789.4	2784.1	2789.4	2767.9	2767.9	2762.7	2773.4	2746.4
37.5°	2660.5	2644.5	2639.0	2633.7	2639.0	2628.2	2639.0	2623.0	2639.0	2617.5
40°	2515.3	2504.6	2510.0	2477.8	2477.8	2483.1	2472.3	2467.0	2472.3	2493.8
42.5°	2370.3	2348.8	2338.1	2327.4	2332.6	2316.6	2311.1	2300.4	2311.1	2289.6
45°	2198.2	2198.2	2192.9	2166.0	2171.4	2171.4	2149.9	2128.5	2133.7	2133.7
47.5°	2042.5	2031.7	2026.3	1999.5	1994.0	1988.8	1967.1	1951.1	1951.1	1934.8
50°	1870.4	1859.6	1843.6	1816.6	1805.9	1773.6	1757.6	1736.1	1714.6	1714.6
52.5°	1709.2	1671.5	1650.0	1607.0	1591.0	1574.7	1531.8	1515.8	1499.5	1483.5
55°	1515.8	1483.5	1440.5	1392.1	1370.6	1343.6	1300.6	1268.4	1246.9	1252.4
57.5°	1327.6	1273.9	1230.9	1166.4	1139.4	1123.2	1080.2	1037.3	1015.8	1015.8
60°	1096.5	1053.5	999.8	940.6	919.1	892.3	838.4	811.6	795.4	779.4
62.5°	876.1	843.8	795.4	720.2	704.1	677.2	639.7	607.4	591.2	591.2
65°	655.7	623.5	580.5	526.7	505.3	483.8	451.5	419.3	403.1	397.8
67.5°	462.3	424.6	387.0	344.1	327.8	317.1	284.9	263.4	252.6	247.1
70°	279.4	257.9	231.1	198.9	182.7	171.9	150.4	134.4	128.9	123.7
72.5°	145.2	128.9	107.5	86.0	75.2	64.5	53.7	43.0	37.7	37.7
75°	53.7	43.0	27.0	16.2	10.7	10.7	10.7	10.7	10.7	10.7
77.5°	10.7	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
80°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.5
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)