

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C15D010 FEU4C159050 F4LC-CSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C15D010 FEU4C159050 F4LC-CSSQ-MW
 Description: 4 INCH 1500 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND F4LC-CSSQ TRIM WITH MW FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 1570.0 lumens
 Efficiency: N/A
 Efficacy: 99.4 lumens/watt
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 15.8
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C15D010 FEU4C159050 F4LC-CSSQ-MW

Luminous Intensity Polar Plot



TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C15D010 FEU4C159050 F4LC-CSSQ-MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96		97	95	94		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	74	71		77	73	69	67
4	88	77	70	64	86	76	69	63	74	67	63		71	66	62		69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55		65	59	54		63	58	54	52
6	75	63	55	49	73	62	55	49	61	54	49		59	53	48		57	52	48	46
7	70	58	50	44	68	57	49	44	55	49	44		54	48	43		53	47	43	41
8	65	53	45	40	64	52	45	39	51	44	39		50	44	39		49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36		46	40	35		45	39	35	33
10	57	45	38	33	56	44	37	33	44	37	32		43	37	32		42	36	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	70919	70919	70919
5°	69776	70677	70880
10°	70377	70171	70475
15°	69146	69246	69455
20°	67534	68601	68283
25°	67242	67242	67690
30°	65368	65836	65947
35°	63325	63949	62842
40°	60359	61543	61014
45°	57120	58403	56547
50°	50302	54700	49987
55°	40744	50046	40929
60°	29815	41510	29217
65°	18128	29544	17649
70°	7053	15911	6771
75°	783	4287	783
80°	611	611	611
85°	0	0	0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C15D010 FEU4C159050 F4LC-CSSQ-MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.4	4.4
10°-20°	196.3	12.5
20°-30°	291.3	18.6
30°-40°	337.5	21.5
40°-50°	323.6	20.6
50°-60°	237.9	15.2
60°-70°	102.8	6.5
70°-80°	11.1	0.7
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	557.0	35.5
0°-40°	894.5	57.0
0°-60°	1456.0	92.7
0°-90°	1570.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1570.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	735	735	735	735	735	
5°	720	728	730	731	732	69
15°	692	696	693	694	695	195
25°	632	631	632	633	636	289
35°	538	541	543	542	534	336
45°	419	420	428	422	414	318
55°	242	267	298	266	243	218
65°	79	99	129	98	77	82
75°	2	3	12	2	2	6
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C15D010 FEU4C159050 F4LC-CSSQ-MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	735.0	735.0	735.0	735.0	735.0	735.0	735.0	735.0	735.0	735.0	735.0
2.5°	729.7	738.1	739.1	733.9	731.8	728.7	736.0	730.8	732.9	730.8	729.7
5°	720.4	729.7	730.8	730.8	728.7	727.6	730.8	729.7	728.7	726.6	729.7
7.5°	716.2	721.4	726.6	720.4	723.5	722.4	729.7	726.6	725.6	725.6	723.5
10°	718.3	717.2	721.4	715.1	717.2	715.1	721.4	721.4	719.3	717.2	716.2
12.5°	701.5	709.9	709.9	708.9	706.8	703.6	709.9	714.1	707.8	707.8	706.8
15°	692.2	694.2	695.3	695.3	694.2	696.3	699.4	695.3	696.3	691.1	693.2
17.5°	681.7	677.5	680.7	678.6	679.6	681.7	685.9	685.9	679.6	678.6	680.7
20°	657.7	670.2	671.3	665.0	666.0	666.0	673.4	667.1	671.3	666.0	668.1
22.5°	646.2	654.5	655.6	647.3	652.5	646.2	653.5	644.1	654.5	647.3	650.4
25°	631.6	630.6	633.7	629.5	630.6	630.6	635.8	631.6	634.7	630.6	631.6
27.5°	607.6	616.0	614.9	610.7	612.8	611.8	622.2	610.7	617.0	611.8	613.9
30°	586.7	594.0	591.9	587.8	587.8	584.6	596.1	593.0	591.9	591.9	590.9
32.5°	565.8	566.9	564.8	565.8	566.9	562.7	572.1	567.9	566.9	567.9	569.0
35°	537.6	537.6	539.7	536.6	540.8	540.8	549.1	543.9	542.9	539.7	542.9
37.5°	512.6	509.5	510.5	510.5	512.6	514.7	518.8	516.8	516.8	513.6	515.7
40°	479.2	477.1	480.2	480.2	483.4	483.4	487.5	485.4	488.6	488.6	488.6
42.5°	450.0	450.0	447.9	451.0	452.1	451.0	458.3	457.3	458.3	456.2	457.3
45°	418.6	418.6	416.5	415.5	420.7	419.7	428.0	424.9	429.1	427.0	428.0
47.5°	375.8	381.0	377.9	381.0	387.3	388.4	393.6	391.5	395.7	392.5	396.7
50°	335.1	335.1	338.2	342.4	348.7	349.7	356.0	360.2	362.3	363.3	364.4
52.5°	292.3	291.3	294.4	299.6	304.8	309.0	315.3	321.5	325.7	332.0	328.8
55°	242.2	244.3	247.4	253.7	262.0	267.2	272.5	280.8	288.2	291.3	297.5
57.5°	199.4	197.3	199.4	207.7	217.1	221.3	228.6	237.0	247.4	253.7	255.8
60°	154.5	155.6	157.6	165.0	172.3	178.5	181.7	195.2	204.6	210.9	215.1
62.5°	113.8	115.9	118.0	124.2	131.5	136.8	142.0	153.5	161.8	168.1	172.3
65°	79.4	80.4	83.5	86.6	94.0	99.2	103.3	112.7	121.1	126.3	129.4
67.5°	49.1	50.1	52.2	56.4	61.6	65.8	69.9	76.2	83.5	88.7	89.8
70°	25.0	26.1	27.1	30.3	34.5	36.5	39.7	44.9	50.1	54.3	56.4
72.5°	8.3	8.3	9.4	11.5	13.6	15.7	16.7	21.9	26.1	28.2	29.2
75°	2.1	2.1	2.1	2.1	2.1	3.2	3.2	6.3	8.3	10.4	11.5
77.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	2.1	2.1
80°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C15D010 FEU4C159050 F4LC-CSSQ-MW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	735.0	735.0	735.0	735.0	735.0	735.0	735.0	735.0	735.0	735.0
2.5°	735.0	732.9	731.8	732.9	732.9	731.8	735.0	739.1	744.3	730.8
5°	733.9	731.8	733.9	727.6	730.8	728.7	732.9	731.8	736.0	731.8
7.5°	730.8	726.6	727.6	724.5	728.7	723.5	726.6	732.9	728.7	722.4
10°	720.4	718.3	725.6	715.1	713.0	717.2	725.6	719.3	717.2	719.3
12.5°	709.9	709.9	713.0	704.7	705.7	707.8	712.0	707.8	709.9	715.1
15°	698.4	696.3	701.5	695.3	694.2	692.2	696.3	696.3	698.4	695.3
17.5°	684.8	681.7	681.7	679.6	678.6	683.8	685.9	686.9	688.0	683.8
20°	668.1	667.1	670.2	667.1	668.1	669.2	669.2	667.1	676.5	665.0
22.5°	650.4	653.5	649.4	647.3	649.4	651.4	651.4	652.5	650.4	648.3
25°	632.7	634.7	635.8	629.5	632.7	629.5	636.8	637.9	633.7	635.8
27.5°	617.0	613.9	612.8	608.6	610.7	609.7	610.7	610.7	617.0	608.6
30°	593.0	589.8	590.9	587.8	588.8	587.8	588.8	588.8	593.0	591.9
32.5°	570.0	566.9	567.9	564.8	564.8	565.8	563.7	563.7	566.9	564.8
35°	548.1	540.8	541.8	540.8	541.8	537.6	537.6	536.6	538.7	533.5
37.5°	516.8	513.6	512.6	511.6	512.6	510.5	512.6	509.5	512.6	508.4
40°	488.6	486.5	487.5	481.3	481.3	482.3	480.2	479.2	480.2	484.4
42.5°	460.4	456.2	454.1	452.1	453.1	450.0	448.9	446.8	448.9	444.7
45°	427.0	427.0	425.9	420.7	421.8	421.8	417.6	413.4	414.4	414.4
47.5°	396.7	394.6	393.6	388.4	387.3	386.3	382.1	379.0	379.0	375.8
50°	363.3	361.2	358.1	352.9	350.8	344.5	341.4	337.2	333.0	333.0
52.5°	332.0	324.7	320.5	312.1	309.0	305.9	297.5	294.4	291.3	288.2
55°	294.4	288.2	279.8	270.4	266.2	261.0	252.6	246.4	242.2	243.3
57.5°	257.9	247.4	239.1	226.6	221.3	218.2	209.8	201.5	197.3	197.3
60°	213.0	204.6	194.2	182.7	178.5	173.3	162.8	157.6	154.5	151.4
62.5°	170.2	163.9	154.5	139.9	136.8	131.5	124.2	118.0	114.8	114.8
65°	127.4	121.1	112.7	102.3	98.1	94.0	87.7	81.4	78.3	77.3
67.5°	89.8	82.5	75.2	66.8	63.7	61.6	55.3	51.2	49.1	48.0
70°	54.3	50.1	44.9	38.6	35.5	33.4	29.2	26.1	25.0	24.0
72.5°	28.2	25.0	20.9	16.7	14.6	12.5	10.4	8.3	7.3	7.3
75°	10.4	8.3	5.2	3.2	2.1	2.1	2.1	2.1	2.1	2.1
77.5°	2.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
80°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)