

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C08D010 FEU4C089030 F4LC-CSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.



**Test Information**

Test Method: LM-79-08  
 Report Number: P#  
 Test Lab: INNOVATION CENTER  
 Issue Date: 12/13/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: FAIL-SAFE  
 Catalog Number: FLDSQ4C08D010 FEU4C089030 F4LC-CSSQ-MW  
 Description: 4 INCH 800 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND F4LC-CSSQ TRIM WITH MW FINISH  
 Light Source: -  
 Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 863.0 lumens  
 Efficiency: N/A  
 Efficacy: 87.4 lumens/watt  
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29  
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
 CIE Type: Direct

Input Watts (W): 9.87  
 Input Voltage (V):  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#  
CATALOG NUMBER: FLDSQ4C08D010 FEU4C089030 F4LC-CSSQ-MW

### Luminous Intensity Polar Plot



TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C08D010 FEU4C089030 F4LC-CSSQ-MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96		97	95	94		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	74	71		77	73	69	67
4	88	77	70	64	86	76	69	63	74	67	63		71	66	62		69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55		65	59	54		63	58	54	52
6	75	63	55	49	73	62	55	49	61	54	49		59	53	48		57	52	48	46
7	70	58	50	44	68	57	49	44	55	49	44		54	48	43		53	47	43	41
8	65	53	45	40	64	52	45	39	51	44	39		50	44	39		49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36		46	40	35		45	39	35	33
10	57	45	38	33	56	44	37	33	44	37	32		43	37	32		42	36	32	31

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	38982	38982	38982
5°	38356	38850	38966
10°	38681	38574	38740
15°	38009	38059	38179
20°	37119	37715	37540
25°	36964	36964	37209
30°	35932	36188	36255
35°	34807	35149	34536
40°	33177	33832	33542
45°	31399	32108	31085
50°	27650	30067	27485
55°	22391	27505	22491
60°	16384	22810	16056
65°	9954	16256	9703
70°	3893	8746	3724
75°	410	2349	410
80°	333	333	333
85°	0	0	0

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C08D010 FEU4C089030 F4LC-CSSQ-MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.1	4.4
10°-20°	107.9	12.5
20°-30°	160.1	18.6
30°-40°	185.5	21.5
40°-50°	177.9	20.6
50°-60°	130.8	15.2
60°-70°	56.5	6.5
70°-80°	6.1	0.7
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.2	35.5
0°-40°	491.7	57.0
0°-60°	800.3	92.7
0°-90°	863.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	863.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	404	404	404	404	404	
5°	396	400	401	402	402	38
15°	380	383	381	382	382	107
25°	347	347	347	348	350	159
35°	296	297	298	298	293	185
45°	230	231	235	232	228	175
55°	133	147	164	146	134	120
65°	44	54	71	54	42	45
75°	1	2	6	1	1	4
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P#

CATALOG NUMBER: FLDSQ4C08D010 FEU4C089030 F4LC-CSSQ-MW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	404.0	404.0	404.0	404.0	404.0	404.0	404.0	404.0	404.0	404.0	404.0
2.5°	401.1	405.7	406.3	403.4	402.3	400.6	404.6	401.7	402.8	401.7	401.1
5°	396.0	401.1	401.7	401.7	400.6	400.0	401.7	401.1	400.6	399.4	401.1
7.5°	393.7	396.5	399.4	396.0	397.7	397.1	401.1	399.4	398.8	398.8	397.7
10°	394.8	394.2	396.5	393.1	394.2	393.1	396.5	396.5	395.4	394.2	393.7
12.5°	385.6	390.2	390.2	389.6	388.5	386.8	390.2	392.5	389.1	389.1	388.5
15°	380.5	381.6	382.2	382.2	381.6	382.8	384.5	382.2	382.8	379.9	381.0
17.5°	374.7	372.4	374.1	373.0	373.6	374.7	377.0	377.0	373.6	373.0	374.1
20°	361.5	368.4	369.0	365.6	366.1	366.1	370.1	366.7	369.0	366.1	367.3
22.5°	355.2	359.8	360.4	355.8	358.6	355.2	359.2	354.1	359.8	355.8	357.5
25°	347.2	346.6	348.3	346.0	346.6	346.6	349.5	347.2	348.9	346.6	347.2
27.5°	334.0	338.6	338.0	335.7	336.8	336.3	342.0	335.7	339.1	336.3	337.4
30°	322.5	326.5	325.4	323.1	323.1	321.3	327.7	325.9	325.4	325.4	324.8
32.5°	311.0	311.6	310.5	311.0	311.6	309.3	314.5	312.2	311.6	312.2	312.8
35°	295.5	295.5	296.7	295.0	297.3	297.3	301.8	299.0	298.4	296.7	298.4
37.5°	281.8	280.0	280.6	280.6	281.8	282.9	285.2	284.1	284.1	282.3	283.5
40°	263.4	262.3	264.0	264.0	265.7	265.7	268.0	266.8	268.6	268.6	268.6
42.5°	247.3	247.3	246.2	247.9	248.5	247.9	251.9	251.3	251.9	250.8	251.3
45°	230.1	230.1	229.0	228.4	231.3	230.7	235.3	233.5	235.8	234.7	235.3
47.5°	206.6	209.5	207.7	209.5	212.9	213.5	216.3	215.2	217.5	215.8	218.1
50°	184.2	184.2	185.9	188.2	191.7	192.2	195.7	198.0	199.1	199.7	200.3
52.5°	160.7	160.1	161.8	164.7	167.6	169.9	173.3	176.7	179.0	182.5	180.8
55°	133.1	134.3	136.0	139.4	144.0	146.9	149.8	154.4	158.4	160.1	163.5
57.5°	109.6	108.5	109.6	114.2	119.4	121.7	125.7	130.3	136.0	139.4	140.6
60°	84.9	85.5	86.7	90.7	94.7	98.1	99.9	107.3	112.5	115.9	118.2
62.5°	62.6	63.7	64.9	68.3	72.3	75.2	78.0	84.4	88.9	92.4	94.7
65°	43.6	44.2	45.9	47.6	51.6	54.5	56.8	62.0	66.6	69.4	71.2
67.5°	27.0	27.5	28.7	31.0	33.9	36.2	38.4	41.9	45.9	48.8	49.4
70°	13.8	14.4	14.9	16.6	18.9	20.1	21.8	24.7	27.5	29.8	31.0
72.5°	4.6	4.6	5.2	6.3	7.5	8.6	9.2	12.1	14.4	15.5	16.1
75°	1.1	1.1	1.1	1.1	1.1	1.7	1.7	3.4	4.6	5.7	6.3
77.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	1.1	1.1
80°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C08D010 FEU4C089030 F4LC-CSSQ-MW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	404.0	404.0	404.0	404.0	404.0	404.0	404.0	404.0	404.0	404.0
2.5°	404.0	402.8	402.3	402.8	402.8	402.3	404.0	406.3	409.1	401.7
5°	403.4	402.3	403.4	400.0	401.7	400.6	402.8	402.3	404.6	402.3
7.5°	401.7	399.4	400.0	398.3	400.6	397.7	399.4	402.8	400.6	397.1
10°	396.0	394.8	398.8	393.1	391.9	394.2	398.8	395.4	394.2	395.4
12.5°	390.2	390.2	391.9	387.4	387.9	389.1	391.4	389.1	390.2	393.1
15°	383.9	382.8	385.6	382.2	381.6	380.5	382.8	382.8	383.9	382.2
17.5°	376.4	374.7	374.7	373.6	373.0	375.9	377.0	377.6	378.2	375.9
20°	367.3	366.7	368.4	366.7	367.3	367.8	367.8	366.7	371.9	365.6
22.5°	357.5	359.2	356.9	355.8	356.9	358.1	358.1	358.6	357.5	356.4
25°	347.8	348.9	349.5	346.0	347.8	346.0	350.1	350.6	348.3	349.5
27.5°	339.1	337.4	336.8	334.6	335.7	335.1	335.7	335.7	339.1	334.6
30°	325.9	324.2	324.8	323.1	323.6	323.1	323.6	323.6	325.9	325.4
32.5°	313.3	311.6	312.2	310.5	310.5	311.0	309.9	309.9	311.6	310.5
35°	301.3	297.3	297.8	297.3	297.8	295.5	295.5	295.0	296.1	293.2
37.5°	284.1	282.3	281.8	281.2	281.8	280.6	281.8	280.0	281.8	279.5
40°	268.6	267.4	268.0	264.5	264.5	265.1	264.0	263.4	264.0	266.3
42.5°	253.1	250.8	249.6	248.5	249.0	247.3	246.8	245.6	246.8	244.5
45°	234.7	234.7	234.1	231.3	231.8	231.8	229.5	227.2	227.8	227.8
47.5°	218.1	216.9	216.3	213.5	212.9	212.3	210.0	208.3	208.3	206.6
50°	199.7	198.5	196.8	194.0	192.8	189.4	187.7	185.4	183.1	183.1
52.5°	182.5	178.5	176.2	171.6	169.9	168.1	163.5	161.8	160.1	158.4
55°	161.8	158.4	153.8	148.6	146.3	143.5	138.9	135.4	133.1	133.7
57.5°	141.7	136.0	131.4	124.5	121.7	119.9	115.3	110.7	108.5	108.5
60°	117.1	112.5	106.7	100.4	98.1	95.3	89.5	86.7	84.9	83.2
62.5°	93.5	90.1	84.9	76.9	75.2	72.3	68.3	64.9	63.1	63.1
65°	70.0	66.6	62.0	56.2	53.9	51.6	48.2	44.8	43.0	42.5
67.5°	49.4	45.3	41.3	36.7	35.0	33.9	30.4	28.1	27.0	26.4
70°	29.8	27.5	24.7	21.2	19.5	18.4	16.1	14.4	13.8	13.2
72.5°	15.5	13.8	11.5	9.2	8.0	6.9	5.7	4.6	4.0	4.0
75°	5.7	4.6	2.9	1.7	1.1	1.1	1.1	1.1	1.1	1.1
77.5°	1.1	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
80°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)