

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C08D010 FEU4C089035 F4LC-SQ-WH**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C08D010 FEU4C089035 F4LC-SQ-WH
 Description: 4 INCH 800 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND F4LC-SQW TRIM WITH H FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 590.0 lumens
 Efficiency: N/A
 Efficacy: 59.6 lumens/watt
 Spacing Criteria (0/90/45): 0.93 / 0.93 / 0.94
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 9.9
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C08D010 FEU4C089035 F4LC-SQ-WH

Luminous Intensity Polar Plot





TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C08D010 FEU4C089035 F4LC-SQ-WH

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92
2	107	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	101	93	88	84	98	92	87	83	89	85	82	87	83	80	85	82	79	77
4	95	87	80	76	93	85	80	75	83	78	74	81	77	74	79	76	73	71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65
6	85	75	68	64	83	74	68	63	72	67	63	71	66	63	70	65	62	61
7	80	70	63	59	79	69	63	59	68	62	58	67	62	58	65	61	58	56
8	76	65	59	55	74	65	59	54	64	58	54	63	58	54	62	57	54	52
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49
10	68	58	52	48	67	57	51	47	57	51	47	56	51	47	55	50	47	46

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	53783	53783	53783
5°	53291	53262	53281
10°	51928	51722	51928
15°	50676	49767	50735
20°	48055	47870	48137
25°	39413	44970	39626
30°	28110	37157	28144
35°	20272	24618	20331
40°	16248	14309	16248
45°	12404	8351	12308
50°	8181	5329	8151
55°	5501	3583	5434
60°	3705	2451	3724
65°	2534	1735	2489
70°	1693	1241	1693
75°	1118	932	1118
80°	778	667	778
85°	554	554	554

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C08D010 FEU4C089035 F4LC-SQ-WH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.8	8.8
10°-20°	141.3	23.9
20°-30°	176.6	29.9
30°-40°	118.8	20.1
40°-50°	62.7	10.6
50°-60°	25.5	4.3
60°-70°	9.5	1.6
70°-80°	3.0	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	369.8	62.7
0°-40°	488.6	82.8
0°-60°	576.8	97.8
0°-90°	590.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	590.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	557	557	557	557	557	
5°	550	550	550	550	550	52
15°	507	503	498	503	508	142
25°	370	391	422	392	372	167
35°	172	181	209	181	173	111
45°	91	86	61	86	90	70
55°	33	27	21	27	32	30
65°	11	9	8	9	11	11
75°	3	3	2	3	3	3
85°	0	0	0	0	0	1
90°	0	0	0	0	0	

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C08D010 FEU4C089035 F4LC-SQ-WH

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	557.4	557.4	557.4	557.4	557.4
2.5°	556.0	555.7	555.5	555.5	555.7
5°	550.2	549.7	549.9	549.9	550.1
7.5°	540.9	540.7	540.2	540.9	540.9
10°	530.0	529.1	527.9	529.3	530.0
12.5°	518.8	516.1	514.0	516.1	518.8
15°	507.3	503.1	498.2	502.9	507.9
17.5°	492.4	488.2	482.7	489.1	493.8
20°	468.0	468.3	466.2	468.0	468.8
22.5°	428.8	436.7	447.7	436.8	427.5
25°	370.2	391.0	422.4	391.7	372.2
27.5°	307.5	333.8	385.3	335.4	309.4
30°	252.3	275.6	333.5	277.2	252.6
32.5°	204.3	221.7	271.1	223.8	206.6
35°	172.1	180.7	209.0	181.1	172.6
37.5°	147.5	147.5	155.2	148.2	146.8
40°	129.0	123.4	113.6	123.2	129.0
42.5°	111.8	103.4	82.4	103.0	112.2
45°	90.9	86.3	61.2	86.0	90.2
47.5°	69.8	66.6	46.1	66.3	70.3
50°	54.5	49.6	35.5	49.2	54.3
52.5°	41.8	36.6	27.4	36.6	41.5
55°	32.7	27.4	21.3	27.4	32.3
57.5°	25.1	20.9	16.2	20.6	25.0
60°	19.2	15.6	12.7	15.6	19.3
62.5°	14.6	12.0	9.7	11.8	14.4
65°	11.1	9.0	7.6	9.0	10.9
67.5°	8.1	6.7	5.8	6.7	8.3
70°	6.0	5.1	4.4	4.9	6.0
72.5°	4.4	3.7	3.3	3.7	4.4
75°	3.0	2.6	2.5	2.6	3.0
77.5°	2.1	1.9	1.8	1.9	2.1
80°	1.4	1.2	1.2	1.4	1.4
82.5°	0.9	0.9	0.9	0.9	0.9
85°	0.5	0.5	0.5	0.5	0.5
87.5°	0.4	0.4	0.4	0.4	0.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)