

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C20D010 FEU4C209027 F4LC-CSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.



Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C20D010 FEU4C209027 F4LC-CSSQ-MW
 Description: 4 INCH 2000 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 2700K, 90CRI LEDS AND F4LC-CSSQ TRIM WITH MW FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 1880.0 lumens
 Efficiency: N/A
 Efficacy: 86.2 lumens/watt
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 21.8
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C20D010 FEU4C209027 F4LC-CSSQ-MW

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: FLDSQ4C20D010 FEU4C209027 F4LC-CSSQ-MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89				89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67				67
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46				46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41				41
8	65	53	45	40	64	52	45	39	51	44	39	50	44	39	49	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	33				33
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	31				31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	84920	84920	84920
5°	83549	84634	84876
10°	84270	84025	84388
15°	82791	82921	83171
20°	80872	82155	81765
25°	80519	80519	81051
30°	78270	78827	78972
35°	75834	76576	75245
40°	72274	73685	73055
45°	68405	69934	67723
50°	60239	65493	59864
55°	48785	59938	49003
60°	35701	49692	34987
65°	21690	35388	21119
70°	8463	19043	8125
75°	932	5145	932
80°	722	722	722
85°	0	0	0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C20D010 FEU4C209027 F4LC-CSSQ-MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	83.1	4.4
10°-20°	235.1	12.5
20°-30°	348.8	18.6
30°-40°	404.2	21.5
40°-50°	387.5	20.6
50°-60°	284.9	15.2
60°-70°	123.1	6.5
70°-80°	13.3	0.7
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	666.9	35.5
0°-40°	1071.1	57.0
0°-60°	1743.5	92.7
0°-90°	1880.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1880.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	880	880	880	880	880	
5°	863	871	874	875	876	82
15°	829	834	830	831	833	234
25°	756	755	756	758	761	346
35°	644	648	650	649	639	403
45°	501	502	512	505	496	381
55°	290	320	356	319	291	261
65°	95	119	155	118	92	98
75°	2	4	14	2	2	8
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P#

CATALOG NUMBER: FLDSQ4C20D010 FEU4C209027 F4LC-CSSQ-MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	880.1	880.1	880.1	880.1	880.1	880.1	880.1	880.1	880.1	880.1	880.1
2.5°	873.8	883.8	885.1	878.8	876.3	872.6	881.3	875.1	877.6	875.1	873.8
5°	862.6	873.8	875.1	875.1	872.6	871.3	875.1	873.8	872.6	870.1	873.8
7.5°	857.6	863.8	870.1	862.6	866.3	865.1	873.8	870.1	868.8	868.8	866.3
10°	860.1	858.8	863.8	856.3	858.8	856.3	863.8	863.8	861.3	858.8	857.6
12.5°	840.0	850.0	850.0	848.8	846.3	842.5	850.0	855.1	847.5	847.5	846.3
15°	828.8	831.3	832.6	832.6	831.3	833.8	837.5	832.6	833.8	827.6	830.1
17.5°	816.3	811.3	815.1	812.6	813.8	816.3	821.3	821.3	813.8	812.6	815.1
20°	787.6	802.6	803.8	796.3	797.6	797.6	806.3	798.8	803.8	797.6	800.1
22.5°	773.8	783.8	785.1	775.1	781.3	773.8	782.6	771.3	783.8	775.1	778.8
25°	756.3	755.1	758.8	753.8	755.1	755.1	761.3	756.3	760.1	755.1	756.3
27.5°	727.6	737.6	736.3	731.3	733.8	732.6	745.1	731.3	738.8	732.6	735.1
30°	702.5	711.3	708.8	703.8	703.8	700.0	713.8	710.0	708.8	708.8	707.5
32.5°	677.5	678.8	676.3	677.5	678.8	673.8	685.0	680.0	678.8	680.0	681.3
35°	643.8	643.8	646.3	642.6	647.6	647.6	657.6	651.3	650.1	646.3	650.1
37.5°	613.8	610.1	611.3	611.3	613.8	616.3	621.3	618.8	618.8	615.1	617.6
40°	573.8	571.3	575.0	575.0	578.8	578.8	583.8	581.3	585.0	585.0	585.0
42.5°	538.8	538.8	536.3	540.0	541.3	540.0	548.8	547.5	548.8	546.3	547.5
45°	501.3	501.3	498.8	497.6	503.8	502.5	512.5	508.8	513.8	511.3	512.5
47.5°	450.0	456.3	452.5	456.3	463.8	465.1	471.3	468.8	473.8	470.1	475.1
50°	401.3	401.3	405.0	410.0	417.5	418.8	426.3	431.3	433.8	435.0	436.3
52.5°	350.0	348.8	352.5	358.8	365.0	370.0	377.5	385.0	390.0	397.5	393.8
55°	290.0	292.5	296.3	303.8	313.8	320.0	326.3	336.3	345.0	348.8	356.3
57.5°	238.8	236.3	238.8	248.8	260.0	265.0	273.8	283.8	296.3	303.8	306.3
60°	185.0	186.3	188.8	197.5	206.3	213.8	217.5	233.8	245.0	252.5	257.5
62.5°	136.3	138.8	141.3	148.8	157.5	163.8	170.0	183.8	193.8	201.3	206.3
65°	95.0	96.2	100.0	103.7	112.5	118.7	123.7	135.0	145.0	151.3	155.0
67.5°	58.8	60.0	62.5	67.5	73.8	78.8	83.8	91.2	100.0	106.2	107.5
70°	30.0	31.3	32.5	36.3	41.3	43.8	47.5	53.8	60.0	65.0	67.5
72.5°	10.0	10.0	11.3	13.8	16.3	18.8	20.0	26.3	31.3	33.8	35.0
75°	2.5	2.5	2.5	2.5	2.5	3.8	3.8	7.5	10.0	12.5	13.8
77.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	2.5	2.5
80°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C20D010 FEU4C209027 F4LC-CSSQ-MW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	880.1	880.1	880.1	880.1	880.1	880.1	880.1	880.1	880.1	880.1
2.5°	880.1	877.6	876.3	877.6	877.6	876.3	880.1	885.1	891.3	875.1
5°	878.8	876.3	878.8	871.3	875.1	872.6	877.6	876.3	881.3	876.3
7.5°	875.1	870.1	871.3	867.6	872.6	866.3	870.1	877.6	872.6	865.1
10°	862.6	860.1	868.8	856.3	853.8	858.8	868.8	861.3	858.8	861.3
12.5°	850.0	850.0	853.8	843.8	845.0	847.5	852.5	847.5	850.0	856.3
15°	836.3	833.8	840.0	832.6	831.3	828.8	833.8	833.8	836.3	832.6
17.5°	820.1	816.3	816.3	813.8	812.6	818.8	821.3	822.6	823.8	818.8
20°	800.1	798.8	802.6	798.8	800.1	801.3	801.3	798.8	810.1	796.3
22.5°	778.8	782.6	777.6	775.1	777.6	780.1	780.1	781.3	778.8	776.3
25°	757.6	760.1	761.3	753.8	757.6	753.8	762.6	763.8	758.8	761.3
27.5°	738.8	735.1	733.8	728.8	731.3	730.1	731.3	731.3	738.8	728.8
30°	710.0	706.3	707.5	703.8	705.0	703.8	705.0	705.0	710.0	708.8
32.5°	682.5	678.8	680.0	676.3	676.3	677.5	675.0	675.0	678.8	676.3
35°	656.3	647.6	648.8	647.6	648.8	643.8	643.8	642.6	645.1	638.8
37.5°	618.8	615.1	613.8	612.6	613.8	611.3	613.8	610.1	613.8	608.8
40°	585.0	582.5	583.8	576.3	576.3	577.5	575.0	573.8	575.0	580.0
42.5°	551.3	546.3	543.8	541.3	542.5	538.8	537.5	535.0	537.5	532.5
45°	511.3	511.3	510.0	503.8	505.0	505.0	500.1	495.1	496.3	496.3
47.5°	475.1	472.6	471.3	465.1	463.8	462.6	457.5	453.8	453.8	450.0
50°	435.0	432.5	428.8	422.5	420.0	412.5	408.8	403.8	398.8	398.8
52.5°	397.5	388.8	383.8	373.8	370.0	366.3	356.3	352.5	348.8	345.0
55°	352.5	345.0	335.0	323.8	318.8	312.5	302.5	295.0	290.0	291.3
57.5°	308.8	296.3	286.3	271.3	265.0	261.2	251.3	241.3	236.3	236.3
60°	255.0	245.0	232.5	218.8	213.8	207.5	195.0	188.8	185.0	181.3
62.5°	203.8	196.3	185.0	167.5	163.8	157.5	148.8	141.3	137.5	137.5
65°	152.5	145.0	135.0	122.5	117.5	112.5	105.0	97.5	93.7	92.5
67.5°	107.5	98.7	90.0	80.0	76.3	73.8	66.3	61.3	58.8	57.5
70°	65.0	60.0	53.8	46.3	42.5	40.0	35.0	31.3	30.0	28.8
72.5°	33.8	30.0	25.0	20.0	17.5	15.0	12.5	10.0	8.8	8.8
75°	12.5	10.0	6.3	3.8	2.5	2.5	2.5	2.5	2.5	2.5
77.5°	2.5	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
80°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)