

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C20D010 FEU4C209035 F4LC-CSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.



**Test Information**

Test Method: LM-79-08  
 Report Number: P#  
 Test Lab: INNOVATION CENTER  
 Issue Date: 12/13/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: FAIL-SAFE  
 Catalog Number: FLDSQ4C20D010 FEU4C209035 F4LC-CSSQ-MW  
 Description: 4 INCH 2000 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 3500K, 90CRI LEDS AND F4LC-CSSQ TRIM WITH MW FINISH  
 Light Source: -  
 Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 1982.0 lumens  
 Efficiency: N/A  
 Efficacy: 90.9 lumens/watt  
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29  
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
 CIE Type: Direct

Input Watts (W): 21.8  
 Input Voltage (V):  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#  
CATALOG NUMBER: FLDSQ4C20D010 FEU4C209035 F4LC-CSSQ-MW

### Luminous Intensity Polar Plot



TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C20D010 FEU4C209035 F4LC-CSSQ-MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96		97	95	94		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	74	71		77	73	69	67
4	88	77	70	64	86	76	69	63	74	67	63		71	66	62		69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55		65	59	54		63	58	54	52
6	75	63	55	49	73	62	55	49	61	54	49		59	53	48		57	52	48	46
7	70	58	50	44	68	57	49	44	55	49	44		54	48	43		53	47	43	41
8	65	53	45	40	64	52	45	39	51	44	39		50	44	39		49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36		46	40	35		45	39	35	34
10	57	45	38	33	56	44	37	33	44	37	32		43	37	32		42	36	32	31

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	89522	89522	89522
5°	88082	89225	89487
10°	88846	88581	88963
15°	87286	87416	87676
20°	85256	86612	86201
25°	84884	84884	85448
30°	82526	83105	83261
35°	79945	80722	79321
40°	76192	77690	77023
45°	72117	73741	71394
50°	63512	69051	63106
55°	51426	63185	51661
60°	37631	52393	36878
65°	22877	37306	22260
70°	8915	20087	8548
75°	969	5406	969
80°	722	722	722
85°	0	0	0

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C20D010 FEU4C209035 F4LC-CSSQ-MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.6	4.4
10°-20°	247.8	12.5
20°-30°	367.7	18.6
30°-40°	426.1	21.5
40°-50°	408.5	20.6
50°-60°	300.4	15.2
60°-70°	129.7	6.5
70°-80°	14.0	0.7
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	703.1	35.5
0°-40°	1129.2	57.0
0°-60°	1838.1	92.7
0°-90°	1982.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1982.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	928	928	928	928	928	
5°	909	919	921	923	924	87
15°	874	879	875	876	878	246
25°	797	796	797	799	803	365
35°	679	683	685	684	673	424
45°	528	530	540	532	523	402
55°	306	337	376	336	307	275
65°	100	125	163	124	98	103
75°	3	4	14	3	3	8
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C20D010 FEU4C209035 F4LC-CSSQ-MW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	927.8	927.8	927.8	927.8	927.8	927.8	927.8	927.8	927.8	927.8	927.8
2.5°	921.2	931.8	933.1	926.5	923.9	919.9	929.1	922.6	925.2	922.6	921.2
5°	909.4	921.2	922.6	922.6	919.9	918.6	922.6	921.2	919.9	917.3	921.2
7.5°	904.1	910.7	917.3	909.4	913.3	912.0	921.2	917.3	916.0	916.0	913.3
10°	906.8	905.4	910.7	902.8	905.4	902.8	910.7	910.7	908.0	905.4	904.1
12.5°	885.6	896.2	896.2	894.9	892.2	888.3	896.2	901.5	893.5	893.5	892.2
15°	873.8	876.4	877.7	877.7	876.4	879.1	883.0	877.7	879.1	872.5	875.1
17.5°	860.6	855.4	859.3	856.6	858.0	860.6	865.9	865.9	858.0	856.6	859.3
20°	830.3	846.1	847.4	839.5	840.8	840.8	850.1	842.2	847.4	840.8	843.5
22.5°	815.8	826.3	827.7	817.1	823.7	815.8	825.0	813.1	826.3	817.1	821.0
25°	797.3	796.0	800.0	794.7	796.0	796.0	802.6	797.3	801.3	796.0	797.3
27.5°	767.1	777.6	776.3	771.0	773.6	772.3	785.5	771.0	778.9	772.3	775.0
30°	740.7	749.9	747.3	742.0	742.0	738.0	752.5	748.6	747.3	747.3	745.9
32.5°	714.3	715.7	713.0	714.3	715.7	710.4	722.2	716.9	715.7	716.9	718.3
35°	678.7	678.7	681.3	677.4	682.7	682.7	693.2	686.6	685.3	681.3	685.3
37.5°	647.1	643.2	644.5	644.5	647.1	649.7	655.0	652.4	652.4	648.4	651.1
40°	604.9	602.3	606.2	606.2	610.2	610.2	615.5	612.8	616.8	616.8	616.8
42.5°	568.0	568.0	565.4	569.3	570.7	569.3	578.6	577.2	578.6	576.0	577.2
45°	528.5	528.5	525.8	524.5	531.1	529.8	540.4	536.4	541.6	539.0	540.4
47.5°	474.4	481.0	477.1	481.0	488.9	490.3	496.9	494.2	499.5	495.6	500.8
50°	423.1	423.1	427.0	432.3	440.2	441.5	449.4	454.7	457.3	458.6	460.0
52.5°	369.0	367.7	371.7	378.2	384.8	390.1	398.0	405.9	411.2	419.1	415.1
55°	305.7	308.4	312.4	320.3	330.8	337.4	344.0	354.5	363.8	367.7	375.6
57.5°	251.7	249.1	251.7	262.2	274.1	279.4	288.6	299.2	312.4	320.3	322.9
60°	195.0	196.4	199.0	208.3	217.5	225.4	229.3	246.4	258.3	266.2	271.5
62.5°	143.7	146.3	148.9	156.9	166.0	172.7	179.2	193.7	204.3	212.2	217.5
65°	100.2	101.5	105.4	109.4	118.6	125.2	130.5	142.3	152.9	159.5	163.4
67.5°	61.9	63.2	65.9	71.2	77.8	83.0	88.3	96.2	105.4	112.0	113.4
70°	31.6	33.0	34.3	38.2	43.5	46.1	50.1	56.7	63.2	68.5	71.2
72.5°	10.5	10.5	11.9	14.5	17.2	19.8	21.1	27.7	33.0	35.6	36.9
75°	2.6	2.6	2.6	2.6	2.6	4.0	4.0	7.9	10.5	13.2	14.5
77.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	2.6	2.6
80°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C20D010 FEU4C209035 F4LC-CSSQ-MW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	927.8	927.8	927.8	927.8	927.8	927.8	927.8	927.8	927.8	927.8
2.5°	927.8	925.2	923.9	925.2	925.2	923.9	927.8	933.1	939.7	922.6
5°	926.5	923.9	926.5	918.6	922.6	919.9	925.2	923.9	929.1	923.9
7.5°	922.6	917.3	918.6	914.7	919.9	913.3	917.3	925.2	919.9	912.0
10°	909.4	906.8	916.0	902.8	900.1	905.4	916.0	908.0	905.4	908.0
12.5°	896.2	896.2	900.1	889.6	890.9	893.5	898.8	893.5	896.2	902.8
15°	881.7	879.1	885.6	877.7	876.4	873.8	879.1	879.1	881.7	877.7
17.5°	864.5	860.6	860.6	858.0	856.6	863.3	865.9	867.2	868.5	863.3
20°	843.5	842.2	846.1	842.2	843.5	844.8	844.8	842.2	854.0	839.5
22.5°	821.0	825.0	819.8	817.1	819.8	822.4	822.4	823.7	821.0	818.4
25°	798.7	801.3	802.6	794.7	798.7	794.7	803.9	805.2	800.0	802.6
27.5°	778.9	775.0	773.6	768.3	771.0	769.7	771.0	771.0	778.9	768.3
30°	748.6	744.6	745.9	742.0	743.3	742.0	743.3	743.3	748.6	747.3
32.5°	719.6	715.7	716.9	713.0	713.0	714.3	711.7	711.7	715.7	713.0
35°	691.9	682.7	684.0	682.7	684.0	678.7	678.7	677.4	680.1	673.4
37.5°	652.4	648.4	647.1	645.8	647.1	644.5	647.1	643.2	647.1	641.8
40°	616.8	614.1	615.5	607.6	607.6	608.9	606.2	604.9	606.2	611.5
42.5°	581.2	576.0	573.3	570.7	572.0	568.0	566.7	564.1	566.7	561.4
45°	539.0	539.0	537.7	531.1	532.5	532.5	527.2	521.9	523.2	523.2
47.5°	500.8	498.2	496.9	490.3	488.9	487.7	482.3	478.4	478.4	474.4
50°	458.6	456.0	452.1	445.4	442.8	434.9	431.0	425.7	420.4	420.4
52.5°	419.1	409.9	404.6	394.0	390.1	386.1	375.6	371.7	367.7	363.8
55°	371.7	363.8	353.2	341.3	336.1	329.5	318.9	311.0	305.7	307.1
57.5°	325.5	312.4	301.8	286.0	279.4	275.4	264.9	254.3	249.1	249.1
60°	268.9	258.3	245.1	230.6	225.4	218.8	205.6	199.0	195.0	191.1
62.5°	214.8	206.9	195.0	176.6	172.7	166.0	156.9	148.9	145.0	145.0
65°	160.8	152.9	142.3	129.2	123.9	118.6	110.7	102.8	98.8	97.5
67.5°	113.4	104.1	94.9	84.4	80.4	77.8	69.8	64.6	61.9	60.6
70°	68.5	63.2	56.7	48.8	44.8	42.2	36.9	33.0	31.6	30.3
72.5°	35.6	31.6	26.3	21.1	18.4	15.8	13.2	10.5	9.2	9.2
75°	13.2	10.5	6.6	4.0	2.6	2.6	2.6	2.6	2.6	2.6
77.5°	2.6	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
80°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)