

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C90D010 FEU4C909027 F4LC-CSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C90D010 FEU4C909027 F4LC-CSSQ-MW
 Description: 4 INCH 9000 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 2700K, 90CRI LEDS AND F4LC-CSSQ TRIM WITH MW FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 8944.0 lumens
 Efficiency: N/A
 Efficacy: 92.1 lumens/watt
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 97.1
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C90D010 FEU4C909027 F4LC-CSSQ-MW

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: FLDSQ4C90D010 FEU4C909027 F4LC-CSSQ-MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89				89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67				67
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46				46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41				41
8	65	53	45	40	64	52	45	39	51	44	39	50	44	39	49	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	33				33
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	31				31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	403999	403999	403999
5°	397474	402646	403799
10°	400904	399748	401482
15°	393887	394466	395655
20°	384726	390826	389008
25°	383067	383067	385590
30°	372385	375037	375705
35°	360771	364281	357967
40°	343838	350564	347567
45°	325420	332734	322172
50°	286590	311568	284804
55°	232098	285122	233124
60°	169840	236436	166424
65°	103220	168357	100503
70°	40258	90643	38621
75°	4436	24419	4436
80°	3390	3390	3390
85°	0	0	0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C90D010 FEU4C909027 F4LC-CSSQ-MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	395.2	4.4
10°-20°	1118.3	12.5
20°-30°	1659.4	18.6
30°-40°	1922.7	21.5
40°-50°	1843.5	20.6
50°-60°	1355.4	15.2
60°-70°	585.4	6.5
70°-80°	63.2	0.7
80°-90°	0.8	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	3172.9	35.5
0°-40°	5095.7	57.0
0°-60°	8294.6	92.7
0°-90°	8944.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	8944.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4187	4187	4187	4187	4187	
5°	4104	4145	4157	4163	4169	392
15°	3943	3967	3949	3955	3961	1111
25°	3598	3592	3598	3604	3622	1647
35°	3063	3081	3093	3086	3039	1915
45°	2385	2391	2438	2403	2361	1813
55°	1380	1522	1695	1517	1386	1242
65°	452	565	737	559	440	465
75°	12	18	66	12	12	37
85°	0	0	0	0	0	1
90°	0	0	0	0	0	

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C90D010 FEU4C909027 F4LC-CSSQ-MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	4187.0	4187.0	4187.0	4187.0	4187.0	4187.0	4187.0	4187.0	4187.0	4187.0	4187.0
2.5°	4157.1	4204.7	4210.7	4180.9	4169.0	4151.3	4192.8	4163.2	4175.1	4163.2	4157.1
5°	4103.7	4157.1	4163.2	4163.2	4151.3	4145.2	4163.2	4157.1	4151.3	4139.4	4157.1
7.5°	4080.0	4109.6	4139.4	4103.7	4121.5	4115.6	4157.1	4139.4	4133.3	4133.3	4121.5
10°	4091.8	4085.8	4109.6	4073.9	4085.8	4073.9	4109.6	4109.6	4097.7	4085.8	4080.0
12.5°	3996.5	4044.0	4044.0	4038.2	4026.3	4008.4	4044.0	4068.1	4032.2	4032.2	4026.3
15°	3943.1	3955.0	3960.8	3960.8	3955.0	3966.9	3984.6	3960.8	3966.9	3937.0	3948.9
17.5°	3883.6	3859.9	3877.6	3865.7	3871.8	3883.6	3907.4	3907.4	3871.8	3865.7	3877.6
20°	3746.8	3818.1	3824.2	3788.5	3794.4	3794.4	3836.1	3800.4	3824.2	3794.4	3806.2
22.5°	3681.3	3728.8	3734.9	3687.3	3717.0	3681.3	3723.0	3669.4	3728.8	3687.3	3705.1
25°	3598.1	3592.2	3609.9	3586.2	3592.2	3592.2	3621.8	3598.1	3616.0	3592.2	3598.1
27.5°	3461.4	3509.0	3502.9	3479.1	3491.0	3485.2	3544.7	3479.1	3514.8	3485.2	3497.1
30°	3342.3	3384.0	3372.1	3348.4	3348.4	3330.4	3395.9	3378.0	3372.1	3372.1	3366.1
32.5°	3223.4	3229.5	3217.6	3223.4	3229.5	3205.7	3259.1	3235.3	3229.5	3235.3	3241.3
35°	3062.8	3062.8	3074.7	3056.9	3080.7	3080.7	3128.3	3098.4	3092.6	3074.7	3092.6
37.5°	2920.1	2902.4	2908.2	2908.2	2920.1	2932.0	2955.8	2943.9	2943.9	2926.1	2938.0
40°	2729.8	2717.9	2735.7	2735.7	2753.6	2753.6	2777.4	2765.5	2783.2	2783.2	2783.2
42.5°	2563.4	2563.4	2551.5	2569.2	2575.3	2569.2	2610.9	2604.9	2610.9	2599.0	2604.9
45°	2384.8	2384.8	2372.9	2367.1	2396.7	2390.9	2438.4	2420.5	2444.2	2432.4	2438.4
47.5°	2140.9	2170.8	2152.8	2170.8	2206.4	2212.5	2242.1	2230.2	2254.0	2236.3	2260.1
50°	1909.2	1909.2	1926.9	1950.7	1986.4	1992.4	2028.1	2051.9	2063.8	2069.6	2075.6
52.5°	1665.3	1659.3	1677.2	1706.8	1736.7	1760.4	1796.1	1831.8	1855.6	1891.2	1873.3
55°	1379.7	1391.6	1409.6	1445.2	1492.8	1522.4	1552.2	1599.8	1641.5	1659.3	1694.9
57.5°	1135.9	1124.0	1135.9	1183.4	1237.0	1260.8	1302.6	1350.1	1409.6	1445.2	1457.1
60°	880.1	886.2	898.1	939.8	981.3	1017.0	1034.9	1112.1	1165.7	1201.4	1225.2
62.5°	648.4	660.3	672.1	707.8	749.3	779.2	808.8	874.3	921.8	957.5	981.3
65°	452.1	457.9	475.8	493.6	535.3	564.9	588.7	642.3	689.9	719.7	737.4
67.5°	279.5	285.4	297.3	321.3	350.9	374.7	398.4	434.1	475.8	505.4	511.5
70°	142.7	148.7	154.6	172.5	196.3	208.2	225.9	255.8	285.4	309.1	321.3
72.5°	47.6	47.6	53.6	65.5	77.4	89.3	95.1	125.0	148.7	160.6	166.5
75°	11.9	11.9	11.9	11.9	11.9	18.0	18.0	35.7	47.6	59.5	65.5
77.5°	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	11.9	11.9
80°	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C90D010 FEU4C909027 F4LC-CSSQ-MW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	4187.0	4187.0	4187.0	4187.0	4187.0	4187.0	4187.0	4187.0	4187.0	4187.0
2.5°	4187.0	4175.1	4169.0	4175.1	4175.1	4169.0	4187.0	4210.7	4240.4	4163.2
5°	4180.9	4169.0	4180.9	4145.2	4163.2	4151.3	4175.1	4169.0	4192.8	4169.0
7.5°	4163.2	4139.4	4145.2	4127.5	4151.3	4121.5	4139.4	4175.1	4151.3	4115.6
10°	4103.7	4091.8	4133.3	4073.9	4062.0	4085.8	4133.3	4097.7	4085.8	4097.7
12.5°	4044.0	4044.0	4062.0	4014.4	4020.3	4032.2	4055.9	4032.2	4044.0	4073.9
15°	3978.8	3966.9	3996.5	3960.8	3955.0	3943.1	3966.9	3966.9	3978.8	3960.8
17.5°	3901.4	3883.6	3883.6	3871.8	3865.7	3895.5	3907.4	3913.3	3919.3	3895.5
20°	3806.2	3800.4	3818.1	3800.4	3806.2	3812.3	3812.3	3800.4	3853.8	3788.5
22.5°	3705.1	3723.0	3699.2	3687.3	3699.2	3711.1	3711.1	3717.0	3705.1	3693.2
25°	3604.1	3616.0	3621.8	3586.2	3604.1	3586.2	3627.9	3633.7	3609.9	3621.8
27.5°	3514.8	3497.1	3491.0	3467.3	3479.1	3473.3	3479.1	3479.1	3514.8	3467.3
30°	3378.0	3360.2	3366.1	3348.4	3354.2	3348.4	3354.2	3354.2	3378.0	3372.1
32.5°	3247.2	3229.5	3235.3	3217.6	3217.6	3223.4	3211.5	3211.5	3229.5	3217.6
35°	3122.2	3080.7	3086.5	3080.7	3086.5	3062.8	3062.8	3056.9	3068.8	3039.0
37.5°	2943.9	2926.1	2920.1	2914.3	2920.1	2908.2	2920.1	2902.4	2920.1	2896.3
40°	2783.2	2771.3	2777.4	2741.7	2741.7	2747.6	2735.7	2729.8	2735.7	2759.4
42.5°	2622.8	2599.0	2587.2	2575.3	2581.1	2563.4	2557.3	2545.4	2557.3	2533.5
45°	2432.4	2432.4	2426.5	2396.7	2402.7	2402.7	2379.0	2355.2	2361.0	2361.0
47.5°	2260.1	2248.2	2242.1	2212.5	2206.4	2200.6	2176.6	2158.9	2158.9	2140.9
50°	2069.6	2057.7	2040.0	2010.1	1998.2	1962.6	1944.9	1921.1	1897.3	1897.3
52.5°	1891.2	1849.5	1825.7	1778.2	1760.4	1742.5	1694.9	1677.2	1659.3	1641.5
55°	1677.2	1641.5	1594.0	1540.4	1516.6	1486.7	1439.2	1403.5	1379.7	1385.8
57.5°	1469.0	1409.6	1362.0	1290.7	1260.8	1242.9	1195.3	1147.7	1124.0	1124.0
60°	1213.3	1165.7	1106.2	1040.7	1017.0	987.3	927.7	898.1	880.1	862.4
62.5°	969.4	933.7	880.1	796.9	779.2	749.3	707.8	672.1	654.2	654.2
65°	725.5	689.9	642.3	582.9	559.1	535.3	499.6	463.9	446.0	440.2
67.5°	511.5	469.8	428.3	380.7	362.8	350.9	315.2	291.4	279.5	273.5
70°	309.1	285.4	255.8	220.1	202.1	190.2	166.5	148.7	142.7	136.9
72.5°	160.6	142.7	118.9	95.1	83.2	71.3	59.5	47.6	41.7	41.7
75°	59.5	47.6	29.8	18.0	11.9	11.9	11.9	11.9	11.9	11.9
77.5°	11.9	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1
80°	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)