

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P973806

Luminaire Tested: FLR2-22-25HE-L835-CP080

Issue Date: 3/13/2025

Test Information

Test Method: LM-79-2019
Report Number: P973806
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-281-2)
Test Lab: INNOVATION CENTER
Issue Date: 3/13/2025
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: FAIL-SAFE
Catalog Number: FLR2-22-25HE-L835-CP080
Description: SHAPER SENSE CIRCLE

Light Source:
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2343.5 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.38
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')
CIE Type: Direct

Input Watts (W): 19.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor:
Total Harmonic Distortion (THDi):
Frequency (hertz): 60
Stabilization Time: HR
Operation Time: HR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P973806
CATALOG NUMBER: FLR2-22-25HE-L835-CP080

Luminous Intensity Polar Plot





TEST NUMBER: P973806
 CATALOG NUMBER: FLR2-22-25HE-L835-CP080

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	70	66	62	60
4	83	71	63	56	81	70	62	55	67	60	55	65	59	54	63	58	53	51
5	76	64	55	48	74	62	54	48	60	53	47	58	52	47	57	51	46	44
6	71	57	48	42	69	56	48	42	54	47	41	53	46	41	51	45	41	39
7	65	52	43	37	64	51	43	37	50	42	37	48	41	36	47	41	36	34
8	61	47	39	33	59	47	39	33	45	38	33	44	37	32	43	37	32	30
9	57	43	35	30	55	43	35	30	42	34	29	41	34	29	40	34	29	27
10	53	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	26	25

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2255	2255	2255
5°	2269	2259	2266
10°	2269	2259	2263
15°	2267	2257	2260
20°	2259	2250	2253
25°	2247	2238	2239
30°	2231	2221	2223
35°	2211	2202	2204
40°	2187	2177	2178
45°	2155	2145	2149
50°	2117	2102	2106
55°	2057	2040	2047
60°	1956	1947	1947
65°	1826	1822	1816
70°	1617	1625	1621
75°	1362	1351	1340
80°	978	962	955
85°	513	513	494

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2155 cd/sqm



TEST NUMBER: P973806
 CATALOG NUMBER: FLR2-22-25HE-L835-CP080

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.4	3.4
10°-20°	228.2	9.7
20°-30°	346.8	14.8
30°-40°	419.2	17.9
40°-50°	435.1	18.6
50°-60°	389.0	16.6
60°-70°	282.8	12.1
70°-80°	139.1	5.9
80°-90°	24.1	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	654.3	27.9
0°-40°	1073.5	45.8
0°-60°	1897.5	81.0
0°-90°	2343.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2343.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	838	838	838	838	838	
5°	840	830	836	833	839	80
15°	814	804	810	808	811	230
25°	757	748	754	752	754	349
35°	673	668	670	671	671	421
45°	566	564	564	565	565	437
55°	438	436	435	436	436	391
65°	287	288	286	286	285	283
75°	131	132	130	130	129	139
85°	17	17	17	17	16	24
90°	0	0	0	0	0	



TEST NUMBER: P973806
 CATALOG NUMBER: FLR2-22-25HE-L835-CP080

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	838.0	838.0	838.0	838.0	838.0
2.5°	842.7	832.8	839.0	835.4	841.1
5°	840.1	830.2	836.4	833.3	839.0
7.5°	835.4	825.6	831.8	828.7	833.3
10°	830.2	819.9	826.6	823.5	828.2
12.5°	823.5	813.7	819.9	817.3	821.4
15°	813.7	804.4	810.0	808.0	811.1
17.5°	801.8	792.4	798.1	796.6	799.2
20°	788.8	780.0	785.7	784.2	786.8
22.5°	774.3	765.0	770.2	769.2	771.2
25°	756.7	748.5	753.6	752.1	754.1
27.5°	738.1	730.3	734.5	734.5	735.5
30°	717.9	710.7	714.8	714.8	715.3
32.5°	696.2	690.5	693.1	693.6	693.6
35°	672.9	668.2	670.3	670.8	670.8
37.5°	648.6	643.9	645.4	646.5	646.5
40°	622.7	618.5	619.6	620.6	620.1
42.5°	594.7	591.6	592.1	593.2	593.2
45°	566.3	563.7	563.7	564.7	564.7
47.5°	537.3	534.7	533.6	534.7	534.7
50°	505.7	503.1	502.1	503.1	503.1
52.5°	472.6	470.0	470.0	470.0	470.5
55°	438.4	435.8	434.8	435.8	436.3
57.5°	402.2	401.1	399.6	400.1	398.6
60°	363.4	363.4	361.8	362.8	361.8
62.5°	325.6	326.6	325.1	325.1	324.0
65°	286.8	287.8	286.2	286.2	285.2
67.5°	246.9	248.4	246.4	246.4	245.3
70°	205.5	208.6	206.5	207.0	206.0
72.5°	168.2	169.8	167.7	167.7	166.7
75°	131.0	132.0	129.9	130.4	128.9
77.5°	94.2	95.8	93.7	94.2	93.7
80°	63.1	63.7	62.1	62.6	61.6
82.5°	36.7	37.3	36.7	36.2	35.7
85°	16.6	17.1	16.6	16.6	16.0
87.5°	4.1	4.1	4.1	4.1	4.1
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)