

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: FAIL-SAFE

Report Number: P973770

Luminaire Tested: FLR2-22-25HE-L930-CP125

Issue Date: 3/13/2025

**Test Information**

Test Method: LM-79-2019  
Report Number: P973770  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2411-281-2)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/13/2025  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: FAIL-SAFE  
Catalog Number: FLR2-22-25HE-L930-CP125  
Description: SHAPER SENSE CIRCLE  
  
Light Source:  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1904.6 lumens  
Efficiency: N/A  
Efficacy: 99.2 lumens/watt  
Spacing Criteria (0/90/45): 1.27 / 1.27 / 1.38  
Luminous Opening: Rectangular (W 2' x L: 2' x H: 0')  
CIE Type: Direct

Input Watts (W): 19.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor:  
Total Harmonic Distortion (THDi):  
Frequency (hertz): 60  
Stabilization Time: HR  
Operation Time: HR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P973770  
CATALOG NUMBER: FLR2-22-25HE-L930-CP125

### Luminous Intensity Polar Plot





TEST NUMBER: P973770  
 CATALOG NUMBER: FLR2-22-25HE-L930-CP125

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100														
1	109	105	101	97	107	102	99	95	98	95	92	94	92	89	91	89	87	85						85														
2	99	91	85	79	97	90	83	78	86	81	76	83	78	75	80	76	73	71						71														
3	91	80	72	66	88	79	71	65	76	69	64	73	68	63	70	66	62	60						60														
4	83	71	63	56	81	70	62	55	67	60	55	65	59	54	63	58	53	51						51														
5	76	64	55	48	74	62	54	48	60	53	47	58	52	47	57	51	46	44						44														
6	71	57	48	42	69	56	48	42	54	47	41	53	46	41	51	45	41	39						39														
7	65	52	43	37	64	51	43	37	50	42	37	48	41	36	47	41	36	34						34														
8	61	47	39	33	59	47	39	33	45	38	33	44	37	32	43	37	32	30						30														
9	57	43	35	30	55	43	35	30	42	34	29	41	34	29	40	34	29	27						27														
10	53	40	32	27	52	40	32	27	39	32	27	38	31	27	37	31	26	25						25														

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1833	1833	1833
5°	1844	1836	1842
10°	1844	1836	1839
15°	1842	1834	1836
20°	1836	1829	1831
25°	1826	1819	1820
30°	1813	1805	1807
35°	1797	1790	1791
40°	1778	1769	1770
45°	1751	1743	1746
50°	1721	1708	1712
55°	1672	1658	1664
60°	1589	1582	1582
65°	1484	1481	1476
70°	1314	1320	1317
75°	1106	1098	1089
80°	795	783	776
85°	417	417	401

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1751 cd/sqm



TEST NUMBER: P973770  
 CATALOG NUMBER: FLR2-22-25HE-L930-CP125

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	64.5	3.4
10°-20°	185.5	9.7
20°-30°	281.8	14.8
30°-40°	340.7	17.9
40°-50°	353.6	18.6
50°-60°	316.1	16.6
60°-70°	229.8	12.1
70°-80°	113.0	5.9
80°-90°	19.6	1.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	531.8	27.9
0°-40°	872.4	45.8
0°-60°	1542.2	81.0
0°-90°	1904.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1904.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	681	681	681	681	681	
5°	683	675	680	677	682	65
15°	661	654	658	657	659	187
25°	615	608	612	611	613	283
35°	547	543	545	545	545	342
45°	460	458	458	459	459	355
55°	356	354	353	354	355	318
65°	233	234	233	233	232	230
75°	106	107	106	106	105	113
85°	14	14	14	14	13	20
90°	0	0	0	0	0	



TEST NUMBER: P973770  
 CATALOG NUMBER: FLR2-22-25HE-L930-CP125

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	681.1	681.1	681.1	681.1	681.1
2.5°	684.8	676.9	681.9	679.0	683.6
5°	682.7	674.8	679.8	677.3	681.9
7.5°	679.0	671.0	676.0	673.5	677.3
10°	674.8	666.3	671.8	669.3	673.1
12.5°	669.3	661.3	666.3	664.2	667.6
15°	661.3	653.7	658.3	656.7	659.2
17.5°	651.6	644.0	648.7	647.4	649.5
20°	641.1	633.9	638.6	637.3	639.4
22.5°	629.3	621.7	626.0	625.1	626.8
25°	615.0	608.3	612.5	611.2	612.9
27.5°	599.9	593.6	596.9	596.9	597.8
30°	583.5	577.6	580.9	580.9	581.4
32.5°	565.8	561.2	563.3	563.7	563.7
35°	546.9	543.1	544.8	545.2	545.2
37.5°	527.1	523.3	524.6	525.4	525.4
40°	506.1	502.7	503.5	504.4	504.0
42.5°	483.3	480.8	481.2	482.1	482.1
45°	460.2	458.1	458.1	458.9	458.9
47.5°	436.7	434.6	433.7	434.6	434.6
50°	411.0	408.9	408.0	408.9	408.9
52.5°	384.1	382.0	382.0	382.0	382.4
55°	356.3	354.2	353.4	354.2	354.6
57.5°	326.9	326.0	324.8	325.2	323.9
60°	295.3	295.3	294.0	294.9	294.0
62.5°	264.6	265.4	264.2	264.2	263.3
65°	233.1	233.9	232.6	232.6	231.8
67.5°	200.7	201.9	200.2	200.2	199.4
70°	167.0	169.5	167.8	168.3	167.4
72.5°	136.7	138.0	136.3	136.3	135.5
75°	106.4	107.3	105.6	106.0	104.7
77.5°	76.6	77.8	76.1	76.6	76.1
80°	51.3	51.7	50.5	50.9	50.1
82.5°	29.9	30.3	29.9	29.4	29.0
85°	13.5	13.9	13.5	13.5	13.0
87.5°	3.4	3.4	3.4	3.4	3.4
90°	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)