

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C25D010 FEU4C259027 F4LC-DFSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C25D010 FEU4C259027 F4LC-DFSSQ-MW
 Description: 4 INCH 2500 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 2700K, 90CRI LEDS AND F4LC-DFSSQ TRIM WITH MW FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 2362.0 lumens
 Efficiency: N/A
 Efficacy: 75.0 lumens/watt
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 31.5
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C25D010 FEU4C259027 F4LC-DFSSQ-MW

Luminous Intensity Polar Plot



TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C25D010 FEU4C259027 F4LC-DFSSQ-MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96		97	95	94		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	74	71		77	73	69	67
4	88	77	70	64	86	76	69	63	74	67	63		71	66	62		69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55		65	59	54		63	58	54	52
6	75	63	55	49	73	62	55	49	61	54	49		59	53	48		57	52	48	46
7	70	58	50	44	68	57	49	44	55	49	44		54	48	43		53	47	43	41
8	65	53	45	40	64	52	45	39	51	44	39		50	44	39		49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36		46	40	35		45	39	35	33
10	57	45	38	33	56	44	37	33	44	37	32		43	37	32		42	36	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	106688	106688	106688
5°	104964	106330	106640
10°	105874	105571	106021
15°	104018	104178	104488
20°	101603	103215	102733
25°	101162	101162	101833
30°	98347	99037	99216
35°	95270	96200	94539
40°	90803	92579	91785
45°	85940	87878	85080
50°	75685	82290	75220
55°	61301	75297	61570
60°	44848	62428	43941
65°	27260	44452	26530
70°	10636	23923	10184
75°	1156	6450	1156
80°	889	889	889
85°	0	0	0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C25D010 FEU4C259027 F4LC-DFSSQ-MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	4.4
10°-20°	295.3	12.5
20°-30°	438.2	18.6
30°-40°	507.8	21.5
40°-50°	486.8	20.6
50°-60°	357.9	15.2
60°-70°	154.6	6.5
70°-80°	16.7	0.7
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	837.9	35.5
0°-40°	1345.7	57.0
0°-60°	2190.5	92.7
0°-90°	2362.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2362.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1106	1106	1106	1106	1106	
5°	1084	1095	1098	1099	1101	103
15°	1041	1048	1043	1044	1046	293
25°	950	949	950	952	956	435
35°	809	814	817	815	803	506
45°	630	631	644	634	624	479
55°	364	402	448	400	366	328
65°	119	149	195	148	116	123
75°	3	5	17	3	3	10
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C25D010 FEU4C259027 F4LC-DFSSQ-MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	1105.7	1105.7	1105.7	1105.7	1105.7	1105.7	1105.7	1105.7	1105.7	1105.7	1105.7
2.5°	1097.8	1110.4	1112.0	1104.1	1101.0	1096.3	1107.3	1099.4	1102.6	1099.4	1097.8
5°	1083.7	1097.8	1099.4	1099.4	1096.3	1094.7	1099.4	1097.8	1096.3	1093.2	1097.8
7.5°	1077.5	1085.3	1093.2	1083.7	1088.4	1086.9	1097.8	1093.2	1091.6	1091.6	1088.4
10°	1080.6	1079.0	1085.3	1075.9	1079.0	1075.9	1085.3	1085.3	1082.1	1079.0	1077.5
12.5°	1055.4	1068.0	1068.0	1066.4	1063.3	1058.6	1068.0	1074.3	1064.8	1064.8	1063.3
15°	1041.3	1044.5	1046.0	1046.0	1044.5	1047.6	1052.3	1046.0	1047.6	1039.7	1042.9
17.5°	1025.6	1019.3	1024.0	1020.9	1022.5	1025.6	1031.9	1031.9	1022.5	1020.9	1024.0
20°	989.5	1008.3	1009.9	1000.5	1002.0	1002.0	1013.1	1003.6	1009.9	1002.0	1005.2
22.5°	972.2	984.7	986.3	973.8	981.6	972.2	983.2	969.0	984.7	973.8	978.5
25°	950.2	948.7	953.3	947.1	948.7	948.7	956.5	950.2	954.9	948.7	950.2
27.5°	914.1	926.7	925.1	918.8	921.9	920.4	936.1	918.8	928.2	920.4	923.5
30°	882.7	893.7	890.5	884.3	884.3	879.5	896.8	892.1	890.5	890.5	888.9
32.5°	851.3	852.9	849.7	851.3	852.9	846.6	860.7	854.4	852.9	854.4	856.0
35°	808.8	808.8	812.0	807.3	813.6	813.6	826.1	818.3	816.7	812.0	816.7
37.5°	771.2	766.5	768.0	768.0	771.2	774.3	780.6	777.4	777.4	772.8	775.9
40°	720.9	717.8	722.5	722.5	727.2	727.2	733.5	730.3	735.0	735.0	735.0
42.5°	677.0	677.0	673.8	678.5	680.1	678.5	689.5	687.9	689.5	686.4	687.9
45°	629.8	629.8	626.7	625.1	632.9	631.4	644.0	639.2	645.5	642.4	644.0
47.5°	565.4	573.3	568.5	573.3	582.7	584.3	592.1	589.0	595.3	590.6	596.9
50°	504.2	504.2	508.9	515.2	524.6	526.2	535.6	541.9	545.0	546.6	548.2
52.5°	439.8	438.2	442.9	450.7	458.6	464.9	474.3	483.8	490.0	499.5	494.7
55°	364.4	367.5	372.2	381.7	394.2	402.0	409.9	422.5	433.5	438.2	447.6
57.5°	300.0	296.8	300.0	312.5	326.7	333.0	344.0	356.5	372.2	381.7	384.8
60°	232.4	234.0	237.2	248.2	259.1	268.6	273.3	293.7	307.8	317.3	323.5
62.5°	171.2	174.4	177.5	186.9	197.9	205.8	213.6	230.9	243.4	252.9	259.1
65°	119.4	120.9	125.7	130.3	141.4	149.2	155.5	169.6	182.2	190.1	194.7
67.5°	73.8	75.4	78.5	84.8	92.7	98.9	105.2	114.6	125.7	133.5	135.1
70°	37.7	39.3	40.8	45.6	51.8	55.0	59.7	67.5	75.4	81.6	84.8
72.5°	12.6	12.6	14.2	17.3	20.4	23.6	25.1	33.0	39.3	42.4	44.0
75°	3.1	3.1	3.1	3.1	3.1	4.7	4.7	9.4	12.6	15.7	17.3
77.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	3.1	3.1
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C25D010 FEU4C259027 F4LC-DFSSQ-MW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	1105.7	1105.7	1105.7	1105.7	1105.7	1105.7	1105.7	1105.7	1105.7	1105.7
2.5°	1105.7	1102.6	1101.0	1102.6	1102.6	1101.0	1105.7	1112.0	1119.8	1099.4
5°	1104.1	1101.0	1104.1	1094.7	1099.4	1096.3	1102.6	1101.0	1107.3	1101.0
7.5°	1099.4	1093.2	1094.7	1090.0	1096.3	1088.4	1093.2	1102.6	1096.3	1086.9
10°	1083.7	1080.6	1091.6	1075.9	1072.7	1079.0	1091.6	1082.1	1079.0	1082.1
12.5°	1068.0	1068.0	1072.7	1060.2	1061.7	1064.8	1071.1	1064.8	1068.0	1075.9
15°	1050.7	1047.6	1055.4	1046.0	1044.5	1041.3	1047.6	1047.6	1050.7	1046.0
17.5°	1030.3	1025.6	1025.6	1022.5	1020.9	1028.8	1031.9	1033.4	1035.0	1028.8
20°	1005.2	1003.6	1008.3	1003.6	1005.2	1006.8	1006.8	1003.6	1017.7	1000.5
22.5°	978.5	983.2	976.9	973.8	976.9	980.1	980.1	981.6	978.5	975.3
25°	951.8	954.9	956.5	947.1	951.8	947.1	958.1	959.6	953.3	956.5
27.5°	928.2	923.5	921.9	915.7	918.8	917.3	918.8	918.8	928.2	915.7
30°	892.1	887.4	888.9	884.3	885.8	884.3	885.8	885.8	892.1	890.5
32.5°	857.5	852.9	854.4	849.7	849.7	851.3	848.1	848.1	852.9	849.7
35°	824.5	813.6	815.1	813.6	815.1	808.8	808.8	807.3	810.4	802.6
37.5°	777.4	772.8	771.2	769.6	771.2	768.0	771.2	766.5	771.2	764.9
40°	735.0	731.9	733.5	724.1	724.1	725.6	722.5	720.9	722.5	728.7
42.5°	692.7	686.4	683.2	680.1	681.6	677.0	675.4	672.2	675.4	669.1
45°	642.4	642.4	640.8	632.9	634.5	634.5	628.3	622.0	623.5	623.5
47.5°	596.9	593.7	592.1	584.3	582.7	581.2	574.8	570.1	570.1	565.4
50°	546.6	543.4	538.7	530.9	527.7	518.3	513.6	507.3	501.1	501.1
52.5°	499.5	488.4	482.2	469.6	464.9	460.2	447.6	442.9	438.2	433.5
55°	442.9	433.5	421.0	406.8	400.5	392.6	380.1	370.6	364.4	366.0
57.5°	387.9	372.2	359.7	340.8	333.0	328.2	315.7	303.1	296.8	296.8
60°	320.4	307.8	292.1	274.8	268.6	260.7	245.0	237.2	232.4	227.7
62.5°	256.0	246.6	232.4	210.4	205.8	197.9	186.9	177.5	172.8	172.8
65°	191.6	182.2	169.6	153.9	147.6	141.4	131.9	122.5	117.8	116.2
67.5°	135.1	124.1	113.1	100.5	95.8	92.7	83.2	77.0	73.8	72.2
70°	81.6	75.4	67.5	58.1	53.4	50.2	44.0	39.3	37.7	36.1
72.5°	42.4	37.7	31.4	25.1	22.0	18.8	15.7	12.6	11.0	11.0
75°	15.7	12.6	7.9	4.7	3.1	3.1	3.1	3.1	3.1	3.1
77.5°	3.1	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
80°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)