

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C45D010 FEU4C459027 F4LC-CSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

**Test Information**

Test Method: LM-79-08  
 Report Number: P#  
 Test Lab: INNOVATION CENTER  
 Issue Date: 12/13/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: FAIL-SAFE  
 Catalog Number: FLDSQ4C45D010 FEU4C459027 F4LC-CSSQ-MW  
 Description: 4 INCH 4500 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 2700K, 90CRI LEDS AND F4LC-CSSQ TRIM WITH MW FINISH  
 Light Source: -  
 Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
 Luminaire Lumens: 4397.0 lumens  
 Efficiency: N/A  
 Efficacy: 88.6 lumens/watt  
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29  
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')  
 CIE Type: Direct

Input Watts (W): 49.6  
 Input Voltage (V):  
 Input Current (Ain): NR  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#  
CATALOG NUMBER: FLDSQ4C45D010 FEU4C459027 F4LC-CSSQ-MW

### Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: FLDSQ4C45D010 FEU4C459027 F4LC-CSSQ-MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	111	108	104	101	109	105	102	100	101	99	96	97	95	94	94	92	91	89				89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77				77
3	95	86	79	74	93	85	78	73	82	76	72	79	74	71	77	73	69	67				67
4	88	77	70	64	86	76	69	63	74	67	63	71	66	62	69	65	61	59				59
5	81	70	62	56	79	69	61	56	67	60	55	65	59	54	63	58	54	52				52
6	75	63	55	49	73	62	55	49	61	54	49	59	53	48	57	52	48	46				46
7	70	58	50	44	68	57	49	44	55	49	44	54	48	43	53	47	43	41				41
8	65	53	45	40	64	52	45	39	51	44	39	50	44	39	49	43	39	37				37
9	61	49	41	36	60	48	41	36	47	40	36	46	40	35	45	39	35	33				33
10	57	45	38	33	56	44	37	33	44	37	32	43	37	32	42	36	32	31				31

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	198613	198613	198613
5°	195410	197948	198509
10°	197091	196523	197375
15°	193642	193922	194511
20°	189139	192137	191244
25°	188324	188324	189559
30°	183067	184371	184705
35°	177358	179090	175980
40°	169035	172347	170874
45°	159981	163583	158384
50°	140893	153172	140008
55°	114106	140180	114611
60°	83501	116231	81823
65°	50731	82763	49407
70°	19776	44546	18986
75°	2162	12004	2162
80°	1667	1667	1667
85°	0	0	0

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C45D010 FEU4C459027 F4LC-CSSQ-MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	194.3	4.4
10°-20°	549.8	12.5
20°-30°	815.8	18.6
30°-40°	945.2	21.5
40°-50°	906.3	20.6
50°-60°	666.3	15.2
60°-70°	287.8	6.5
70°-80°	31.1	0.7
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1559.9	35.5
0°-40°	2505.1	57.0
0°-60°	4077.7	92.7
0°-90°	4397.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4397.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2058	2058	2058	2058	2058	
5°	2018	2038	2044	2047	2050	192
15°	1938	1950	1941	1944	1947	546
25°	1769	1766	1769	1772	1780	810
35°	1506	1514	1520	1517	1494	942
45°	1172	1175	1199	1181	1161	891
55°	678	748	833	746	681	610
65°	222	278	362	275	216	228
75°	6	9	32	6	6	18
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C45D010 FEU4C459027 F4LC-CSSQ-MW

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	2058.4	2058.4	2058.4	2058.4	2058.4	2058.4	2058.4	2058.4	2058.4	2058.4	2058.4
2.5°	2043.7	2067.1	2070.1	2055.4	2049.5	2040.8	2061.2	2046.7	2052.5	2046.7	2043.7
5°	2017.5	2043.7	2046.7	2046.7	2040.8	2037.9	2046.7	2043.7	2040.8	2035.0	2043.7
7.5°	2005.8	2020.3	2035.0	2017.5	2026.2	2023.3	2043.7	2035.0	2032.0	2032.0	2026.2
10°	2011.6	2008.6	2020.3	2002.8	2008.6	2002.8	2020.3	2020.3	2014.5	2008.6	2005.8
12.5°	1964.7	1988.1	1988.1	1985.2	1979.4	1970.6	1988.1	1999.9	1982.3	1982.3	1979.4
15°	1938.5	1944.3	1947.2	1947.2	1944.3	1950.2	1958.9	1947.2	1950.2	1935.5	1941.3
17.5°	1909.3	1897.6	1906.3	1900.4	1903.4	1909.3	1920.9	1920.9	1903.4	1900.4	1906.3
20°	1842.0	1877.1	1880.0	1862.5	1865.4	1865.4	1885.9	1868.3	1880.0	1865.4	1871.2
22.5°	1809.8	1833.2	1836.1	1812.8	1827.3	1809.8	1830.3	1803.9	1833.2	1812.8	1821.5
25°	1768.9	1766.0	1774.7	1763.0	1766.0	1766.0	1780.5	1768.9	1777.7	1766.0	1768.9
27.5°	1701.7	1725.1	1722.1	1710.4	1716.2	1713.4	1742.6	1710.4	1727.9	1713.4	1719.2
30°	1643.1	1663.6	1657.8	1646.1	1646.1	1637.3	1669.5	1660.7	1657.8	1657.8	1654.8
32.5°	1584.7	1587.6	1581.8	1584.7	1587.6	1576.0	1602.2	1590.5	1587.6	1590.5	1593.5
35°	1505.7	1505.7	1511.5	1502.8	1514.5	1514.5	1537.9	1523.2	1520.4	1511.5	1520.4
37.5°	1435.6	1426.8	1429.7	1429.7	1435.6	1441.4	1453.1	1447.2	1447.2	1438.5	1444.4
40°	1342.0	1336.2	1344.9	1344.9	1353.7	1353.7	1365.4	1359.6	1368.3	1368.3	1368.3
42.5°	1260.2	1260.2	1254.3	1263.1	1266.0	1263.1	1283.6	1280.6	1283.6	1277.7	1280.6
45°	1172.4	1172.4	1166.6	1163.7	1178.2	1175.4	1198.8	1189.9	1201.6	1195.8	1198.8
47.5°	1052.5	1067.2	1058.4	1067.2	1084.7	1087.7	1102.3	1096.4	1108.1	1099.4	1111.1
50°	938.6	938.6	947.3	959.0	976.5	979.5	997.0	1008.7	1014.6	1017.4	1020.4
52.5°	818.7	815.7	824.5	839.1	853.8	865.5	883.0	900.5	912.2	929.8	920.9
55°	678.3	684.1	693.0	710.5	733.9	748.4	763.1	786.5	807.0	815.7	833.3
57.5°	558.4	552.6	558.4	581.8	608.1	619.8	640.4	663.7	693.0	710.5	716.3
60°	432.7	435.7	441.5	462.0	482.4	500.0	508.8	546.7	573.1	590.6	602.3
62.5°	318.7	324.6	330.4	348.0	368.4	383.0	397.6	429.8	453.2	470.7	482.4
65°	222.2	225.1	233.9	242.6	263.2	277.7	289.4	315.8	339.1	353.8	362.5
67.5°	137.4	140.3	146.1	157.9	172.5	184.2	195.9	213.4	233.9	248.5	251.5
70°	70.1	73.1	76.0	84.8	96.5	102.4	111.1	125.7	140.3	152.0	157.9
72.5°	23.4	23.4	26.4	32.2	38.1	43.9	46.8	61.4	73.1	79.0	81.8
75°	5.8	5.8	5.8	5.8	5.8	8.8	8.8	17.5	23.4	29.2	32.2
77.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	5.8	5.8
80°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#  
 CATALOG NUMBER: FLDSQ4C45D010 FEU4C459027 F4LC-CSSQ-MW

**CANDELA DISTRIBUTION (continued):**

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	2058.4	2058.4	2058.4	2058.4	2058.4	2058.4	2058.4	2058.4	2058.4	2058.4
2.5°	2058.4	2052.5	2049.5	2052.5	2052.5	2049.5	2058.4	2070.1	2084.6	2046.7
5°	2055.4	2049.5	2055.4	2037.9	2046.7	2040.8	2052.5	2049.5	2061.2	2049.5
7.5°	2046.7	2035.0	2037.9	2029.1	2040.8	2026.2	2035.0	2052.5	2040.8	2023.3
10°	2017.5	2011.6	2032.0	2002.8	1996.9	2008.6	2032.0	2014.5	2008.6	2014.5
12.5°	1988.1	1988.1	1996.9	1973.6	1976.4	1982.3	1994.0	1982.3	1988.1	2002.8
15°	1956.0	1950.2	1964.7	1947.2	1944.3	1938.5	1950.2	1950.2	1956.0	1947.2
17.5°	1918.0	1909.3	1909.3	1903.4	1900.4	1915.1	1920.9	1923.8	1926.8	1915.1
20°	1871.2	1868.3	1877.1	1868.3	1871.2	1874.2	1874.2	1868.3	1894.6	1862.5
22.5°	1821.5	1830.3	1818.6	1812.8	1818.6	1824.4	1824.4	1827.3	1821.5	1815.6
25°	1771.8	1777.7	1780.5	1763.0	1771.8	1763.0	1783.5	1786.4	1774.7	1780.5
27.5°	1727.9	1719.2	1716.2	1704.6	1710.4	1707.5	1710.4	1710.4	1727.9	1704.6
30°	1660.7	1651.9	1654.8	1646.1	1649.0	1646.1	1649.0	1649.0	1660.7	1657.8
32.5°	1596.4	1587.6	1590.5	1581.8	1581.8	1584.7	1578.8	1578.8	1587.6	1581.8
35°	1534.9	1514.5	1517.4	1514.5	1517.4	1505.7	1505.7	1502.8	1508.7	1494.0
37.5°	1447.2	1438.5	1435.6	1432.7	1435.6	1429.7	1435.6	1426.8	1435.6	1423.9
40°	1368.3	1362.4	1365.4	1347.9	1347.9	1350.7	1344.9	1342.0	1344.9	1356.6
42.5°	1289.4	1277.7	1271.9	1266.0	1268.9	1260.2	1257.2	1251.4	1257.2	1245.5
45°	1195.8	1195.8	1192.9	1178.2	1181.2	1181.2	1169.5	1157.8	1160.7	1160.7
47.5°	1111.1	1105.2	1102.3	1087.7	1084.7	1081.9	1070.0	1061.3	1061.3	1052.5
50°	1017.4	1011.6	1002.9	988.2	982.4	964.8	956.1	944.4	932.7	932.7
52.5°	929.8	909.2	897.6	874.2	865.5	856.6	833.3	824.5	815.7	807.0
55°	824.5	807.0	783.6	757.3	745.6	730.9	707.5	690.0	678.3	681.3
57.5°	722.2	693.0	669.6	634.5	619.8	611.0	587.6	564.2	552.6	552.6
60°	596.5	573.1	543.8	511.6	500.0	485.4	456.1	441.5	432.7	424.0
62.5°	476.6	459.0	432.7	391.8	383.0	368.4	348.0	330.4	321.6	321.6
65°	356.7	339.1	315.8	286.5	274.8	263.2	245.6	228.1	219.3	216.4
67.5°	251.5	230.9	210.5	187.2	178.3	172.5	155.0	143.3	137.4	134.4
70°	152.0	140.3	125.7	108.2	99.4	93.5	81.8	73.1	70.1	67.3
72.5°	79.0	70.1	58.5	46.8	40.9	35.1	29.2	23.4	20.5	20.5
75°	29.2	23.4	14.7	8.8	5.8	5.8	5.8	5.8	5.8	5.8
77.5°	5.8	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
80°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)