

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C05D010 FEU4C059030 F4LC-CSSQ-MMS**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.



Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C05D010 FEU4C059030 F4LC-CSSQ-MMS
 Description: 4 INCH 500 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 3000K, 90CRI LEDS AND F4LC-CSSQ TRIM WITH MMS FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 525.0 lumens
 Efficiency: N/A
 Efficacy: 72.9 lumens/watt
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 7.2
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C05D010 FEU4C059030 F4LC-CSSQ-MMS

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: FLDSQ4C05D010 FEU4C059030 F4LC-CSSQ-MMS

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96		97	95	94		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	74	71		77	73	69	67
4	88	77	70	64	86	76	69	63	74	67	63		71	66	62		69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55		65	59	54		63	58	54	52
6	75	63	55	49	73	62	55	49	61	54	49		59	53	48		57	52	48	46
7	70	58	50	44	68	57	49	44	55	49	44		54	48	43		53	47	43	41
8	65	53	45	40	64	52	45	39	51	44	39		50	44	39		49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36		46	40	35		45	39	35	33
10	57	45	38	33	56	44	37	33	44	37	32		43	37	32		42	36	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23717	23717	23717
5°	23333	23633	23701
10°	23534	23466	23564
15°	23125	23155	23225
20°	22580	22939	22836
25°	22485	22485	22634
30°	21860	22016	22049
35°	21179	21379	21014
40°	20178	20581	20405
45°	19104	19527	18913
50°	16827	18283	16722
55°	13626	16738	13677
60°	9977	13875	9765
65°	6050	9886	5890
70°	2370	5332	2257
75°	261	1417	261
80°	222	222	222
85°	0	0	0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C05D010 FEU4C059030 F4LC-CSSQ-MMS

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.2	4.4
10°-20°	65.6	12.5
20°-30°	97.4	18.6
30°-40°	112.9	21.5
40°-50°	108.2	20.6
50°-60°	79.6	15.2
60°-70°	34.4	6.5
70°-80°	3.7	0.7
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	186.2	35.5
0°-40°	299.1	57.0
0°-60°	486.9	92.7
0°-90°	525.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	525.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	246	246	246	246	246	
5°	241	243	244	244	245	23
15°	232	233	232	232	232	65
25°	211	211	211	212	213	97
35°	180	181	182	181	178	112
45°	140	140	143	141	139	106
55°	81	89	100	89	81	73
65°	26	33	43	33	26	27
75°	1	1	4	1	1	2
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C05D010 FEU4C059030 F4LC-CSSQ-MMS

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	245.8	245.8	245.8	245.8	245.8	245.8	245.8	245.8	245.8	245.8	245.8
2.5°	244.0	246.8	247.2	245.4	244.7	243.7	246.1	244.4	245.1	244.4	244.0
5°	240.9	244.0	244.4	244.4	243.7	243.3	244.4	244.0	243.7	243.0	244.0
7.5°	239.5	241.2	243.0	240.9	241.9	241.6	244.0	243.0	242.6	242.6	241.9
10°	240.2	239.8	241.2	239.1	239.8	239.1	241.2	241.2	240.5	239.8	239.5
12.5°	234.6	237.4	237.4	237.0	236.3	235.3	237.4	238.8	236.7	236.7	236.3
15°	231.5	232.2	232.5	232.5	232.2	232.9	233.9	232.5	232.9	231.1	231.8
17.5°	228.0	226.6	227.6	226.9	227.3	228.0	229.4	229.4	227.3	226.9	227.6
20°	219.9	224.1	224.5	222.4	222.7	222.7	225.2	223.1	224.5	222.7	223.4
22.5°	216.1	218.9	219.2	216.4	218.2	216.1	218.5	215.4	218.9	216.4	217.5
25°	211.2	210.9	211.9	210.5	210.9	210.9	212.6	211.2	212.3	210.9	211.2
27.5°	203.2	206.0	205.6	204.2	204.9	204.6	208.1	204.2	206.3	204.6	205.3
30°	196.2	198.6	197.9	196.5	196.5	195.5	199.3	198.3	197.9	197.9	197.6
32.5°	189.2	189.6	188.9	189.2	189.6	188.2	191.3	189.9	189.6	189.9	190.3
35°	179.8	179.8	180.5	179.4	180.8	180.8	183.6	181.9	181.5	180.5	181.5
37.5°	171.4	170.4	170.7	170.7	171.4	172.1	173.5	172.8	172.8	171.8	172.5
40°	160.2	159.5	160.6	160.6	161.6	161.6	163.0	162.3	163.4	163.4	163.4
42.5°	150.5	150.5	149.8	150.8	151.2	150.8	153.3	152.9	153.3	152.6	152.9
45°	140.0	140.0	139.3	138.9	140.7	140.3	143.1	142.1	143.5	142.8	143.1
47.5°	125.7	127.4	126.4	127.4	129.5	129.9	131.6	130.9	132.3	131.3	132.7
50°	112.1	112.1	113.1	114.5	116.6	117.0	119.0	120.4	121.1	121.5	121.8
52.5°	97.8	97.4	98.4	100.2	101.9	103.3	105.4	107.5	108.9	111.0	110.0
55°	81.0	81.7	82.7	84.8	87.6	89.4	91.1	93.9	96.4	97.4	99.5
57.5°	66.7	66.0	66.7	69.5	72.6	74.0	76.5	79.2	82.7	84.8	85.5
60°	51.7	52.0	52.7	55.2	57.6	59.7	60.7	65.3	68.4	70.5	71.9
62.5°	38.1	38.8	39.5	41.5	44.0	45.7	47.5	51.3	54.1	56.2	57.6
65°	26.5	26.9	27.9	29.0	31.4	33.2	34.6	37.7	40.5	42.2	43.3
67.5°	16.4	16.8	17.4	18.9	20.6	22.0	23.4	25.5	27.9	29.7	30.0
70°	8.4	8.7	9.1	10.1	11.5	12.2	13.3	15.0	16.8	18.1	18.9
72.5°	2.8	2.8	3.1	3.8	4.5	5.2	5.6	7.3	8.7	9.4	9.8
75°	0.7	0.7	0.7	0.7	0.7	1.1	1.1	2.1	2.8	3.5	3.8
77.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.7	0.7
80°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C05D010 FEU4C059030 F4LC-CSSQ-MMS

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	245.8	245.8	245.8	245.8	245.8	245.8	245.8	245.8	245.8	245.8
2.5°	245.8	245.1	244.7	245.1	245.1	244.7	245.8	247.2	248.9	244.4
5°	245.4	244.7	245.4	243.3	244.4	243.7	245.1	244.7	246.1	244.7
7.5°	244.4	243.0	243.3	242.3	243.7	241.9	243.0	245.1	243.7	241.6
10°	240.9	240.2	242.6	239.1	238.4	239.8	242.6	240.5	239.8	240.5
12.5°	237.4	237.4	238.4	235.6	236.0	236.7	238.1	236.7	237.4	239.1
15°	233.5	232.9	234.6	232.5	232.2	231.5	232.9	232.9	233.5	232.5
17.5°	229.0	228.0	228.0	227.3	226.9	228.7	229.4	229.7	230.1	228.7
20°	223.4	223.1	224.1	223.1	223.4	223.8	223.8	223.1	226.2	222.4
22.5°	217.5	218.5	217.1	216.4	217.1	217.8	217.8	218.2	217.5	216.8
25°	211.6	212.3	212.6	210.5	211.6	210.5	213.0	213.3	211.9	212.6
27.5°	206.3	205.3	204.9	203.5	204.2	203.9	204.2	204.2	206.3	203.5
30°	198.3	197.2	197.6	196.5	196.9	196.5	196.9	196.9	198.3	197.9
32.5°	190.6	189.6	189.9	188.9	188.9	189.2	188.5	188.5	189.6	188.9
35°	183.3	180.8	181.2	180.8	181.2	179.8	179.8	179.4	180.1	178.4
37.5°	172.8	171.8	171.4	171.1	171.4	170.7	171.4	170.4	171.4	170.0
40°	163.4	162.7	163.0	160.9	160.9	161.3	160.6	160.2	160.6	162.0
42.5°	154.0	152.6	151.9	151.2	151.5	150.5	150.1	149.4	150.1	148.7
45°	142.8	142.8	142.4	140.7	141.0	141.0	139.6	138.2	138.6	138.6
47.5°	132.7	132.0	131.6	129.9	129.5	129.2	127.8	126.7	126.7	125.7
50°	121.5	120.8	119.7	118.0	117.3	115.2	114.2	112.8	111.4	111.4
52.5°	111.0	108.6	107.2	104.4	103.3	102.3	99.5	98.4	97.4	96.4
55°	98.4	96.4	93.6	90.4	89.0	87.3	84.5	82.4	81.0	81.3
57.5°	86.2	82.7	79.9	75.8	74.0	73.0	70.2	67.4	66.0	66.0
60°	71.2	68.4	64.9	61.1	59.7	58.0	54.5	52.7	51.7	50.6
62.5°	56.9	54.8	51.7	46.8	45.7	44.0	41.5	39.5	38.4	38.4
65°	42.6	40.5	37.7	34.2	32.8	31.4	29.3	27.2	26.2	25.8
67.5°	30.0	27.6	25.1	22.3	21.3	20.6	18.5	17.1	16.4	16.1
70°	18.1	16.8	15.0	12.9	11.9	11.2	9.8	8.7	8.4	8.0
72.5°	9.4	8.4	7.0	5.6	4.9	4.2	3.5	2.8	2.4	2.4
75°	3.5	2.8	1.8	1.1	0.7	0.7	0.7	0.7	0.7	0.7
77.5°	0.7	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
80°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)