

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C08D010 FEU4C089040 F4LC-SQLWW-H**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.



Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C08D010 FEU4C089040 F4LC-SQLWW-H
 Description: 4 INCH 800 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 4000K, 90CRI LEDS AND F4LC-SQLWW TRIM WITH H FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 585.0 lumens
 Efficiency: N/A
 Efficacy: 59.1 lumens/watt
 Spacing Criteria (0/90/45): 1.01 / 1 / 1.06
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 9.9
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C08D010 FEU4C089040 F4LC-SQLWW-H

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: FLDSQ4C08D010 FEU4C089040 F4LC-SQLWW-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	98		98	96	95		95	93	92	90
2	104	98	93	89	102	96	92	88	93	89	86		90	87	84		87	84	82	80
3	97	89	83	78	95	88	82	77	85	80	76		82	78	75		80	77	74	72
4	91	81	74	69	89	80	74	69	78	72	68		76	71	67		74	70	66	64
5	85	75	67	62	83	74	67	62	72	66	61		70	65	60		68	64	60	58
6	80	69	61	56	78	68	61	56	66	60	55		65	59	55		63	58	54	53
7	75	63	56	51	73	63	56	51	61	55	50		60	54	50		59	54	50	48
8	70	59	52	47	69	58	51	46	57	51	46		56	50	46		55	50	46	44
9	66	55	48	43	65	54	47	43	53	47	43		52	46	42		51	46	42	41
10	62	51	44	40	61	51	44	40	50	44	39		49	43	39		48	43	39	38

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	39377	39377	39377
5°	41658	38917	36825
10°	43296	37545	33949
15°	42434	35831	31336
20°	41052	34121	28843
25°	38295	31726	26307
30°	34572	28077	23553
35°	28470	24041	19542
40°	23239	18554	15039
45°	19963	14096	10821
50°	18073	10733	6830
55°	16620	7738	2473
60°	15959	5288	386
65°	15411	3585	114
70°	13795	2483	141
75°	11296	1268	0
80°	7057	556	0
85°	0	0	0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C08D010 FEU4C089040 F4LC-SQLWW-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.2	6.5
10°-20°	103.0	17.6
20°-30°	137.6	23.5
30°-40°	130.6	22.3
40°-50°	90.3	15.4
50°-60°	49.9	8.5
60°-70°	24.8	4.2
70°-80°	9.8	1.7
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	278.8	47.7
0°-40°	409.4	70.0
0°-60°	549.6	93.9
0°-90°	585.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	585.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	408	408	408	408	408	
5°	430	426	402	384	380	41
15°	425	412	359	324	314	120
25°	360	358	298	247	247	164
35°	242	267	204	168	166	151
45°	146	168	103	85	79	114
55°	99	93	46	24	15	89
65°	68	49	16	0	0	66
75°	30	19	3	0	0	32
85°	0	0	0	0	0	3
90°	0	0	0	0	0	

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C08D010 FEU4C089040 F4LC-SQLWW-H

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1
2.5°	406.2	417.4	418.4	417.4	418.9	418.4	420.8	418.4	421.3	416.9	417.9
5°	430.1	425.7	435.0	430.1	430.1	429.7	428.2	427.7	429.7	423.3	426.2
7.5°	436.5	442.9	451.2	440.9	441.4	441.4	438.5	437.5	437.5	425.7	429.2
10°	441.9	438.0	442.4	438.5	441.9	441.4	443.3	437.0	441.4	434.5	434.0
12.5°	437.5	436.0	441.9	435.5	433.6	434.0	431.6	430.1	431.6	423.8	423.3
15°	424.8	426.2	435.0	428.2	427.2	426.2	423.3	418.4	422.3	411.5	412.0
17.5°	420.4	417.9	419.4	413.5	415.0	414.0	413.5	409.1	408.1	401.3	401.3
20°	399.8	405.2	405.2	401.3	401.3	400.8	394.4	398.3	393.9	392.0	393.9
22.5°	385.6	386.1	386.1	382.7	383.2	381.2	377.8	375.3	377.8	375.3	371.4
25°	359.7	360.7	366.5	360.2	359.2	361.1	358.2	356.7	356.2	350.4	358.2
27.5°	328.4	338.1	337.7	335.2	338.1	334.2	332.8	333.2	334.7	334.2	336.2
30°	310.3	311.7	313.2	311.2	311.7	310.3	310.3	310.7	314.6	313.2	312.7
32.5°	273.5	278.4	282.4	282.4	282.8	284.3	283.8	294.1	296.5	291.7	290.7
35°	241.7	245.2	248.6	249.1	255.4	255.9	256.4	259.4	266.2	267.7	267.2
37.5°	211.4	214.8	215.8	220.2	223.6	227.1	231.0	234.9	240.8	245.6	243.2
40°	184.5	185.9	188.4	190.4	197.2	197.2	199.2	207.0	213.4	217.3	216.8
42.5°	162.0	162.5	164.4	167.8	174.2	172.7	174.2	179.6	188.9	189.4	194.8
45°	146.3	145.8	147.3	147.8	151.7	153.7	154.6	158.6	166.4	167.4	167.8
47.5°	132.1	131.6	134.1	135.1	136.5	138.5	138.5	139.0	141.9	144.4	142.4
50°	120.4	120.4	120.4	121.4	123.8	123.3	123.8	125.8	127.2	126.2	125.8
52.5°	107.6	109.6	111.1	111.6	112.1	112.1	112.6	111.6	111.1	109.6	106.7
55°	98.8	100.8	100.8	100.8	100.8	102.8	100.3	100.8	100.8	96.9	93.0
57.5°	90.0	92.0	93.5	91.5	93.5	91.5	90.5	90.0	89.1	85.1	79.3
60°	82.7	83.7	83.2	82.7	83.7	82.2	81.2	79.3	78.3	72.9	69.0
62.5°	74.4	74.9	75.4	74.4	73.4	72.9	71.0	68.0	66.1	61.7	58.2
65°	67.5	66.1	65.6	65.1	64.1	62.6	61.2	57.7	56.3	52.4	48.9
67.5°	57.2	56.8	57.7	56.3	53.8	53.8	52.4	49.4	46.0	43.6	40.1
70°	48.9	48.4	47.5	46.0	45.5	43.6	43.6	40.1	39.1	34.7	31.8
72.5°	40.1	40.1	38.7	37.2	35.7	34.7	34.3	31.8	30.3	27.9	25.4
75°	30.3	30.3	29.9	28.4	27.4	26.4	25.9	24.0	22.5	20.1	18.6
77.5°	21.5	21.5	19.6	18.6	19.1	18.1	17.1	16.6	16.1	14.7	12.7
80°	12.7	12.2	10.8	11.3	10.8	10.8	10.3	9.8	8.8	7.8	6.8
82.5°	3.4	3.9	3.9	3.9	4.4	3.4	3.4	3.4	3.9	3.9	2.5
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.5	0.5	0.5
87.5°	0.5	1.0	2.0	2.0	2.0	2.0	2.0	1.5	1.5	1.5	1.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C08D010 FEU4C089040 F4LC-SQLWW-H

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°	95°
0°	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1
2.5°	413.0	412.5	413.0	409.6	417.4	411.5	410.6	409.6	413.0	409.6	404.7
5°	421.8	416.9	415.5	414.0	418.4	411.5	410.1	410.6	408.1	401.8	402.2
7.5°	424.8	420.4	416.0	406.7	410.6	409.1	405.2	402.2	398.3	392.9	392.0
10°	425.7	420.8	414.5	411.5	405.7	403.7	402.2	397.4	392.5	383.2	380.7
12.5°	422.8	416.9	409.1	406.7	402.2	395.9	392.5	387.6	383.2	375.8	370.4
15°	410.1	405.2	402.7	394.4	392.5	388.5	381.7	374.8	368.5	358.7	355.8
17.5°	395.4	393.4	391.0	384.6	384.1	380.2	373.9	368.0	359.7	344.5	339.6
20°	380.2	380.2	372.4	370.0	374.8	367.0	362.1	356.7	339.6	332.3	323.5
22.5°	369.0	363.6	359.2	355.3	355.8	350.9	344.0	333.2	326.9	318.1	307.8
25°	347.0	348.9	339.1	337.7	339.1	327.9	324.4	315.6	306.3	298.0	290.2
27.5°	333.2	327.9	321.5	316.1	316.1	311.7	301.9	300.0	285.8	278.0	268.2
30°	312.7	308.8	303.4	295.6	294.6	291.2	283.3	278.4	263.8	252.0	246.6
32.5°	286.8	285.3	280.9	272.1	269.2	265.2	255.4	247.1	240.3	227.1	220.7
35°	268.2	262.8	253.5	246.1	243.7	236.8	229.0	223.1	215.8	204.1	195.7
37.5°	240.3	234.9	226.1	217.3	217.3	210.4	199.7	193.8	183.5	176.6	169.8
40°	215.8	209.0	200.2	189.9	188.4	178.6	174.2	164.4	158.1	147.3	146.3
42.5°	188.4	182.0	174.2	166.4	160.5	155.6	144.4	137.0	130.2	124.8	123.3
45°	163.4	155.1	148.3	138.5	132.6	126.7	119.4	114.5	109.1	103.3	99.8
47.5°	141.9	135.1	125.3	116.5	110.6	107.6	99.3	94.0	89.6	85.6	83.2
50°	119.9	111.6	106.2	96.4	95.4	88.6	81.7	77.3	74.9	71.5	68.0
52.5°	103.3	95.4	88.1	80.8	76.8	74.4	68.0	63.6	60.2	57.7	55.8
55°	87.1	80.3	74.4	67.0	64.6	61.2	53.8	52.9	49.4	46.0	43.6
57.5°	74.9	68.5	61.7	56.8	52.4	49.9	44.0	40.1	38.2	35.2	32.8
60°	63.6	56.8	51.4	45.5	43.6	40.1	35.7	32.3	29.9	27.4	25.0
62.5°	53.3	47.5	41.6	36.7	33.8	31.8	28.4	25.4	23.0	21.1	19.1
65°	44.0	38.7	33.8	28.9	27.4	25.0	22.5	20.1	18.1	15.7	13.7
67.5°	36.2	31.3	26.4	23.0	21.5	20.6	17.6	15.2	13.7	12.2	10.3
70°	28.4	25.0	21.1	18.1	16.6	15.2	13.2	11.8	9.8	8.8	7.3
72.5°	22.0	19.1	15.7	13.2	12.2	11.3	9.3	7.8	6.8	5.9	4.9
75°	15.7	13.2	11.3	8.8	8.3	7.8	6.4	5.4	4.4	3.4	2.9
77.5°	10.8	8.8	6.8	5.9	5.4	4.4	3.9	2.9	2.5	2.0	1.5
80°	5.9	4.4	3.4	2.9	2.5	2.0	2.0	1.5	1.0	1.0	0.5
82.5°	2.0	1.5	1.0	0.5	0.5	0.5	0.5	0.5	0.5	0.0	0.5
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C08D010 FEU4C089040 F4LC-SQLWW-H

CANDELA DISTRIBUTION (continued):

	100°	105°	110°	112.5°	115°	120°	125°	130°	135°	140°	145°
0°	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1
2.5°	407.6	402.2	403.7	403.7	402.7	402.7	401.8	400.3	400.8	397.8	391.5
5°	403.2	396.4	395.4	396.4	392.5	391.5	389.5	392.5	383.6	387.1	383.2
7.5°	390.5	384.1	382.7	386.1	381.2	378.3	377.8	381.7	373.9	370.0	365.5
10°	376.3	373.9	369.5	367.0	365.5	366.0	362.1	357.2	355.8	354.8	350.9
12.5°	363.6	358.2	354.3	351.4	350.4	350.4	344.0	343.0	338.6	337.7	331.8
15°	348.4	342.1	339.6	335.7	332.3	334.2	326.9	324.9	323.5	317.1	318.1
17.5°	335.2	328.4	322.5	320.0	317.1	314.2	307.3	308.8	305.3	305.3	296.5
20°	318.1	310.7	306.3	301.4	301.4	297.5	292.6	293.1	288.7	284.3	276.5
22.5°	300.0	292.1	286.8	284.8	279.9	278.9	273.1	271.6	265.7	266.2	259.4
25°	280.9	273.1	265.7	266.2	261.8	259.9	256.4	249.6	247.1	244.2	242.2
27.5°	258.4	253.0	246.6	246.1	237.8	238.3	233.9	232.0	226.1	227.5	223.1
30°	237.8	230.0	224.1	222.7	219.2	218.3	211.4	208.5	209.5	205.5	203.1
32.5°	216.8	205.0	202.6	199.7	197.7	195.2	190.4	192.3	187.9	188.9	185.0
35°	188.9	184.0	177.6	177.6	175.7	173.7	170.3	172.3	167.8	165.9	162.0
37.5°	165.4	161.0	154.6	156.6	153.2	150.2	147.3	147.8	143.9	143.4	139.5
40°	140.0	137.5	133.1	133.1	130.7	130.7	129.2	127.7	125.3	122.3	117.9
42.5°	116.0	114.0	112.1	112.6	109.1	112.1	108.1	110.6	102.8	102.3	99.3
45°	98.4	94.0	94.4	92.5	90.5	91.5	88.1	89.1	84.7	83.7	80.8
47.5°	79.8	78.3	75.4	74.4	74.4	72.9	71.5	71.0	69.0	66.5	62.6
50°	65.6	60.2	59.2	57.7	56.8	56.8	54.8	51.9	52.4	49.9	46.0
52.5°	51.4	47.0	45.0	44.5	42.6	41.6	39.1	37.2	35.7	34.7	32.3
55°	39.6	35.7	33.3	33.3	30.3	30.3	26.9	25.4	23.5	21.5	20.1
57.5°	29.9	27.9	25.4	23.5	22.5	20.1	18.1	15.7	14.2	11.3	9.3
60°	22.5	20.6	18.1	16.6	15.7	13.2	10.8	8.8	5.4	4.4	3.9
62.5°	16.6	14.7	12.2	11.3	10.3	8.3	5.9	2.9	1.5	1.5	1.5
65°	12.2	9.8	7.8	6.8	5.9	4.4	2.0	1.0	0.5	0.5	0.5
67.5°	8.3	6.4	4.4	3.9	2.9	1.5	0.5	0.5	0.5	0.5	0.5
70°	5.4	3.9	2.0	1.5	1.0	0.5	0.5	0.5	0.5	0.5	0.5
72.5°	3.4	2.0	1.0	0.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	2.0	1.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	1.0	0.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.5	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.5	0.5	0.5
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C08D010 FEU4C089040 F4LC-SQLWW-H

CANDELA DISTRIBUTION (continued):

	150°	155°	157.5°	160°	165°	170°	175°	180°
0°	408.1	408.1	408.1	408.1	408.1	408.1	408.1	408.1
2.5°	398.3	394.9	396.9	392.5	394.4	397.8	395.4	396.4
5°	384.6	382.7	380.2	373.9	378.8	382.7	380.7	380.2
7.5°	370.0	363.1	366.5	364.6	363.6	367.5	363.1	368.0
10°	354.8	349.9	349.4	346.0	346.0	348.9	349.4	346.5
12.5°	332.3	329.8	329.8	329.3	328.8	331.8	332.3	330.8
15°	316.1	315.1	312.7	312.2	309.3	313.7	314.2	313.7
17.5°	296.5	297.0	294.6	294.6	296.5	298.0	294.1	298.0
20°	283.3	280.9	279.9	275.5	278.0	280.4	280.4	280.9
22.5°	264.2	260.3	261.8	259.4	257.9	261.3	261.3	262.8
25°	242.7	242.7	243.7	242.2	243.2	245.2	243.7	247.1
27.5°	222.2	224.1	224.1	222.2	223.1	229.0	231.5	227.5
30°	203.1	203.6	205.0	204.1	207.0	209.0	208.5	211.4
32.5°	181.6	184.0	185.0	183.5	184.5	188.9	186.4	185.9
35°	164.9	160.5	160.0	160.5	162.5	163.4	162.5	165.9
37.5°	140.9	139.5	137.5	138.0	139.5	141.4	142.4	144.8
40°	117.9	116.0	116.0	115.5	114.0	119.4	119.4	119.4
42.5°	97.9	97.4	94.9	94.9	96.9	98.4	97.4	100.8
45°	80.3	78.3	76.8	76.8	78.3	78.3	79.8	79.3
47.5°	63.1	61.2	61.7	60.2	61.7	63.6	61.2	61.7
50°	47.5	47.5	46.5	47.5	47.0	47.5	46.5	45.5
52.5°	32.3	36.7	37.2	35.2	30.8	26.9	24.5	26.4
55°	18.6	16.6	16.6	16.1	15.2	14.7	13.2	14.7
57.5°	9.3	8.3	8.3	8.3	7.8	7.3	6.4	6.4
60°	3.9	3.4	3.4	2.9	2.5	2.0	1.5	2.0
62.5°	1.5	1.0	1.0	1.0	1.0	1.0	1.0	1.0
65°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
67.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
70°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
72.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)