

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P#

Luminaire Tested: **FLDSQ4C08D010 FEU4C089050 F4LC-DFSSQ-MW**

Issue Date: 12/13/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P#
 Test Lab: INNOVATION CENTER
 Issue Date: 12/13/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: FAIL-SAFE
 Catalog Number: FLDSQ4C08D010 FEU4C089050 F4LC-DFSSQ-MW
 Description: 4 INCH 800 LUMEN FAIL-SAFE LED DOWNLIGHT WITH, 5000K, 90CRI LEDS AND F4LC-DFSSQ TRIM WITH MW FINISH
 Light Source: -
 Ballast/Driver: -

Summary


Lumens per Lamp: N/A
 Luminaire Lumens: 894.0 lumens
 Efficiency: N/A
 Efficacy: 90.3 lumens/watt
 Spacing Criteria (0/90/45): 1.19 / 1.2 / 1.29
 Luminous Opening: Rectangular (W 0.33' x L: 0.33' x H: 0')
 CIE Type: Direct

Input Watts (W): 9.9
 Input Voltage (V):
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P#
CATALOG NUMBER: FLDSQ4C08D010 FEU4C089050 F4LC-DFSSQ-MW

Luminous Intensity Polar Plot



TEST NUMBER: P#

CATALOG NUMBER: FLDSQ4C08D010 FEU4C089050 F4LC-DFSSQ-MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	108	104	101	109	105	102	100	101	99	96		97	95	94		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	74	71		77	73	69	67
4	88	77	70	64	86	76	69	63	74	67	63		71	66	62		69	65	61	59
5	81	70	62	56	79	69	61	56	67	60	55		65	59	54		63	58	54	52
6	75	63	55	49	73	62	55	49	61	54	49		59	53	48		57	52	48	46
7	70	58	50	44	68	57	49	44	55	49	44		54	48	43		53	47	43	41
8	65	53	45	40	64	52	45	39	51	44	39		50	44	39		49	43	39	37
9	61	49	41	36	60	48	41	36	47	40	36		46	40	35		45	39	35	33
10	57	45	38	33	56	44	37	33	44	37	32		43	37	32		42	36	32	31

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	40381	40381	40381
5°	39731	40244	40361
10°	40073	39955	40132
15°	39368	39428	39548
20°	38454	39070	38885
25°	38284	38284	38540
30°	37224	37491	37558
35°	36056	36409	35785
40°	34374	35041	34739
45°	32531	33254	32204
50°	28641	31148	28461
55°	23198	28497	23299
60°	16982	23640	16635
65°	10320	16827	10046
70°	4034	9056	3865
75°	447	2423	447
80°	333	333	333
85°	0	0	0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C08D010 FEU4C089050 F4LC-DFSSQ-MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.5	4.4
10°-20°	111.8	12.5
20°-30°	165.9	18.6
30°-40°	192.2	21.5
40°-50°	184.3	20.6
50°-60°	135.5	15.2
60°-70°	58.5	6.5
70°-80°	6.3	0.7
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	317.2	35.5
0°-40°	509.3	57.0
0°-60°	829.1	92.7
0°-90°	894.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	894.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	418	418	418	418	418	
5°	410	414	416	416	417	39
15°	394	396	395	395	396	111
25°	360	359	360	360	362	165
35°	306	308	309	308	304	191
45°	238	239	244	240	236	181
55°	138	152	169	152	138	124
65°	45	56	74	56	44	46
75°	1	2	6	1	1	4
85°	0	0	0	0	0	0
90°	0	0	0	0	0	

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C08D010 FEU4C089050 F4LC-DFSSQ-MW

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	25°	30°	35°	40°	45°
0°	418.5	418.5	418.5	418.5	418.5	418.5	418.5	418.5	418.5	418.5	418.5
2.5°	415.5	420.3	420.9	417.9	416.7	414.9	419.1	416.1	417.3	416.1	415.5
5°	410.2	415.5	416.1	416.1	414.9	414.3	416.1	415.5	414.9	413.8	415.5
7.5°	407.8	410.8	413.8	410.2	412.0	411.4	415.5	413.8	413.1	413.1	412.0
10°	409.0	408.4	410.8	407.2	408.4	407.2	410.8	410.8	409.6	408.4	407.8
12.5°	399.5	404.2	404.2	403.6	402.5	400.7	404.2	406.6	403.0	403.0	402.5
15°	394.1	395.3	395.9	395.9	395.3	396.5	398.3	395.9	396.5	393.5	394.7
17.5°	388.2	385.8	387.6	386.4	387.0	388.2	390.6	390.6	387.0	386.4	387.6
20°	374.5	381.6	382.2	378.7	379.3	379.3	383.4	379.9	382.2	379.3	380.5
22.5°	368.0	372.7	373.3	368.6	371.5	368.0	372.1	366.8	372.7	368.6	370.3
25°	359.6	359.1	360.8	358.5	359.1	359.1	362.0	359.6	361.4	359.1	359.6
27.5°	346.0	350.7	350.1	347.8	348.9	348.4	354.3	347.8	351.3	348.4	349.6
30°	334.1	338.3	337.1	334.7	334.7	332.9	339.4	337.6	337.1	337.1	336.5
32.5°	322.2	322.8	321.6	322.2	322.8	320.4	325.8	323.4	322.8	323.4	324.0
35°	306.1	306.1	307.3	305.6	307.9	307.9	312.7	309.7	309.1	307.3	309.1
37.5°	291.9	290.1	290.7	290.7	291.9	293.1	295.4	294.3	294.3	292.5	293.7
40°	272.9	271.7	273.4	273.4	275.2	275.2	277.6	276.4	278.2	278.2	278.2
42.5°	256.2	256.2	255.0	256.8	257.4	256.8	261.0	260.4	261.0	259.8	260.4
45°	238.4	238.4	237.2	236.6	239.6	239.0	243.7	241.9	244.3	243.1	243.7
47.5°	214.0	217.0	215.2	217.0	220.5	221.2	224.1	222.9	225.3	223.5	225.9
50°	190.8	190.8	192.6	195.0	198.5	199.2	202.7	205.1	206.3	206.9	207.5
52.5°	166.5	165.9	167.6	170.6	173.6	176.0	179.5	183.1	185.5	189.0	187.2
55°	137.9	139.1	140.9	144.5	149.2	152.2	155.2	159.9	164.1	165.9	169.4
57.5°	113.5	112.3	113.5	118.3	123.6	126.0	130.2	135.0	140.9	144.5	145.6
60°	88.0	88.6	89.8	93.9	98.1	101.7	103.4	111.2	116.5	120.1	122.5
62.5°	64.8	66.0	67.2	70.7	74.9	77.9	80.8	87.4	92.1	95.7	98.1
65°	45.2	45.8	47.6	49.3	53.5	56.5	58.8	64.2	69.0	71.9	73.7
67.5°	27.9	28.5	29.7	32.1	35.1	37.4	39.8	43.4	47.6	50.5	51.1
70°	14.3	14.9	15.5	17.2	19.6	20.8	22.6	25.6	28.5	30.9	32.1
72.5°	4.8	4.8	5.4	6.5	7.7	8.9	9.5	12.5	14.9	16.1	16.6
75°	1.2	1.2	1.2	1.2	1.2	1.8	1.8	3.6	4.8	5.9	6.5
77.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	1.2	1.2
80°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P#
 CATALOG NUMBER: FLDSQ4C08D010 FEU4C089050 F4LC-DFSSQ-MW

CANDELA DISTRIBUTION (continued):

	50°	55°	60°	65°	67.5°	70°	75°	80°	85°	90°
0°	418.5	418.5	418.5	418.5	418.5	418.5	418.5	418.5	418.5	418.5
2.5°	418.5	417.3	416.7	417.3	417.3	416.7	418.5	420.9	423.8	416.1
5°	417.9	416.7	417.9	414.3	416.1	414.9	417.3	416.7	419.1	416.7
7.5°	416.1	413.8	414.3	412.6	414.9	412.0	413.8	417.3	414.9	411.4
10°	410.2	409.0	413.1	407.2	406.0	408.4	413.1	409.6	408.4	409.6
12.5°	404.2	404.2	406.0	401.3	401.8	403.0	405.4	403.0	404.2	407.2
15°	397.7	396.5	399.5	395.9	395.3	394.1	396.5	396.5	397.7	395.9
17.5°	390.0	388.2	388.2	387.0	386.4	389.4	390.6	391.2	391.8	389.4
20°	380.5	379.9	381.6	379.9	380.5	381.1	381.1	379.9	385.2	378.7
22.5°	370.3	372.1	369.8	368.6	369.8	370.9	370.9	371.5	370.3	369.2
25°	360.3	361.4	362.0	358.5	360.3	358.5	362.6	363.2	360.8	362.0
27.5°	351.3	349.6	348.9	346.6	347.8	347.2	347.8	347.8	351.3	346.6
30°	337.6	335.9	336.5	334.7	335.3	334.7	335.3	335.3	337.6	337.1
32.5°	324.6	322.8	323.4	321.6	321.6	322.2	321.0	321.0	322.8	321.6
35°	312.1	307.9	308.5	307.9	308.5	306.1	306.1	305.6	306.7	303.8
37.5°	294.3	292.5	291.9	291.3	291.9	290.7	291.9	290.1	291.9	289.5
40°	278.2	277.0	277.6	274.1	274.1	274.6	273.4	272.9	273.4	275.8
42.5°	262.2	259.8	258.6	257.4	258.0	256.2	255.6	254.4	255.6	253.2
45°	243.1	243.1	242.5	239.6	240.2	240.2	237.8	235.4	236.0	236.0
47.5°	225.9	224.7	224.1	221.2	220.5	220.0	217.6	215.8	215.8	214.0
50°	206.9	205.7	203.9	200.9	199.7	196.2	194.4	192.0	189.6	189.6
52.5°	189.0	184.9	182.5	177.7	176.0	174.2	169.4	167.6	165.9	164.1
55°	167.6	164.1	159.3	154.0	151.6	148.6	143.9	140.3	137.9	138.5
57.5°	146.8	140.9	136.1	129.0	126.0	124.2	119.5	114.7	112.3	112.3
60°	121.3	116.5	110.6	104.0	101.7	98.7	92.7	89.8	88.0	86.2
62.5°	96.9	93.3	88.0	79.7	77.9	74.9	70.7	67.2	65.4	65.4
65°	72.5	69.0	64.2	58.3	55.9	53.5	49.9	46.4	44.6	44.0
67.5°	51.1	47.0	42.8	38.1	36.3	35.1	31.5	29.1	27.9	27.3
70°	30.9	28.5	25.6	22.0	20.2	19.0	16.6	14.9	14.3	13.7
72.5°	16.1	14.3	11.9	9.5	8.3	7.1	5.9	4.8	4.2	4.2
75°	5.9	4.8	3.0	1.8	1.2	1.2	1.2	1.2	1.2	1.2
77.5°	1.2	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
80°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

(END OF REPORT)