

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P726574

Luminaire Tested: **MRI-DRV-FLD4C-10-L930 F4LC-N-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P726574
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD4C-10-L930 F4LC-N-X-H
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3000K, 90 CRI
LEDS, 4LBNH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 629.9 lumens
Efficiency: N/A
Efficacy: 64.6 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P726574
CATALOG NUMBER: MRI-DRV-FLD4C-10-L930 F4LC-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P726574

CATALOG NUMBER: MRI-DRV-FLD4C-10-L930 F4LC-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93	93	93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87	87	87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	81	81
4	97	90	84	80	95	89	83	79	86	82	79	84	81	78	83	79	77	75	75	75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70	70	70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65	65	65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61	61	61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58	58	58
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54	54	54
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51	51	51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	97177
5°	95008
10°	87848
15°	78831
20°	69396
25°	59711
30°	48090
35°	32020
40°	16647
45°	7540
50°	3268
55°	2185
60°	1401
65°	988
70°	826
75°	522
80°	0
85°	0



TEST NUMBER: P726574
 CATALOG NUMBER: MRI-DRV-FLD4C-10-L930 F4LC-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	71.4	11.3
10°-20°	173.1	27.5
20°-30°	201.0	31.9
30°-40°	133.1	21.1
40°-50°	37.3	5.9
50°-60°	9.4	1.5
60°-70°	3.5	0.6
70°-80°	1.2	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	445.5	70.7
0°-40°	578.6	91.8
0°-60°	625.3	99.3
0°-90°	629.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	629.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	791	
5°	770	71
15°	620	173
25°	440	201
35°	214	133
45°	43	37
55°	10	9
65°	3	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P726574
CATALOG NUMBER: MRI-DRV-FLD4C-10-L930 F4LC-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	791.0
2.5°	787.6
5°	770.4
7.5°	740.7
10°	704.2
12.5°	663.1
15°	619.8
17.5°	577.5
20°	530.8
22.5°	487.4
25°	440.5
27.5°	396.1
30°	339.0
32.5°	278.5
35°	213.5
37.5°	153.0
40°	103.8
42.5°	67.3
45°	43.4
47.5°	26.3
50°	17.1
52.5°	12.5
55°	10.2
57.5°	8.0
60°	5.7
62.5°	4.6
65°	3.4
67.5°	2.3
70°	2.3
72.5°	1.1
75°	1.1
77.5°	1.1
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)