

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P726592

Luminaire Tested: **MRI-DRV-FLD4C-10-L930 F4LC-W-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P726592
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208077)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD4C-10-L930 F4LC-W-X-LI
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3000K, 90 CRI
LEDS, 4LBWLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 998.0 lumens
Efficiency: N/A
Efficacy: 102.4 lumens/watt
Spacing Criteria (0/90/45): 1.29 / 1.29 / 1.18
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P726592
CATALOG NUMBER: MRI-DRV-FLD4C-10-L930 F4LC-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P726592

CATALOG NUMBER: MRI-DRV-FLD4C-10-L930 F4LC-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	96	95	94	92
2	106	101	97	93	104	99	95	92	96	93	90	93	90	88	90	88	86	84
3	100	93	87	83	98	92	86	82	89	85	81	86	83	80	84	81	78	77
4	94	86	79	75	92	84	79	74	82	77	73	80	76	72	78	75	72	70
5	88	79	72	68	87	78	72	67	76	71	67	74	70	66	73	69	65	64
6	83	73	66	62	82	72	66	61	71	65	61	69	64	60	68	63	60	58
7	78	68	61	56	77	67	61	56	66	60	56	64	59	55	63	59	55	54
8	74	63	56	52	72	62	56	51	61	55	51	60	55	51	59	54	51	49
9	69	59	52	48	68	58	52	47	57	51	47	56	51	47	55	50	47	45
10	66	55	48	44	65	54	48	44	53	48	44	53	47	44	52	47	43	42

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	75125
5°	76398
10°	79852
15°	84745
20°	88457
25°	87690
30°	81555
35°	69769
40°	53164
45°	31187
50°	13321
55°	3920
60°	1130
65°	669
70°	395
75°	522
80°	0
85°	0



TEST NUMBER: P726592
 CATALOG NUMBER: MRI-DRV-FLD4C-10-L930 F4LC-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.8	6.0
10°-20°	188.7	18.9
20°-30°	294.4	29.5
30°-40°	286.5	28.7
40°-50°	143.1	14.3
50°-60°	22.1	2.2
60°-70°	2.7	0.3
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	542.9	54.4
0°-40°	829.3	83.1
0°-60°	994.6	99.7
0°-90°	998.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	998.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	612	
5°	620	60
15°	666	189
25°	647	294
35°	465	286
45°	180	143
55°	18	22
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P726592
CATALOG NUMBER: MRI-DRV-FLD4C-10-L930 F4LC-W-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	611.5
2.5°	613.8
5°	619.5
7.5°	628.6
10°	640.1
12.5°	654.9
15°	666.3
17.5°	675.5
20°	676.6
22.5°	668.6
25°	646.9
27.5°	614.9
30°	574.9
32.5°	524.7
35°	465.2
37.5°	400.0
40°	331.5
42.5°	258.3
45°	179.5
47.5°	115.4
50°	69.7
52.5°	37.7
55°	18.3
57.5°	8.0
60°	4.6
62.5°	3.4
65°	2.3
67.5°	2.3
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)