

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P726604

Luminaire Tested: **MRI-DRV-FLD4C-10-L935 F4LC-M-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P726604
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD4C-10-L935 F4LC-M-X-LI
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI
LEDS, 4LBMLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 959.0 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P726604
CATALOG NUMBER: MRI-DRV-FLD4C-10-L935 F4LC-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P726604
 CATALOG NUMBER: MRI-DRV-FLD4C-10-L935 F4LC-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	147436
5°	146039
10°	138384
15°	125636
20°	111023
25°	95986
30°	75029
35°	46013
40°	23623
45°	9382
50°	3039
55°	1050
60°	909
65°	727
70°	431
75°	570
80°	0
85°	0



TEST NUMBER: P726604
 CATALOG NUMBER: MRI-DRV-FLD4C-10-L935 F4LC-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	110.6	11.5
10°-20°	275.3	28.7
20°-30°	320.0	33.4
30°-40°	195.9	20.4
40°-50°	48.7	5.1
50°-60°	5.7	0.6
60°-70°	2.1	0.2
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	705.8	73.6
0°-40°	901.7	94.0
0°-60°	956.1	99.7
0°-90°	959.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	959.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1200	
5°	1184	111
15°	988	275
25°	708	320
35°	307	196
45°	54	49
55°	5	6
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P726604
CATALOG NUMBER: MRI-DRV-FLD4C-10-L935 F4LC-M-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1200.1
2.5°	1198.9
5°	1184.2
7.5°	1152.3
10°	1109.3
12.5°	1052.9
15°	987.8
17.5°	917.9
20°	849.2
22.5°	780.4
25°	708.1
27.5°	624.6
30°	528.9
32.5°	417.2
35°	306.8
37.5°	216.0
40°	147.3
42.5°	92.0
45°	54.0
47.5°	30.7
50°	15.9
52.5°	7.4
55°	4.9
57.5°	3.7
60°	3.7
62.5°	2.5
65°	2.5
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)