

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P726688

Luminaire Tested: **MRI-DRV-FLD4C-10-L950 F4LC-N-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P726688
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD4C-10-L950 F4LC-N-X-LI
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 5000K, 90 CRI
LEDS, 4LBNLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 769.0 lumens
Efficiency: N/A
Efficacy: 78.9 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P726688
CATALOG NUMBER: MRI-DRV-FLD4C-10-L950 F4LC-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P726688

CATALOG NUMBER: MRI-DRV-FLD4C-10-L950 F4LC-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	243127
5°	218787
10°	169608
15°	122761
20°	85006
25°	61962
30°	45026
35°	26651
40°	11210
45°	3492
50°	459
55°	257
60°	295
65°	349
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P726688
 CATALOG NUMBER: MRI-DRV-FLD4C-10-L950 F4LC-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	156.0	20.3
10°-20°	267.0	34.7
20°-30°	212.2	27.6
30°-40°	112.3	14.6
40°-50°	19.4	2.5
50°-60°	1.5	0.2
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	635.1	82.6
0°-40°	747.5	97.2
0°-60°	768.3	99.9
0°-90°	769.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	769.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1979	
5°	1774	156
15°	965	267
25°	457	212
35°	178	112
45°	20	19
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P726688
CATALOG NUMBER: MRI-DRV-FLD4C-10-L950 F4LC-N-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1979.0
2.5°	1928.0
5°	1774.1
7.5°	1572.8
10°	1359.6
12.5°	1153.5
15°	965.2
17.5°	789.9
20°	650.2
22.5°	543.6
25°	457.1
27.5°	387.3
30°	317.4
32.5°	246.3
35°	177.7
37.5°	117.3
40°	69.9
42.5°	40.3
45°	20.1
47.5°	7.1
50°	2.4
52.5°	2.4
55°	1.2
57.5°	1.2
60°	1.2
62.5°	1.2
65°	1.2
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)