

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P726838

Luminaire Tested: **MRI-DRV-FLD4C-15-L940 F4LC-W-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P726838
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD4C-15-L940 F4LC-W-X-H
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 4000K, 90 CRI
LEDS, 4LBWH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1311.1 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P726838
CATALOG NUMBER: MRI-DRV-FLD4C-15-L940 F4LC-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P726838
 CATALOG NUMBER: MRI-DRV-FLD4C-15-L940 F4LC-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91	91	91	91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82	82	82	82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74	74	74	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67	67	67	67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61	61	61	61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55	55	55	55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50	50	50	50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46	46	46	46
9	67	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43	43	43	43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39	39	39	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	103811
5°	104208
10°	104527
15°	104535
20°	103963
25°	101516
30°	94889
35°	82172
40°	64198
45°	46059
50°	29911
55°	17906
60°	10492
65°	6715
70°	4490
75°	3370
80°	2547
85°	0



TEST NUMBER: P726838
 CATALOG NUMBER: MRI-DRV-FLD4C-15-L940 F4LC-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	80.5	6.1
10°-20°	231.9	17.7
20°-30°	342.1	26.1
30°-40°	337.7	25.8
40°-50°	206.6	15.8
50°-60°	79.2	6.0
60°-70°	24.8	1.9
70°-80°	7.3	0.6
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	654.5	49.9
0°-40°	992.2	75.7
0°-60°	1278.0	97.5
0°-90°	1311.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1311.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	845	
5°	845	80
15°	822	232
25°	749	342
35°	548	338
45°	265	207
55°	84	79
65°	23	25
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P726838
CATALOG NUMBER: MRI-DRV-FLD4C-15-L940 F4LC-W-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	845.0
2.5°	846.8
5°	845.0
7.5°	843.2
10°	837.9
12.5°	830.8
15°	821.9
17.5°	811.2
20°	795.2
22.5°	777.4
25°	748.9
27.5°	713.3
30°	668.9
32.5°	613.8
35°	547.9
37.5°	475.0
40°	400.3
42.5°	330.9
45°	265.1
47.5°	206.3
50°	156.5
52.5°	115.7
55°	83.6
57.5°	58.7
60°	42.7
62.5°	32.1
65°	23.1
67.5°	17.8
70°	12.5
72.5°	8.9
75°	7.1
77.5°	3.6
80°	3.6
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)