

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P726910

Luminaire Tested: **MRI-DRV-FLD4C-20-L927 F4LC-W-X-H**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P726910  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD4C-20-L927 F4LC-W-X-H  
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 2700K, 90 CRI  
LEDS, 4LBWH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1602.1 lumens  
Efficiency: N/A  
Efficacy: 73.5 lumens/watt  
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 21.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P726910  
CATALOG NUMBER: MRI-DRV-FLD4C-20-L927 F4LC-W-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P726910  
 CATALOG NUMBER: MRI-DRV-FLD4C-20-L927 F4LC-W-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10		0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102		100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93		91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84		82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76		74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69		67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62		61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57		55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52		50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48		46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44		43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41		39

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	126858
5°	127343
10°	127730
15°	127734
20°	127038
25°	124059
30°	115956
35°	100409
40°	78439
45°	56275
50°	36562
55°	21890
60°	12801
65°	8227
70°	5460
75°	4130
80°	3113
85°	0



TEST NUMBER: P726910  
 CATALOG NUMBER: MRI-DRV-FLD4C-20-L927 F4LC-W-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	98.3	6.1
10°-20°	283.3	17.7
20°-30°	418.1	26.1
30°-40°	412.6	25.8
40°-50°	252.5	15.8
50°-60°	96.8	6.0
60°-70°	30.3	1.9
70°-80°	8.9	0.6
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	799.8	49.9
0°-40°	1212.4	75.7
0°-60°	1561.7	97.5
0°-90°	1602.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1602.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1033	
5°	1033	98
15°	1004	283
25°	915	418
35°	670	413
45°	324	252
55°	102	97
65°	28	30
75°	9	9
85°	0	1
90°	0	



TEST NUMBER: P726910  
CATALOG NUMBER: MRI-DRV-FLD4C-20-L927 F4LC-W-X-H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1032.6
2.5°	1034.8
5°	1032.6
7.5°	1030.4
10°	1023.9
12.5°	1015.2
15°	1004.3
17.5°	991.2
20°	971.7
22.5°	950.0
25°	915.2
27.5°	871.7
30°	817.4
32.5°	750.0
35°	669.5
37.5°	580.4
40°	489.1
42.5°	404.3
45°	323.9
47.5°	252.1
50°	191.3
52.5°	141.3
55°	102.2
57.5°	71.7
60°	52.1
62.5°	39.2
65°	28.3
67.5°	21.8
70°	15.2
72.5°	10.9
75°	8.7
77.5°	4.4
80°	4.4
82.5°	2.2
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)