

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P726976

Luminaire Tested: **MRI-DRV-FLD4C-20-L935 F4LC-N-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P726976
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD4C-20-L935 F4LC-N-X-LI
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI
LEDS, 4LBNLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1487.0 lumens
Efficiency: N/A
Efficacy: 68.2 lumens/watt
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P726976
CATALOG NUMBER: MRI-DRV-FLD4C-20-L935 F4LC-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P726976
 CATALOG NUMBER: MRI-DRV-FLD4C-20-L935 F4LC-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	109	105	102	99	107	103	100	98	100	98	95		97	95	93		95	93	92	90
3	105	99	95	92	103	98	94	91	95	92	89		93	90	88		91	89	87	85
4	101	94	89	86	99	93	88	85	91	87	84		89	86	83		87	84	82	81
5	96	89	84	80	95	88	84	80	87	82	79		85	81	79		83	80	78	77
6	92	85	80	76	91	84	79	76	83	78	75		81	78	75		80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	71		78	74	71		77	73	71	69
8	85	77	72	68	84	77	72	68	76	71	68		75	71	68		74	70	67	66
9	82	74	69	65	81	73	68	65	72	68	65		72	68	65		71	67	64	63
10	79	71	66	62	78	70	65	62	69	65	62		69	65	62		68	64	62	61

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	470123
5°	423059
10°	327964
15°	237382
20°	164364
25°	119830
30°	87073
35°	51517
40°	21667
45°	6759
50°	879
55°	493
60°	565
65°	669
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P726976
 CATALOG NUMBER: MRI-DRV-FLD4C-20-L935 F4LC-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	301.6	20.3
10°-20°	516.3	34.7
20°-30°	410.3	27.6
30°-40°	217.2	14.6
40°-50°	37.4	2.5
50°-60°	2.8	0.2
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1228.2	82.6
0°-40°	1445.4	97.2
0°-60°	1485.6	99.9
0°-90°	1487.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1487.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3827	
5°	3430	302
15°	1866	516
25°	884	410
35°	344	217
45°	39	37
55°	2	3
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P726976
CATALOG NUMBER: MRI-DRV-FLD4C-20-L935 F4LC-N-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	3826.7
2.5°	3728.2
5°	3430.5
7.5°	3041.2
10°	2629.0
12.5°	2230.5
15°	1866.4
17.5°	1527.4
20°	1257.2
22.5°	1051.1
25°	884.0
27.5°	748.9
30°	613.8
32.5°	476.3
35°	343.5
37.5°	226.8
40°	135.1
42.5°	77.9
45°	38.9
47.5°	13.8
50°	4.6
52.5°	4.6
55°	2.3
57.5°	2.3
60°	2.3
62.5°	2.3
65°	2.3
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)