

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P727078

Luminaire Tested: **MRI-DRV-FLD4C-30-L927 F4LC-N-X-H**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P727078  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD4C-30-L927 F4LC-N-X-H  
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 2700K, 90 CRI  
LEDS, 4LBNH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1765.9 lumens  
Efficiency: N/A  
Efficacy: 55.9 lumens/watt  
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P727078  
CATALOG NUMBER: MRI-DRV-FLD4C-30-L927 F4LC-N-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P727078

CATALOG NUMBER: MRI-DRV-FLD4C-30-L927 F4LC-N-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93				93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87				87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81				81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75				75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70				70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65				65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61				61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58				58
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54				54
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51				51

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	272403
5°	266340
10°	246254
15°	220962
20°	194512
25°	167395
30°	134809
35°	89746
40°	46685
45°	21127
50°	9174
55°	6147
60°	3931
65°	2791
70°	2299
75°	1519
80°	0
85°	0



TEST NUMBER: P727078  
 CATALOG NUMBER: MRI-DRV-FLD4C-30-L927 F4LC-N-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	200.0	11.3
10°-20°	485.3	27.5
20°-30°	563.4	31.9
30°-40°	373.1	21.1
40°-50°	104.6	5.9
50°-60°	26.3	1.5
60°-70°	9.9	0.6
70°-80°	3.4	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1248.7	70.7
0°-40°	1621.8	91.8
0°-60°	1752.7	99.3
0°-90°	1765.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1765.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2217	
5°	2160	200
15°	1737	485
25°	1235	563
35°	598	373
45°	122	105
55°	29	26
65°	10	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P727078  
CATALOG NUMBER: MRI-DRV-FLD4C-30-L927 F4LC-N-X-H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2217.3
2.5°	2207.7
5°	2159.7
7.5°	2076.4
10°	1974.0
12.5°	1858.8
15°	1737.3
17.5°	1618.9
20°	1487.8
22.5°	1366.2
25°	1234.9
27.5°	1110.2
30°	950.3
32.5°	780.7
35°	598.4
37.5°	428.8
40°	291.1
42.5°	188.7
45°	121.6
47.5°	73.6
50°	48.0
52.5°	35.1
55°	28.7
57.5°	22.5
60°	16.0
62.5°	12.8
65°	9.6
67.5°	6.4
70°	6.4
72.5°	3.2
75°	3.2
77.5°	3.2
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)