

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P727102

Luminaire Tested: **MRI-DRV-FLD4C-30-L930 F4LC-M-X-H**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P727102  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207151)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD4C-30-L930 F4LC-M-X-H  
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3000K, 90 CRI  
LEDS, 4LBMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2209.0 lumens  
Efficiency: N/A  
Efficacy: 69.9 lumens/watt  
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.93  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P727102  
CATALOG NUMBER: MRI-DRV-FLD4C-30-L930 F4LC-M-X-H

### Luminous Intensity Polar Plot





TEST NUMBER: P727102  
 CATALOG NUMBER: MRI-DRV-FLD4C-30-L930 F4LC-M-X-H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93
2	107	102	98	94	105	100	96	93	97	94	91	94	91	89	91	89	87	85
3	101	94	89	85	99	93	88	84	90	86	83	88	84	82	86	83	80	79
4	96	88	82	77	94	86	81	77	84	80	76	82	78	75	80	77	74	73
5	90	82	75	71	89	81	75	70	79	74	70	77	73	69	75	72	69	67
6	86	76	70	65	84	75	69	65	74	68	64	72	68	64	71	67	64	62
7	81	71	65	60	80	70	64	60	69	64	60	68	63	59	67	62	59	58
8	77	67	60	56	75	66	60	56	65	59	56	64	59	55	63	58	55	54
9	73	63	56	52	72	62	56	52	61	56	52	60	55	52	59	55	52	50
10	69	59	53	49	68	59	53	49	58	52	49	57	52	48	56	52	48	47

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	269098
5°	265181
10°	254101
15°	240002
20°	224033
25°	203371
30°	169791
35°	123011
40°	76995
45°	44009
50°	22954
55°	12851
60°	8207
65°	4855
70°	3592
75°	1566
80°	2335
85°	0



TEST NUMBER: P727102  
 CATALOG NUMBER: MRI-DRV-FLD4C-30-L930 F4LC-M-X-H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	201.5	9.1
10°-20°	528.8	23.9
20°-30°	679.5	30.8
30°-40°	511.3	23.1
40°-50°	205.3	9.3
50°-60°	58.4	2.6
60°-70°	18.5	0.8
70°-80°	5.2	0.2
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1409.8	63.8
0°-40°	1921.1	87.0
0°-60°	2184.8	98.9
0°-90°	2209.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2209.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2190	
5°	2150	202
15°	1887	529
25°	1500	680
35°	820	511
45°	253	205
55°	60	58
65°	17	18
75°	3	5
85°	0	0
90°	0	



TEST NUMBER: P727102  
CATALOG NUMBER: MRI-DRV-FLD4C-30-L930 F4LC-M-X-H

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2190.4
2.5°	2177.0
5°	2150.3
7.5°	2100.3
10°	2036.9
12.5°	1960.4
15°	1887.0
17.5°	1803.6
20°	1713.6
22.5°	1617.0
25°	1500.3
27.5°	1360.2
30°	1196.9
32.5°	1013.5
35°	820.2
37.5°	640.1
40°	480.1
42.5°	353.4
45°	253.3
47.5°	173.4
50°	120.1
52.5°	83.4
55°	60.0
57.5°	43.4
60°	33.4
62.5°	23.3
65°	16.7
67.5°	13.3
70°	10.0
72.5°	6.7
75°	3.3
77.5°	3.3
80°	3.3
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)