

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P726766

Luminaire Tested: **MRI-DRV-FLD4C-15-L930 F4LC-W-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P726766
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P206636)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD4C-15-L930 F4LC-W-X-H
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3000K, 90 CRI
LEDS, 4LBWH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1291.0 lumens
Efficiency: N/A
Efficacy: 81.7 lumens/watt
Spacing Criteria (0/90/45): 1.18 / 1.18 / 1.13
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P726766
CATALOG NUMBER: MRI-DRV-FLD4C-15-L930 F4LC-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P726766
 CATALOG NUMBER: MRI-DRV-FLD4C-15-L930 F4LC-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	109	106	104	110	107	104	102	103	101	99	99	97	96	96	94	93	91
2	105	100	95	91	103	98	93	90	95	91	88	91	88	86	89	86	84	82
3	99	91	85	80	97	90	84	80	87	82	78	84	80	77	82	79	76	74
4	92	83	77	72	90	82	76	71	80	75	70	78	73	70	76	72	69	67
5	87	77	70	65	85	76	69	64	74	68	64	72	67	63	70	66	62	61
6	81	71	64	58	80	70	63	58	68	62	58	67	61	57	65	61	57	55
7	76	65	58	53	75	65	58	53	63	57	53	62	56	52	61	56	52	50
8	72	60	53	49	70	60	53	49	59	53	48	58	52	48	57	52	48	46
9	68	56	49	45	66	56	49	45	55	49	44	54	48	44	53	48	44	43
10	64	52	46	41	63	52	46	41	51	45	41	50	45	41	49	44	41	39

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	102226
5°	102617
10°	102930
15°	102933
20°	102368
25°	99971
30°	93443
35°	80912
40°	63203
45°	45346
50°	29472
55°	17628
60°	10320
65°	6628
70°	4418
75°	3323
80°	2476
85°	0



TEST NUMBER: P726766
 CATALOG NUMBER: MRI-DRV-FLD4C-15-L930 F4LC-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.2	6.1
10°-20°	228.3	17.7
20°-30°	336.9	26.1
30°-40°	332.5	25.8
40°-50°	203.5	15.8
50°-60°	78.0	6.0
60°-70°	24.4	1.9
70°-80°	7.2	0.6
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	644.5	49.9
0°-40°	977.0	75.7
0°-60°	1258.5	97.5
0°-90°	1291.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1291.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	832	
5°	832	79
15°	809	228
25°	738	337
35°	540	332
45°	261	203
55°	82	78
65°	23	24
75°	7	7
85°	0	1
90°	0	



TEST NUMBER: P726766
CATALOG NUMBER: MRI-DRV-FLD4C-15-L930 F4LC-W-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	832.1
2.5°	833.9
5°	832.1
7.5°	830.4
10°	825.1
12.5°	818.1
15°	809.3
17.5°	798.8
20°	783.0
22.5°	765.6
25°	737.5
27.5°	702.4
30°	658.7
32.5°	604.4
35°	539.5
37.5°	467.7
40°	394.1
42.5°	325.8
45°	261.0
47.5°	203.2
50°	154.2
52.5°	113.9
55°	82.3
57.5°	57.8
60°	42.0
62.5°	31.6
65°	22.8
67.5°	17.5
70°	12.3
72.5°	8.8
75°	7.0
77.5°	3.5
80°	3.5
82.5°	1.8
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)