

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P726796

Luminaire Tested: **MRI-DRV-FLD4C-15-L935 F4LC-N-X-LI**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P726796  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P208279)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD4C-15-L935 F4LC-N-X-LI  
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI  
LEDS, 4LBNLI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1153.1 lumens  
Efficiency: N/A  
Efficacy: 73.0 lumens/watt  
Spacing Criteria (0/90/45): 0.48 / 0.48 / 0.54  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P726796  
CATALOG NUMBER: MRI-DRV-FLD4C-15-L935 F4LC-N-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P726796

CATALOG NUMBER: MRI-DRV-FLD4C-15-L935 F4LC-N-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77
6	92	85	80	76	91	84	79	76	83	78	75	81	78	75	80	77	74	73
7	89	81	76	72	88	80	75	72	79	75	71	78	74	71	77	73	71	69
8	85	77	72	68	84	77	72	68	76	71	68	75	71	68	74	70	67	66
9	82	74	69	65	81	73	68	65	72	68	65	72	68	65	71	67	64	63
10	79	71	66	62	78	70	65	62	69	65	62	69	65	62	68	64	62	61

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	364531
5°	328039
10°	254300
15°	184065
20°	127443
25°	92909
30°	67511
35°	39954
40°	16807
45°	5247
50°	688
55°	386
60°	442
65°	523
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P726796  
 CATALOG NUMBER: MRI-DRV-FLD4C-15-L935 F4LC-N-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	233.8	20.3
10°-20°	400.3	34.7
20°-30°	318.2	27.6
30°-40°	168.4	14.6
40°-50°	29.0	2.5
50°-60°	2.2	0.2
60°-70°	1.1	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	952.3	82.6
0°-40°	1120.7	97.2
0°-60°	1152.0	99.9
0°-90°	1153.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1153.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2967	
5°	2660	234
15°	1447	400
25°	685	318
35°	266	168
45°	30	29
55°	2	2
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P726796  
CATALOG NUMBER: MRI-DRV-FLD4C-15-L935 F4LC-N-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	2967.2
2.5°	2890.8
5°	2660.0
7.5°	2358.1
10°	2038.5
12.5°	1729.5
15°	1447.2
17.5°	1184.4
20°	974.8
22.5°	815.0
25°	685.4
27.5°	580.7
30°	475.9
32.5°	369.3
35°	266.4
37.5°	175.8
40°	104.8
42.5°	60.4
45°	30.2
47.5°	10.7
50°	3.6
52.5°	3.6
55°	1.8
57.5°	1.8
60°	1.8
62.5°	1.8
65°	1.8
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)