

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P726856

Luminaire Tested: **MRI-DRV-FLD4C-15-L950 F4LC-M-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P726856
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD4C-15-L950 F4LC-M-X-LI
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 5000K, 90 CRI
LEDS, 4LBMLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1502.0 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P726856
CATALOG NUMBER: MRI-DRV-FLD4C-15-L950 F4LC-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P726856
 CATALOG NUMBER: MRI-DRV-FLD4C-15-L950 F4LC-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	230928
5°	228727
10°	216738
15°	196784
20°	173881
25°	150329
30°	117516
35°	72064
40°	36982
45°	14698
50°	4778
55°	1649
60°	1401
65°	1134
70°	682
75°	902
80°	0
85°	0



TEST NUMBER: P726856
 CATALOG NUMBER: MRI-DRV-FLD4C-15-L950 F4LC-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	173.2	11.5
10°-20°	431.1	28.7
20°-30°	501.1	33.4
30°-40°	306.9	20.4
40°-50°	76.2	5.1
50°-60°	8.9	0.6
60°-70°	3.3	0.2
70°-80°	1.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1105.4	73.6
0°-40°	1412.3	94.0
0°-60°	1497.4	99.7
0°-90°	1502.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1502.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1880	
5°	1855	173
15°	1547	431
25°	1109	501
35°	480	307
45°	85	76
55°	8	9
65°	4	3
75°	2	1
85°	0	0
90°	0	



TEST NUMBER: P726856
CATALOG NUMBER: MRI-DRV-FLD4C-15-L950 F4LC-M-X-LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1879.7
2.5°	1877.7
5°	1854.7
7.5°	1804.7
10°	1737.4
12.5°	1649.0
15°	1547.2
17.5°	1437.6
20°	1330.0
22.5°	1222.3
25°	1109.0
27.5°	978.3
30°	828.4
32.5°	653.5
35°	480.5
37.5°	338.2
40°	230.6
42.5°	144.1
45°	84.6
47.5°	48.1
50°	25.0
52.5°	11.5
55°	7.7
57.5°	5.7
60°	5.7
62.5°	3.9
65°	3.9
67.5°	1.9
70°	1.9
72.5°	1.9
75°	1.9
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)