

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P727216

Luminaire Tested: **MRI-DRV-FLD4C-30-L950 F4LC-M-X-LI**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P727216  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD4C-30-L950 F4LC-M-X-LI  
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 5000K, 90 CRI  
LEDS, 4LBMLI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2857.0 lumens  
Efficiency: N/A  
Efficacy: 90.4 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.6  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P727216  
CATALOG NUMBER: MRI-DRV-FLD4C-30-L950 F4LC-M-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P727216  
 CATALOG NUMBER: MRI-DRV-FLD4C-30-L950 F4LC-M-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

|     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|
| RF  | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     | 20  |     |     |     |     |
| RC  | 80  |     |     |     | 70  |     |     |     | 50  |     |     |     | 30  |     |     |     | 10  |     |     | 0   |     |
| RW  | 70  | 50  | 30  | 10  | 70  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 50  | 30  | 10  | 0   |
| RCR |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |     |
| 0   | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | 100 | 100 | 100 |
| 1   | 114 | 111 | 109 | 106 | 111 | 109 | 107 | 105 | 105 | 103 | 101 | 101 | 100 | 98  | 98  | 97  | 96  | 94  | 94  | 94  | 94  |
| 2   | 108 | 103 | 100 | 96  | 106 | 102 | 98  | 95  | 99  | 96  | 93  | 96  | 93  | 91  | 93  | 91  | 89  | 88  | 88  | 88  | 88  |
| 3   | 103 | 97  | 92  | 88  | 101 | 95  | 91  | 87  | 93  | 89  | 86  | 90  | 87  | 85  | 88  | 85  | 83  | 82  | 82  | 82  | 82  |
| 4   | 98  | 91  | 85  | 81  | 96  | 89  | 84  | 81  | 87  | 83  | 80  | 85  | 82  | 79  | 83  | 80  | 78  | 76  | 76  | 76  | 76  |
| 5   | 93  | 85  | 79  | 75  | 91  | 84  | 79  | 75  | 82  | 78  | 74  | 81  | 77  | 73  | 79  | 76  | 73  | 71  | 71  | 71  | 71  |
| 6   | 89  | 80  | 74  | 70  | 87  | 79  | 74  | 70  | 78  | 73  | 69  | 76  | 72  | 69  | 75  | 71  | 68  | 67  | 67  | 67  | 67  |
| 7   | 84  | 75  | 69  | 65  | 83  | 75  | 69  | 65  | 73  | 68  | 65  | 72  | 68  | 64  | 71  | 67  | 64  | 63  | 63  | 63  | 63  |
| 8   | 80  | 71  | 65  | 61  | 79  | 70  | 65  | 61  | 69  | 64  | 61  | 68  | 64  | 60  | 67  | 63  | 60  | 59  | 59  | 59  | 59  |
| 9   | 77  | 67  | 61  | 57  | 75  | 67  | 61  | 57  | 66  | 61  | 57  | 65  | 60  | 57  | 64  | 60  | 57  | 55  | 55  | 55  | 55  |
| 10  | 73  | 64  | 58  | 54  | 72  | 63  | 58  | 54  | 62  | 57  | 54  | 62  | 57  | 54  | 61  | 57  | 54  | 52  | 52  | 52  | 52  |

**AVERAGE LUMINANCE (cd/sqm):**

|     |        |
|-----|--------|
|     | 0°     |
| 0°  | 439250 |
| 5°  | 435070 |
| 10° | 412269 |
| 15° | 374299 |
| 20° | 330754 |
| 25° | 285951 |
| 30° | 223513 |
| 35° | 137078 |
| 40° | 70356  |
| 45° | 27955  |
| 50° | 9078   |
| 55° | 3127   |
| 60° | 2678   |
| 65° | 2151   |
| 70° | 1329   |
| 75° | 1756   |
| 80° | 0      |
| 85° | 0      |



TEST NUMBER: P727216  
 CATALOG NUMBER: MRI-DRV-FLD4C-30-L950 F4LC-M-X-LI

**ZONAL LUMENS:**

| Zone      | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10°    | 329.4  | 11.5      |
| 10°-20°   | 820.0  | 28.7      |
| 20°-30°   | 953.2  | 33.4      |
| 30°-40°   | 583.7  | 20.4      |
| 40°-50°   | 144.9  | 5.1       |
| 50°-60°   | 16.9   | 0.6       |
| 60°-70°   | 6.4    | 0.2       |
| 70°-80°   | 2.4    | 0.1       |
| 80°-90°   | 0.0    | 0.0       |
| 90°-100°  | 0.0    | 0.0       |
| 100°-110° | 0.0    | 0.0       |
| 110°-120° | 0.0    | 0.0       |
| 120°-130° | 0.0    | 0.0       |
| 130°-140° | 0.0    | 0.0       |
| 140°-150° | 0.0    | 0.0       |
| 150°-160° | 0.0    | 0.0       |
| 160°-170° | 0.0    | 0.0       |
| 170°-180° | 0.0    | 0.0       |
| 0°-30°    | 2102.6 | 73.6      |
| 0°-40°    | 2686.4 | 94.0      |
| 0°-60°    | 2848.3 | 99.7      |
| 0°-90°    | 2857.0 | 100.0     |
| 90°-120°  | 0.0    | 0.0       |
| 90°-150°  | 0.0    | 0.0       |
| 90°-180°  | 0.0    | 0.0       |
| 0°-180°   | 2857.0 | 100.0     |

**CANDELA DISTRIBUTION:**

|     | 0°   | Flux |
|-----|------|------|
| 0°  | 3575 |      |
| 5°  | 3528 | 329  |
| 15° | 2943 | 820  |
| 25° | 2110 | 953  |
| 35° | 914  | 584  |
| 45° | 161  | 145  |
| 55° | 15   | 17   |
| 65° | 7    | 6    |
| 75° | 4    | 2    |
| 85° | 0    | 0    |
| 90° | 0    |      |



TEST NUMBER: P727216  
CATALOG NUMBER: MRI-DRV-FLD4C-30-L950 F4LC-M-X-LI

**CANDELA DISTRIBUTION (FULL):**

|       | 0°     |
|-------|--------|
| 0°    | 3575.4 |
| 2.5°  | 3571.7 |
| 5°    | 3527.9 |
| 7.5°  | 3432.8 |
| 10°   | 3304.8 |
| 12.5° | 3136.7 |
| 15°   | 2942.9 |
| 17.5° | 2734.6 |
| 20°   | 2529.9 |
| 22.5° | 2325.1 |
| 25°   | 2109.5 |
| 27.5° | 1860.8 |
| 30°   | 1575.6 |
| 32.5° | 1243.0 |
| 35°   | 914.0  |
| 37.5° | 643.4  |
| 40°   | 438.7  |
| 42.5° | 274.1  |
| 45°   | 160.9  |
| 47.5° | 91.4   |
| 50°   | 47.5   |
| 52.5° | 22.0   |
| 55°   | 14.6   |
| 57.5° | 10.9   |
| 60°   | 10.9   |
| 62.5° | 7.4    |
| 65°   | 7.4    |
| 67.5° | 3.7    |
| 70°   | 3.7    |
| 72.5° | 3.7    |
| 75°   | 3.7    |
| 77.5° | 0.0    |
| 80°   | 0.0    |
| 82.5° | 0.0    |
| 85°   | 0.0    |
| 87.5° | 0.0    |
| 90°   | 0.0    |

(END OF REPORT)