

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P726934

Luminaire Tested: **MRI-DRV-FLD4C-20-L930 F4LC-N-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P726934
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P207666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD4C-20-L930 F4LC-N-X-H
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3000K, 90 CRI
LEDS, 4LBNH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1245.0 lumens
Efficiency: N/A
Efficacy: 57.1 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.85
Luminous Opening: Circular (Dia: 0.33' x H: 0')
CIE Type: Direct

Input Watts (W): 21.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P726934
CATALOG NUMBER: MRI-DRV-FLD4C-20-L930 F4LC-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P726934
 CATALOG NUMBER: MRI-DRV-FLD4C-20-L930 F4LC-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	113	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	93		
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87		
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81		
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75		
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70		
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65		
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61		
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58		
9	76	66	60	56	74	65	60	56	65	59	56	64	59	56	63	59	55	54		
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	192045
5°	187759
10°	173613
15°	155779
20°	137131
25°	118013
30°	95031
35°	63260
40°	32909
45°	14890
50°	6460
55°	4348
60°	2776
65°	1977
70°	1616
75°	1092
80°	0
85°	0



TEST NUMBER: P726934
 CATALOG NUMBER: MRI-DRV-FLD4C-20-L930 F4LC-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	141.0	11.3
10°-20°	342.1	27.5
20°-30°	397.2	31.9
30°-40°	263.0	21.1
40°-50°	73.7	5.9
50°-60°	18.5	1.5
60°-70°	6.9	0.6
70°-80°	2.4	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	880.3	70.7
0°-40°	1143.3	91.8
0°-60°	1235.6	99.2
0°-90°	1245.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1245.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1563	
5°	1522	141
15°	1225	342
25°	871	397
35°	422	263
45°	86	74
55°	20	19
65°	7	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P726934
CATALOG NUMBER: MRI-DRV-FLD4C-20-L930 F4LC-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1563.2
2.5°	1556.4
5°	1522.5
7.5°	1463.8
10°	1391.7
12.5°	1310.4
15°	1224.8
17.5°	1141.3
20°	1048.9
22.5°	963.1
25°	870.6
27.5°	782.7
30°	669.9
32.5°	550.4
35°	421.8
37.5°	302.3
40°	205.2
42.5°	133.0
45°	85.7
47.5°	51.9
50°	33.8
52.5°	24.8
55°	20.3
57.5°	15.8
60°	11.3
62.5°	9.0
65°	6.8
67.5°	4.5
70°	4.5
72.5°	2.3
75°	2.3
77.5°	2.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)