

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203263

Luminaire Tested: **MRI-DRV-FLD6C-10-L927 F6LC-M-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P203263
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-10-L927 F6LC-M-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 2700K, 90 CRI
LEDS, 6LBMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 724.0 lumens
Efficiency: N/A
Efficacy: 74.3 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P203263
CATALOG NUMBER: MRI-DRV-FLD6C-10-L927 F6LC-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P203263
 CATALOG NUMBER: MRI-DRV-FLD6C-10-L927 F6LC-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39279
5°	38576
10°	36606
15°	34325
20°	31969
25°	29457
30°	24542
35°	17300
40°	11028
45°	6574
50°	3880
55°	2466
60°	1699
65°	1206
70°	833
75°	657
80°	316
85°	0



TEST NUMBER: P203263
 CATALOG NUMBER: MRI-DRV-FLD6C-10-L927 F6LC-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	65.5	9.0
10°-20°	169.5	23.4
20°-30°	219.6	30.3
30°-40°	163.0	22.5
40°-50°	68.8	9.5
50°-60°	24.4	3.4
60°-70°	9.4	1.3
70°-80°	3.3	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	454.6	62.8
0°-40°	617.6	85.3
0°-60°	710.9	98.2
0°-90°	724.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	724.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	716	
5°	701	66
15°	605	169
25°	487	220
35°	258	163
45°	85	69
55°	26	24
65°	9	9
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P203263
CATALOG NUMBER: MRI-DRV-FLD6C-10-L927 F6LC-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	716.5
2.5°	714.4
5°	701.0
7.5°	681.3
10°	657.6
12.5°	631.7
15°	604.8
17.5°	574.9
20°	548.0
22.5°	520.1
25°	487.0
27.5°	441.5
30°	387.7
32.5°	324.6
35°	258.5
37.5°	202.7
40°	154.1
42.5°	114.8
45°	84.8
47.5°	62.0
50°	45.5
52.5°	34.1
55°	25.8
57.5°	19.6
60°	15.5
62.5°	11.4
65°	9.3
67.5°	7.2
70°	5.2
72.5°	4.1
75°	3.1
77.5°	2.1
80°	1.0
82.5°	1.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)