

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203343

Luminaire Tested: **MRI-DRV-FLD6C-10-L930 F6LC-N-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P203343
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203666)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-10-L930 F6LC-N-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3000K, 90 CRI
LEDS, 6LBNH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 648.1 lumens
Efficiency: N/A
Efficacy: 66.5 lumens/watt
Spacing Criteria (0/90/45): 0.78 / 0.78 / 0.84
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P203343
CATALOG NUMBER: MRI-DRV-FLD6C-10-L930 F6LC-N-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P203343
 CATALOG NUMBER: MRI-DRV-FLD6C-10-L930 F6LC-N-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	111	108	106	111	109	106	104	104	103	101	101	99	98	97	96	95	93				93
2	108	103	99	96	106	101	98	94	98	95	92	95	93	90	92	90	89	87				87
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81				81
4	97	90	84	80	95	89	83	79	86	82	78	84	81	78	83	79	77	75				75
5	92	84	78	74	91	83	78	73	81	76	73	80	75	72	78	74	72	70				70
6	88	79	73	69	86	78	72	68	77	72	68	75	71	67	74	70	67	65				65
7	83	74	68	64	82	73	68	64	72	67	63	71	66	63	70	66	63	61				61
8	79	70	64	60	78	69	64	60	68	63	59	67	63	59	66	62	59	58				58
9	76	66	60	56	75	66	60	56	65	59	56	64	59	56	63	59	55	54				54
10	72	62	57	53	71	62	56	53	61	56	53	60	56	52	60	55	52	51				51

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45539
5°	44409
10°	40976
15°	36277
20°	31503
25°	26941
30°	22212
35°	14629
40°	7865
45°	3481
50°	1416
55°	1023
60°	647
65°	467
70°	385
75°	254
80°	379
85°	0



TEST NUMBER: P203343
 CATALOG NUMBER: MRI-DRV-FLD6C-10-L930 F6LC-N-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.7	11.5
10°-20°	178.1	27.5
20°-30°	204.1	31.5
30°-40°	137.1	21.2
40°-50°	39.2	6.0
50°-60°	9.6	1.5
60°-70°	3.7	0.6
70°-80°	1.4	0.2
80°-90°	0.2	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	456.9	70.5
0°-40°	594.0	91.7
0°-60°	642.8	99.2
0°-90°	648.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	648.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	831	
5°	807	75
15°	639	178
25°	445	204
35°	219	137
45°	45	39
55°	11	10
65°	4	4
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P203343
CATALOG NUMBER: MRI-DRV-FLD6C-10-L930 F6LC-N-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	830.7
2.5°	824.8
5°	807.0
7.5°	775.1
10°	736.1
12.5°	686.5
15°	639.2
17.5°	589.6
20°	540.0
22.5°	492.7
25°	445.4
27.5°	401.7
30°	350.9
32.5°	283.6
35°	218.6
37.5°	159.5
40°	109.9
42.5°	72.1
45°	44.9
47.5°	27.2
50°	16.6
52.5°	13.0
55°	10.7
57.5°	8.3
60°	5.9
62.5°	4.7
65°	3.6
67.5°	2.4
70°	2.4
72.5°	1.2
75°	1.2
77.5°	1.2
80°	1.2
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)