

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P727072

Luminaire Tested: **MRI-DRV-FLD4C-30-L927 F4LC-M-X-LI**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P727072  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD4C-30-L927 F4LC-M-X-LI  
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 2700K, 90 CRI  
LEDS, 4LBMLI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2651.0 lumens  
Efficiency: N/A  
Efficacy: 83.9 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P727072  
CATALOG NUMBER: MRI-DRV-FLD4C-30-L927 F4LC-M-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P727072  
 CATALOG NUMBER: MRI-DRV-FLD4C-30-L927 F4LC-M-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	407579
5°	403697
10°	382542
15°	347310
20°	306907
25°	265333
30°	207398
35°	127195
40°	65288
45°	25940
50°	8429
55°	2892
60°	2482
65°	1977
70°	1221
75°	1614
80°	0
85°	0



TEST NUMBER: P727072  
 CATALOG NUMBER: MRI-DRV-FLD4C-30-L927 F4LC-M-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	305.6	11.5
10°-20°	760.9	28.7
20°-30°	884.5	33.4
30°-40°	541.6	20.4
40°-50°	134.5	5.1
50°-60°	15.7	0.6
60°-70°	5.9	0.2
70°-80°	2.2	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1951.0	73.6
0°-40°	2492.7	94.0
0°-60°	2642.9	99.7
0°-90°	2651.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2651.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3318	
5°	3274	306
15°	2731	761
25°	1957	885
35°	848	542
45°	149	135
55°	14	16
65°	7	6
75°	3	2
85°	0	0
90°	0	



TEST NUMBER: P727072  
CATALOG NUMBER: MRI-DRV-FLD4C-30-L927 F4LC-M-X-LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	3317.6
2.5°	3314.2
5°	3273.5
7.5°	3185.3
10°	3066.5
12.5°	2910.5
15°	2730.7
17.5°	2537.4
20°	2347.5
22.5°	2157.4
25°	1957.4
27.5°	1726.7
30°	1462.0
32.5°	1153.3
35°	848.1
37.5°	597.0
40°	407.1
42.5°	254.4
45°	149.3
47.5°	84.8
50°	44.1
52.5°	20.4
55°	13.5
57.5°	10.1
60°	10.1
62.5°	6.8
65°	6.8
67.5°	3.4
70°	3.4
72.5°	3.4
75°	3.4
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)