

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203393

Luminaire Tested: **MRI-DRV-FLD6C-10-L935 F6LC-M-X-LI**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P203393  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD6C-10-L935 F6LC-M-X-LI  
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI  
LEDS, 6LBMLI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 935.0 lumens  
Efficiency: N/A  
Efficacy: 95.9 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.5' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9.75  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P203393  
CATALOG NUMBER: MRI-DRV-FLD6C-10-L935 F6LC-M-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P203393  
 CATALOG NUMBER: MRI-DRV-FLD6C-10-L935 F6LC-M-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94	94	94	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88	88	88	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82	82	82	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76	76	76	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71	71	71	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67	67	67	67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63	63	63	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59	59	59	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55	55	55	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52	52	52	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	64145
5°	63537
10°	60208
15°	54660
20°	48298
25°	41760
30°	32644
35°	20017
40°	10276
45°	4086
50°	1322
55°	459
60°	395
65°	311
70°	192
75°	254
80°	0
85°	0



TEST NUMBER: P203393  
 CATALOG NUMBER: MRI-DRV-FLD6C-10-L935 F6LC-M-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	107.8	11.5
10°-20°	268.4	28.7
20°-30°	312.0	33.4
30°-40°	191.0	20.4
40°-50°	47.4	5.1
50°-60°	5.6	0.6
60°-70°	2.1	0.2
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	688.1	73.6
0°-40°	879.2	94.0
0°-60°	932.2	99.7
0°-90°	935.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	935.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1170	
5°	1155	108
15°	963	268
25°	690	312
35°	299	191
45°	53	47
55°	5	6
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P203393  
CATALOG NUMBER: MRI-DRV-FLD6C-10-L935 F6LC-M-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1170.1
2.5°	1168.9
5°	1154.6
7.5°	1123.4
10°	1081.6
12.5°	1026.5
15°	963.1
17.5°	894.9
20°	827.9
22.5°	760.9
25°	690.4
27.5°	609.0
30°	515.7
32.5°	406.8
35°	299.1
37.5°	210.6
40°	143.6
42.5°	89.7
45°	52.7
47.5°	29.9
50°	15.5
52.5°	7.2
55°	4.8
57.5°	3.6
60°	3.6
62.5°	2.4
65°	2.4
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)