

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203443

Luminaire Tested: **MRI-DRV-FLD6C-10-L940 F6LC-M-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P203443
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-10-L940 F6LC-M-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 4000K, 90 CRI
LEDS, 6LBMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 765.0 lumens
Efficiency: N/A
Efficacy: 78.5 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P203443
CATALOG NUMBER: MRI-DRV-FLD6C-10-L940 F6LC-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P203443

CATALOG NUMBER: MRI-DRV-FLD6C-10-L940 F6LC-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92				92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78				78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72				72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66				66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61				61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57				57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53				53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49				49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46				46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41504
5°	40760
10°	38677
15°	36271
20°	33778
25°	31121
30°	25934
35°	18277
40°	11650
45°	6946
50°	4102
55°	2609
60°	1798
65°	1271
70°	882
75°	699
80°	347
85°	0



TEST NUMBER: P203443
 CATALOG NUMBER: MRI-DRV-FLD6C-10-L940 F6LC-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.2	9.0
10°-20°	179.1	23.4
20°-30°	232.0	30.3
30°-40°	172.3	22.5
40°-50°	72.7	9.5
50°-60°	25.8	3.4
60°-70°	9.9	1.3
70°-80°	3.5	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	480.3	62.8
0°-40°	652.6	85.3
0°-60°	751.1	98.2
0°-90°	765.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	765.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	757	
5°	741	69
15°	639	179
25°	514	232
35°	273	172
45°	90	73
55°	27	26
65°	10	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P203443
CATALOG NUMBER: MRI-DRV-FLD6C-10-L940 F6LC-M-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	757.1
2.5°	754.9
5°	740.7
7.5°	719.9
10°	694.8
12.5°	667.5
15°	639.1
17.5°	607.4
20°	579.0
22.5°	549.5
25°	514.5
27.5°	466.5
30°	409.7
32.5°	343.0
35°	273.1
37.5°	214.1
40°	162.8
42.5°	121.3
45°	89.6
47.5°	65.5
50°	48.1
52.5°	36.0
55°	27.3
57.5°	20.7
60°	16.4
62.5°	12.0
65°	9.8
67.5°	7.6
70°	5.5
72.5°	4.4
75°	3.3
77.5°	2.2
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)