

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P727108

Luminaire Tested: **MRI-DRV-FLD4C-30-L930 F4LC-M-X-LI**

Issue Date: 08/03/2023



**Test Information**


Test Method: LM-79-08  
Report Number: P727108  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)  
Test Lab: INNOVATION CENTER-P3  
Issue Date: 08/03/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: FAIL-SAFE  
Catalog Number: MRI-DRV-FLD4C-30-L930 F4LC-M-X-LI  
Description: 4 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3000K, 90 CRI  
LEDS, 4LBMLI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2756.0 lumens  
Efficiency: N/A  
Efficacy: 87.2 lumens/watt  
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 31.6  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P727108  
CATALOG NUMBER: MRI-DRV-FLD4C-30-L930 F4LC-M-X-LI

### Luminous Intensity Polar Plot





TEST NUMBER: P727108  
 CATALOG NUMBER: MRI-DRV-FLD4C-30-L930 F4LC-M-X-LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	423722
5°	419692
10°	397699
15°	361072
20°	319053
25°	275838
30°	215611
35°	132234
40°	67870
45°	26965
50°	8754
55°	3020
60°	2580
65°	2064
70°	1293
75°	1709
80°	0
85°	0



TEST NUMBER: P727108  
 CATALOG NUMBER: MRI-DRV-FLD4C-30-L930 F4LC-M-X-LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	317.7	11.5
10°-20°	791.0	28.7
20°-30°	919.5	33.4
30°-40°	563.1	20.4
40°-50°	139.8	5.1
50°-60°	16.3	0.6
60°-70°	6.1	0.2
70°-80°	2.4	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2028.3	73.6
0°-40°	2591.4	94.0
0°-60°	2747.5	99.7
0°-90°	2756.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2756.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3449	
5°	3403	318
15°	2839	791
25°	2035	920
35°	882	563
45°	155	140
55°	14	16
65°	7	6
75°	4	2
85°	0	0
90°	0	



TEST NUMBER: P727108  
CATALOG NUMBER: MRI-DRV-FLD4C-30-L930 F4LC-M-X-LI

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3449.0
2.5°	3445.4
5°	3403.2
7.5°	3311.4
10°	3188.0
12.5°	3025.8
15°	2838.9
17.5°	2637.9
20°	2440.4
22.5°	2242.9
25°	2034.9
27.5°	1795.1
30°	1519.9
32.5°	1199.0
35°	881.7
37.5°	620.6
40°	423.2
42.5°	264.4
45°	155.2
47.5°	88.2
50°	45.8
52.5°	21.2
55°	14.1
57.5°	10.5
60°	10.5
62.5°	7.1
65°	7.1
67.5°	3.6
70°	3.6
72.5°	3.6
75°	3.6
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)