

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203503

Luminaire Tested: **MRI-DRV-FLD6C-10-L950 F6LC-M-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P203503
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-10-L950 F6LC-M-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 5000K, 90 CRI
LEDS, 6LBMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 780.0 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P203503
CATALOG NUMBER: MRI-DRV-FLD6C-10-L950 F6LC-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P203503
 CATALOG NUMBER: MRI-DRV-FLD6C-10-L950 F6LC-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	42316
5°	41558
10°	39434
15°	36981
20°	34443
25°	31732
30°	26441
35°	18638
40°	11879
45°	7086
50°	4179
55°	2657
60°	1831
65°	1297
70°	898
75°	699
80°	347
85°	0



TEST NUMBER: P203503
 CATALOG NUMBER: MRI-DRV-FLD6C-10-L950 F6LC-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	70.6	9.0
10°-20°	182.6	23.4
20°-30°	236.6	30.3
30°-40°	175.6	22.5
40°-50°	74.1	9.5
50°-60°	26.3	3.4
60°-70°	10.2	1.3
70°-80°	3.5	0.4
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	489.7	62.8
0°-40°	665.4	85.3
0°-60°	765.9	98.2
0°-90°	780.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	780.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	772	
5°	755	71
15°	652	183
25°	525	237
35°	278	176
45°	91	74
55°	28	26
65°	10	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P203503
CATALOG NUMBER: MRI-DRV-FLD6C-10-L950 F6LC-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	771.9
2.5°	769.7
5°	755.2
7.5°	734.0
10°	708.4
12.5°	680.6
15°	651.6
17.5°	619.3
20°	590.4
22.5°	560.3
25°	524.6
27.5°	475.6
30°	417.7
32.5°	349.7
35°	278.5
37.5°	218.3
40°	166.0
42.5°	123.6
45°	91.4
47.5°	66.8
50°	49.0
52.5°	36.8
55°	27.8
57.5°	21.1
60°	16.7
62.5°	12.3
65°	10.0
67.5°	7.8
70°	5.6
72.5°	4.4
75°	3.3
77.5°	2.2
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)