

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203363

Luminaire Tested: **MRI-DRV-FLD6C-10-L930 F6LC-W-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P203363
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-10-L930 F6LC-W-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3000K, 90 CRI
LEDS, 6LBWH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 911.1 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P203363
CATALOG NUMBER: MRI-DRV-FLD6C-10-L930 F6LC-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P203363

CATALOG NUMBER: MRI-DRV-FLD6C-10-L930 F6LC-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					20				
RC	80					70					50					30					10					0				
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	91	91	91	81	81	81	73	73	73
	1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91	91	91	81	81	81	71	71	71	65	65	65
	2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81	81	81	71	71	71	61	61	61	59	59	59
	3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73	73	73	63	63	63	53	53	53	49	49	49
	4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65	65	65	55	55	55	45	45	45	41	41	41
	5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59	59	59	49	49	49	39	39	39	35	35	35
	6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53	53	53	43	43	43	33	33	33	29	29	29
	7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49	49	49	39	39	39	29	29	29	25	25	25
	8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44	44	44	34	34	34	24	24	24	20	20	20
	9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41	41	41	31	31	31	21	21	21	17	17	17
	10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38	38	38	28	28	28	18	18	18	14	14	14

AVERAGE LUMINANCE (cd/sqm):

0°	
0°	30803
5°	30789
10°	30555
15°	30352
20°	29887
25°	29203
30°	27498
35°	24889
40°	20782
45°	15924
50°	11275
55°	7111
60°	4013
65°	2607
70°	1699
75°	1250
80°	758
85°	755



TEST NUMBER: P203363
 CATALOG NUMBER: MRI-DRV-FLD6C-10-L930 F6LC-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	53.1	5.8
10°-20°	150.6	16.5
20°-30°	220.8	24.2
30°-40°	229.8	25.2
40°-50°	159.0	17.4
50°-60°	69.2	7.6
60°-70°	21.3	2.3
70°-80°	6.4	0.7
80°-90°	1.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	424.5	46.6
0°-40°	654.3	71.8
0°-60°	882.5	96.9
0°-90°	911.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	911.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	562	
5°	560	53
15°	535	151
25°	483	221
35°	372	230
45°	205	159
55°	74	69
65°	20	21
75°	6	6
85°	1	1
90°	0	



TEST NUMBER: P203363
CATALOG NUMBER: MRI-DRV-FLD6C-10-L930 F6LC-W-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	561.9
2.5°	563.1
5°	559.5
7.5°	554.8
10°	548.9
12.5°	543.0
15°	534.8
17.5°	524.1
20°	512.3
22.5°	499.3
25°	482.8
27.5°	461.6
30°	434.4
32.5°	406.1
35°	371.9
37.5°	334.1
40°	290.4
42.5°	246.7
45°	205.4
47.5°	166.4
50°	132.2
52.5°	100.4
55°	74.4
57.5°	53.1
60°	36.6
62.5°	27.2
65°	20.1
67.5°	15.4
70°	10.6
72.5°	8.3
75°	5.9
77.5°	3.5
80°	2.4
82.5°	1.2
85°	1.2
87.5°	0.0
90°	0.0

(END OF REPORT)