

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203603

Luminaire Tested: **MRI-DRV-FLD6C-15-L927 F6LC-W-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P203603
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P202739)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-15-L927 F6LC-W-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 2700K, 90 CRI
LEDS, 6LBWH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1343.0 lumens
Efficiency: N/A
Efficacy: 85.0 lumens/watt
Spacing Criteria (0/90/45): 1.16 / 1.16 / 1.16
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P203603
CATALOG NUMBER: MRI-DRV-FLD6C-15-L927 F6LC-W-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P203603
 CATALOG NUMBER: MRI-DRV-FLD6C-15-L927 F6LC-W-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	112	109	106	103	110	107	104	101	103	100	98	99	97	95	95	94	93	91		
2	105	99	94	90	103	97	93	89	94	90	87	91	88	85	88	85	83	81		
3	98	90	84	79	96	89	83	78	86	81	77	83	79	76	81	78	75	73		
4	92	82	75	70	90	81	75	70	79	73	69	77	72	68	75	71	67	65		
5	86	75	68	63	84	74	68	63	72	66	62	71	65	61	69	64	61	59		
6	80	69	62	57	78	68	61	56	67	61	56	65	60	56	64	59	55	53		
7	75	64	56	51	73	63	56	51	62	55	51	60	55	51	59	54	50	49		
8	70	59	52	47	69	58	51	47	57	51	46	56	50	46	55	50	46	44		
9	66	55	48	43	65	54	47	43	53	47	43	52	47	42	51	46	42	41		
10	62	51	44	40	61	50	44	39	50	43	39	49	43	39	48	43	39	38		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	45408
5°	45394
10°	45045
15°	44739
20°	44057
25°	43055
30°	40538
35°	36687
40°	30636
45°	23475
50°	16622
55°	10485
60°	5910
65°	3840
70°	2500
75°	1843
80°	1105
85°	1132



TEST NUMBER: P203603
 CATALOG NUMBER: MRI-DRV-FLD6C-15-L927 F6LC-W-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.2	5.8
10°-20°	222.0	16.5
20°-30°	325.5	24.2
30°-40°	338.8	25.2
40°-50°	234.4	17.5
50°-60°	102.0	7.6
60°-70°	31.3	2.3
70°-80°	9.4	0.7
80°-90°	1.5	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	625.7	46.6
0°-40°	964.5	71.8
0°-60°	1300.9	96.9
0°-90°	1343.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1343.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	828	
5°	825	78
15°	788	222
25°	712	325
35°	548	339
45°	303	234
55°	110	102
65°	30	31
75°	9	9
85°	2	1
90°	0	



TEST NUMBER: P203603
CATALOG NUMBER: MRI-DRV-FLD6C-15-L927 F6LC-W-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	828.3
2.5°	830.1
5°	824.9
7.5°	817.9
10°	809.2
12.5°	800.5
15°	788.3
17.5°	772.6
20°	755.2
22.5°	736.1
25°	711.8
27.5°	680.4
30°	640.4
32.5°	598.6
35°	548.2
37.5°	492.5
40°	428.1
42.5°	363.7
45°	302.8
47.5°	245.3
50°	194.9
52.5°	147.9
55°	109.7
57.5°	78.3
60°	53.9
62.5°	40.0
65°	29.6
67.5°	22.6
70°	15.6
72.5°	12.2
75°	8.7
77.5°	5.2
80°	3.5
82.5°	1.8
85°	1.8
87.5°	0.0
90°	0.0

(END OF REPORT)