

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203383

Luminaire Tested: **MRI-DRV-FLD6C-10-L935 F6LC-M-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P203383
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-10-L935 F6LC-M-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI
LEDS, 6LBMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 764.0 lumens
Efficiency: N/A
Efficacy: 78.4 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P203383
CATALOG NUMBER: MRI-DRV-FLD6C-10-L935 F6LC-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P203383
 CATALOG NUMBER: MRI-DRV-FLD6C-10-L935 F6LC-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92			92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85			85
3	101	94	88	84	99	92	87	84	90	86	82	87	84	81	85	82	80	78			78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72			72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66			66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53			53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49			49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46			46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	41450
5°	40705
10°	38627
15°	36220
20°	33731
25°	31084
30°	25896
35°	18257
40°	11636
45°	6939
50°	4094
55°	2609
60°	1798
65°	1271
70°	882
75°	699
80°	347
85°	0



TEST NUMBER: P203383
 CATALOG NUMBER: MRI-DRV-FLD6C-10-L935 F6LC-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.1	9.0
10°-20°	178.8	23.4
20°-30°	231.7	30.3
30°-40°	172.0	22.5
40°-50°	72.6	9.5
50°-60°	25.8	3.4
60°-70°	9.9	1.3
70°-80°	3.4	0.5
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	479.7	62.8
0°-40°	651.7	85.3
0°-60°	750.2	98.2
0°-90°	764.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	764.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	756	
5°	740	69
15°	638	179
25°	514	232
35°	273	172
45°	90	73
55°	27	26
65°	10	10
75°	3	3
85°	0	0
90°	0	



TEST NUMBER: P203383
CATALOG NUMBER: MRI-DRV-FLD6C-10-L935 F6LC-M-X-H

CANDELA DISTRIBUTION (FULL):

	0°
0°	756.1
2.5°	753.9
5°	739.7
7.5°	719.0
10°	693.9
12.5°	666.6
15°	638.2
17.5°	606.6
20°	578.2
22.5°	548.8
25°	513.9
27.5°	465.9
30°	409.1
32.5°	342.6
35°	272.8
37.5°	213.8
40°	162.6
42.5°	121.1
45°	89.5
47.5°	65.5
50°	48.0
52.5°	36.0
55°	27.3
57.5°	20.7
60°	16.4
62.5°	12.0
65°	9.8
67.5°	7.6
70°	5.5
72.5°	4.3
75°	3.3
77.5°	2.2
80°	1.1
82.5°	1.1
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)