

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203623

Luminaire Tested: **MRI-DRV-FLD6C-15-L930 F6LC-M-X-H**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P203623
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P203254)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-15-L930 F6LC-M-X-H
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3000K, 90 CRI
LEDS, 6LBMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1154.0 lumens
Efficiency: N/A
Efficacy: 73.0 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.93
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P203623
CATALOG NUMBER: MRI-DRV-FLD6C-15-L930 F6LC-M-X-H

Luminous Intensity Polar Plot





TEST NUMBER: P203623
 CATALOG NUMBER: MRI-DRV-FLD6C-15-L930 F6LC-M-X-H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	92	92	92	92
2	107	102	97	93	105	100	96	92	97	93	90	94	91	88	91	89	87	85	85	85	85
3	101	94	88	84	99	92	88	84	90	86	82	87	84	81	85	82	80	78	78	78	78
4	95	87	81	76	93	86	80	76	84	79	75	82	78	74	80	76	73	72	72	72	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	66	66	66	66
6	85	75	69	64	83	75	69	64	73	68	64	72	67	63	70	66	63	61	61	61	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57	57	57	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	53	53	53	53
9	72	62	56	51	71	61	55	51	60	55	51	60	55	51	59	54	51	49	49	49	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	46	46	46	46

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	62610
5°	61485
10°	58343
15°	54711
20°	50953
25°	46950
30°	39120
35°	27572
40°	17569
45°	10482
50°	6183
55°	3938
60°	2708
65°	1920
70°	1330
75°	1038
80°	505
85°	0



TEST NUMBER: P203623
 CATALOG NUMBER: MRI-DRV-FLD6C-15-L930 F6LC-M-X-H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	104.4	9.0
10°-20°	270.1	23.4
20°-30°	350.0	30.3
30°-40°	259.9	22.5
40°-50°	109.7	9.5
50°-60°	39.0	3.4
60°-70°	15.0	1.3
70°-80°	5.2	0.5
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	724.6	62.8
0°-40°	984.4	85.3
0°-60°	1133.1	98.2
0°-90°	1154.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1154.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1142	
5°	1117	104
15°	964	270
25°	776	350
35°	412	260
45°	135	110
55°	41	39
65°	15	15
75°	5	5
85°	0	1
90°	0	



TEST NUMBER: P203623
CATALOG NUMBER: MRI-DRV-FLD6C-15-L930 F6LC-M-X-H

CANDELA DISTRIBUTION (FULL):

0°	
0°	1142.1
2.5°	1138.7
5°	1117.3
7.5°	1086.0
10°	1048.1
12.5°	1006.9
15°	964.0
17.5°	916.3
20°	873.4
22.5°	828.9
25°	776.2
27.5°	703.7
30°	618.0
32.5°	517.4
35°	412.0
37.5°	323.0
40°	245.5
42.5°	182.9
45°	135.2
47.5°	98.9
50°	72.5
52.5°	54.4
55°	41.2
57.5°	31.3
60°	24.7
62.5°	18.1
65°	14.8
67.5°	11.5
70°	8.3
72.5°	6.6
75°	4.9
77.5°	3.3
80°	1.6
82.5°	1.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)