

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203453

Luminaire Tested: **MRI-DRV-FLD6C-10-L940 F6LC-M-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P203453
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205108)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-10-L940 F6LC-M-X-LI
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 4000K, 90 CRI
LEDS, 6LBMLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 936.0 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 0.85 / 0.85 / 0.85
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 9.75
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P203453
CATALOG NUMBER: MRI-DRV-FLD6C-10-L940 F6LC-M-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P203453
 CATALOG NUMBER: MRI-DRV-FLD6C-10-L940 F6LC-M-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	114	111	109	106	111	109	107	105	105	103	101	101	100	98	98	97	96	94		
2	108	103	100	96	106	102	98	95	99	96	93	96	93	91	93	91	89	88		
3	103	97	92	88	101	95	91	87	93	89	86	90	87	85	88	85	83	82		
4	98	91	85	81	96	89	84	81	87	83	80	85	82	79	83	80	78	76		
5	93	85	79	75	91	84	79	75	82	78	74	81	77	73	79	76	73	71		
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67		
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63		
8	80	71	65	61	79	70	65	61	69	64	61	68	64	60	67	63	60	59		
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55		
10	73	64	58	54	72	63	58	54	62	57	54	62	57	54	61	57	54	52		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	64216
5°	63603
10°	60269
15°	54722
20°	48351
25°	41803
30°	32676
35°	20037
40°	10284
45°	4086
50°	1330
55°	459
60°	395
65°	311
70°	192
75°	254
80°	0
85°	0



TEST NUMBER: P203453
 CATALOG NUMBER: MRI-DRV-FLD6C-10-L940 F6LC-M-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	107.9	11.5
10°-20°	268.7	28.7
20°-30°	312.3	33.4
30°-40°	191.2	20.4
40°-50°	47.5	5.1
50°-60°	5.6	0.6
60°-70°	2.1	0.2
70°-80°	0.8	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	688.8	73.6
0°-40°	880.1	94.0
0°-60°	933.1	99.7
0°-90°	936.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	936.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1171	
5°	1156	108
15°	964	269
25°	691	312
35°	299	191
45°	53	47
55°	5	6
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P203453
CATALOG NUMBER: MRI-DRV-FLD6C-10-L940 F6LC-M-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1171.4
2.5°	1170.2
5°	1155.8
7.5°	1124.6
10°	1082.7
12.5°	1027.6
15°	964.2
17.5°	895.9
20°	828.8
22.5°	761.7
25°	691.1
27.5°	609.6
30°	516.2
32.5°	407.2
35°	299.4
37.5°	210.8
40°	143.7
42.5°	89.8
45°	52.7
47.5°	30.0
50°	15.6
52.5°	7.2
55°	4.8
57.5°	3.6
60°	3.6
62.5°	2.4
65°	2.4
67.5°	1.2
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)