

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203713

Luminaire Tested: **MRI-DRV-FLD6C-15-L935 F6LC-N-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P203713
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205310)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-15-L935 F6LC-N-X-LI
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI
LEDS, 6LBNLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1273.0 lumens
Efficiency: N/A
Efficacy: 80.6 lumens/watt
Spacing Criteria (0/90/45): 0.53 / 0.53 / 0.58
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P203713
CATALOG NUMBER: MRI-DRV-FLD6C-15-L935 F6LC-N-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P203713
 CATALOG NUMBER: MRI-DRV-FLD6C-15-L935 F6LC-N-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	96	95
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	89
3	105	99	94	91	103	97	93	90	95	91	89	93	90	87	90	88	86	85
4	100	93	88	85	98	92	88	84	90	86	83	88	85	82	86	84	81	80
5	96	88	83	79	94	87	83	79	86	82	78	84	81	78	83	80	77	76
6	92	84	79	75	90	83	78	75	82	77	74	80	76	74	79	76	73	72
7	88	80	74	71	87	79	74	71	78	73	70	77	73	70	76	72	69	68
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65
9	81	73	67	64	80	72	67	64	71	67	63	70	66	63	70	66	63	62
10	78	69	64	61	77	69	64	61	68	64	61	67	63	60	67	63	60	59

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	158885
5°	148585
10°	121185
15°	89178
20°	61465
25°	45632
30°	34277
35°	21375
40°	10377
45°	3559
50°	469
55°	354
60°	197
65°	233
70°	289
75°	0
80°	0
85°	0



TEST NUMBER: P203713
 CATALOG NUMBER: MRI-DRV-FLD6C-15-L935 F6LC-N-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	241.0	18.9
10°-20°	432.5	34.0
20°-30°	349.7	27.5
30°-40°	201.5	15.8
40°-50°	42.6	3.3
50°-60°	3.7	0.3
60°-70°	1.8	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1023.2	80.4
0°-40°	1224.7	96.2
0°-60°	1270.9	99.8
0°-90°	1273.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1273.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2898	
5°	2700	241
15°	1571	433
25°	754	350
35°	319	201
45°	46	43
55°	4	4
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P203713
CATALOG NUMBER: MRI-DRV-FLD6C-15-L935 F6LC-N-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2898.3
2.5°	2863.5
5°	2700.1
7.5°	2465.2
10°	2177.0
12.5°	1881.5
15°	1571.3
17.5°	1272.1
20°	1053.6
22.5°	886.6
25°	754.4
27.5°	642.5
30°	541.5
32.5°	429.5
35°	319.4
37.5°	222.1
40°	145.0
42.5°	88.1
45°	45.9
47.5°	18.3
50°	5.5
52.5°	5.5
55°	3.7
57.5°	3.7
60°	1.8
62.5°	1.8
65°	1.8
67.5°	1.8
70°	1.8
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)