

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: FAIL-SAFE

Report Number: P203733

Luminaire Tested: **MRI-DRV-FLD6C-15-L935 F6LC-W-X-LI**

Issue Date: 08/03/2023



Test Information

Test Method: LM-79-08
Report Number: P203733
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P205209)
Test Lab: INNOVATION CENTER-P3
Issue Date: 08/03/2023
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: FAIL-SAFE
Catalog Number: MRI-DRV-FLD6C-15-L935 F6LC-W-X-LI
Description: 6 INCH FAIL-SAFE MRI REMOTE DRIVER LED DOWNLIGHT WITH 3500K, 90 CRI
LEDS, 6LBWLI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1617.0 lumens
Efficiency: N/A
Efficacy: 102.3 lumens/watt
Spacing Criteria (0/90/45): 1.24 / 1.24 / 1.18
Luminous Opening: Circular (Dia: 0.5' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT

TEST NUMBER: P203733
CATALOG NUMBER: MRI-DRV-FLD6C-15-L935 F6LC-W-X-LI

Luminous Intensity Polar Plot





TEST NUMBER: P203733

CATALOG NUMBER: MRI-DRV-FLD6C-15-L935 F6LC-W-X-LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	104	110	107	105	103	103	101	99	100	98	97	96	95	94	92
2	106	101	96	92	104	99	95	91	95	92	89	92	90	87	90	87	85	83
3	100	92	87	82	97	91	86	81	88	84	80	86	82	79	83	80	77	76
4	93	85	78	73	92	84	78	73	81	76	72	79	75	71	77	74	70	69
5	88	78	71	66	86	77	71	66	75	70	65	73	69	65	72	68	64	63
6	82	72	65	60	81	71	65	60	70	64	59	68	63	59	67	62	59	57
7	77	67	60	55	76	66	59	55	65	59	54	63	58	54	62	57	54	52
8	73	62	55	50	71	61	55	50	60	54	50	59	54	50	58	53	49	48
9	69	57	51	46	67	57	50	46	56	50	46	55	50	46	54	49	46	44
10	65	54	47	43	64	53	47	42	52	46	42	51	46	42	51	46	42	41

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	55379
5°	55894
10°	57453
15°	58894
20°	59785
25°	58552
30°	54895
35°	49081
40°	39753
45°	26297
50°	13287
55°	5610
60°	1809
65°	713
70°	593
75°	381
80°	0
85°	0



TEST NUMBER: P203733
 CATALOG NUMBER: MRI-DRV-FLD6C-15-L935 F6LC-W-X-LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	97.5	6.0
10°-20°	292.9	18.1
20°-30°	441.5	27.3
30°-40°	451.9	27.9
40°-50°	263.3	16.3
50°-60°	60.5	3.7
60°-70°	7.5	0.5
70°-80°	1.9	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	831.9	51.4
0°-40°	1283.9	79.4
0°-60°	1607.7	99.4
0°-90°	1617.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1617.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1010	
5°	1016	97
15°	1038	293
25°	968	442
35°	733	452
45°	339	263
55°	59	61
65°	6	7
75°	2	2
85°	0	0
90°	0	



TEST NUMBER: P203733
CATALOG NUMBER: MRI-DRV-FLD6C-15-L935 F6LC-W-X-LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	1010.2
2.5°	1008.3
5°	1015.7
7.5°	1023.0
10°	1032.1
12.5°	1034.0
15°	1037.7
17.5°	1034.0
20°	1024.8
22.5°	995.5
25°	968.0
27.5°	924.0
30°	867.2
32.5°	808.5
35°	733.4
37.5°	649.0
40°	555.5
42.5°	451.0
45°	339.2
47.5°	236.5
50°	155.8
52.5°	99.0
55°	58.7
57.5°	31.2
60°	16.5
62.5°	9.2
65°	5.5
67.5°	5.5
70°	3.7
72.5°	1.8
75°	1.8
77.5°	1.8
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)